

product type designation

product description

PROFIBUS Plastic Fiber Optic standard cable

Fiber-optic cable with polyoptical fiber, preferred length, preassembled

PROFIBUS Plastic Fiber Optic, Standard cable with 4 BFOC connectors, length 80 m.



product brand name

Technical Product Detail Page

suitability for use

version of the assembled FO cable

cable designation

wire length

SIMATIC NET

<https://l.siemens.com/1P6XV1821-0BN80>

Cable for indoor applications

Assembled with four BFOC connectors

I-V4Y(ZN)Y 2P 980/1000

80 m

optical data

attenuation factor per length

- at 650 nm / maximum
- at 660 nm / maximum

160 dB/km
230 dB/km

bandwidth length product

- at 650 nm

1 GHz·m

mechanical data

number of fibers / per FOC core

1

number of FO cores / per FOC cable

2

version of the FO conductor fiber

Step index fiber 980/1000 µm

outer diameter

- of the optical fibers
- of the optical fiber sheath
- of the FOC core sheath

980 µm
1000 µm
2.2 mm

symmetrical deviation / of the outer diameter of the FOC core sheath

0.1 mm

outer diameter / of the cable

7.8 mm

symmetrical deviation / of the outer diameter of the line

0.3 mm

material

- of the fiber-optic cable core
- of the optical fiber sheath
- of the FOC core sheath
- of the fiber-optic cable sheath
- of the strain relief

Polymethylmethacrylate (PMMA)
Fluoridated special polymer
PA
PVC
Kevlar fibers

color

- of the FOC core sheath
- of cable sheath

orange/black
Violet

bending radius

- with single bend / minimum permissible
- with multiple bends / minimum permissible

100 mm
150 mm

tensile load

during installation / short-term	100 N
during operation / maximum	100 N
short-term shear force per length	100 N/cm
weight per length	65 kg/km
ambient conditions	
ambient temperature	
during operation	-30 ... +70 °C
during storage	-30 ... +70 °C
during transport	-30 ... +70 °C
during installation	50 °C
fire behavior	flame-resistant acc. to IEC 60332-1-2
chemical resistance	
to mineral oil	conditional resistance
to grease	conditional resistance
radiological resistance / to UV radiation	not resistant
protection class IP	IP20
product features, product functions, product components / general	
product feature	
halogen-free	No
silicon-free	Yes
product component / rodent protection	No
wire length	
for POF FOC / with PROFIBUS / maximum	80 m
standards, specifications, approvals	
certificate of suitability	
UL approval	Yes; (UL) OFN
RoHS conformity	Yes
further information / internet links	
internet link	
to website: Selection guide for cables and connectors	https://support.industry.siemens.com/cs/ww/en/view/109766358
to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
to website: Industrial communication	https://www.siemens.com/simatic-net
to web page: SiePortal	https://sieportal.siemens.com/
to website: Image database	https://www.automation.siemens.com/bilddb
to website: CAX-Download-Manager	https://www.siemens.com/cax
to website: Industry Online Support	https://support.industry.siemens.com
security information / header	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)
Approvals / Certificates	
General Product Approval	



[Declaration of Con-
formity](#)



[Manufacturer Declara-
tion](#)

[China RoHS](#)

General Product Approval	Maritime application	other
--------------------------	----------------------	-------



[Confirmation](#)

last modified:

3/10/2026 