


product type designation

product description



PROFIBUS FC Standard Cable GP

Standard bus cable (2-core), sold by the meter, unassembled

PROFIBUS FC Standard Cable GP, bus cable 2-wire, shielded, special configuration for quick assembly, Delivery unit: max. 1000 m, minimum order quantity 20 m sold by the meter

product brand name

SIMATIC NET

Technical Product Detail Page

<https://l.siemens.com/1P6XV1830-0EH10>

suitability for use

Standard cable specially designed for fast, permanent installation

cable designation

02YSY (ST) CY 1x2x0,64/2,55-150 VI KF 40 FR

wire length

sold by the meter

electrical data

attenuation factor per length

• at 9.6 kHz / maximum	0.0025 dB/m
• at 38.4 kHz / maximum	0.004 dB/m
• at 4 MHz / maximum	0.022 dB/m
• at 16 MHz / maximum	0.042 dB/m

impedance

• rated value	150 Ω
• at 9.6 kHz	270 Ω
• at 38.4 kHz	185 Ω
• at 3 MHz ... 20 MHz	150 Ω

relative symmetrical tolerance

• of the characteristic impedance at 9.6 kHz	10 %
• of the characteristic impedance at 38.4 kHz	10 %
• of the characteristic impedance at 3 MHz ... 20 MHz	10 %

loop resistance per length / maximum

110 mΩ/m

shield resistance per length / maximum

9.5 Ω/km

capacity per length / at 1 kHz

28.5 pF/m

operating voltage

• RMS value	80 V
-------------	------

mechanical data

number of electrical cores

2

design of the shield

Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires

type of electrical connection / FastConnect

Yes

outer diameter

• of inner conductor	0.65 mm
• of the wire insulation	2.55 mm
• of the inner sheath of the cable	5.4 mm
• of cable sheath	8 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.4 mm

material

• of the wire insulation • of the inner sheath of the cable • of cable sheath	polyethylene (PE) PVC PVC
color • of the insulation of data wires • of cable sheath	red/green Violet
bending radius • with single bend / minimum permissible • with multiple bends / minimum permissible	37.5 mm 75 mm
tensile load / maximum	100 N
weight per length	78 kg/km
ambient conditions	
ambient temperature • during operation • during storage • during transport • during installation • note	-40 ... +75 °C -40 ... +75 °C -40 ... +75 °C -40 ... +75 °C electrical properties measured at 20 °C
fire behavior	flame resistant according to IEC 60332-3-24 (Category C) and UL 1685 (CSA FT 4)
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance • to mineral oil • to grease • to water	oil resistant according to IEC 60811-2-1 (4 h / 70°C) Conditional resistance conditional resistance
radiological resistance / to UV radiation	resistant
product features, product functions, product components / general	
product feature • halogen-free • silicon-free	No Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; c(ETL)us, CMG / (ETL)us CL3 / Sun Res
UL/ETL style / 600 V Rating	Yes; cRUus AWM 21694 AWM I A/B 60°C 600V FT2
certificate of suitability • EAC approval • CE marking • UL approval • RoHS conformity	Yes Yes Yes Yes
• resistance to air pollution / conformity according to ANSI/ISA-71.04	Yes; G3
Marine classification association • American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • Det Norske Veritas (DNV) • Germanische Lloyd (GL) • Lloyds Register of Shipping (LRS) • Nippon Kaiji Kyokai (NK) • Polski Rejestr Statkow (PRS)	No No No No No No No
standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq] • total • during manufacturing • during operation • after end of life	0.92 kg 0.8 kg 0.02 kg 0.1 kg
further information / internet links	
internet link • to website: Selection guide for cables and connectors	https://support.industry.siemens.com/cs/ww/en/view/109766358

- to web page: selection aid TIA Selection Tool
- to web page: SiePortal
- to website: Image database
- to website: CAX-Download-Manager
- to website: Industry Online Support

<https://www.siemens.com/tstcloud>
<https://sieportal.siemens.com/>
<https://www.automation.siemens.com/bilddb>
<https://www.siemens.com/cax>
<https://support.industry.siemens.com>

security information

security information

Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Approvals / Certificates

General Product Approval

[Manufacturer Declaration](#)



[Declaration of Conformity](#)



[China RoHS](#)

General Product Approval

Environment

[Fire safety / Physical security](#)



[Declaration of Conformity](#)

[Environmental Conformations](#)



[Environmental Conformations](#)

Industrial Communication



last modified:

3/10/2026