

Siemens  
EcoTech



circuit breaker 3VA5 UL Frame 125 breaking capacity class S 25 kA @ 277 V 1-pole, line protection TM210, FTFM, In=90 A overload protection Ir=90 A permanently set short-circuit protection Ii=10 x In UL489 SB (naval), 50 degrees Celsius nut keeper kit on two sides

| Model                                                                                                                      |                             |
|----------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| product brand name                                                                                                         | SETRON                      |
| product designation                                                                                                        | Molded-case circuit breaker |
| product designation / according to UL file                                                                                 | SEAM                        |
| design of the product                                                                                                      | System protection           |
| design of the load switch / according to UL 489 / Heating, Air Conditioning, and Refrigeration circuit breaker (HACR Type) | Yes                         |
| design of the load switch / according to UL 489 / High-Intensity-Discharge circuit breaker (HID Type)                      | No                          |
| design of the load switch / according to UL 489 / Switching Duty circuit breaker (SWD Type)                                | No                          |
| design of the overcurrent release                                                                                          | TM210                       |
| protection function of the overcurrent release                                                                             | LI                          |
| number of poles                                                                                                            | 1                           |
| General technical data                                                                                                     |                             |
| operating voltage / at AC / rated value                                                                                    | 415 V                       |
| power loss [W] / maximum                                                                                                   | 7.13 W                      |
| power loss [W] / for rated value of the current / at AC / in hot operating state / per pole                                | 7.13 W                      |
| mechanical service life (operating cycles) / typical                                                                       | 20 000                      |
| electrical endurance (operating cycles) / at AC-1 / at 380/415 V                                                           | 8 000                       |
| electrical endurance (operating cycles) / at AC-1 / at 690 V                                                               | 4 000                       |
| electrical endurance (operating cycles) / at 480 V                                                                         | 8 000                       |
| electrical endurance (operating cycles) / at 600 V                                                                         | 4 000                       |
| product feature / for neutral conductors / upgradable/retrofitable / short-circuit and overload proof                      | No                          |
| product function                                                                                                           |                             |
| • communication function                                                                                                   | No                          |
| • other measurement function                                                                                               | No                          |
| Net Weight                                                                                                                 | 0.404 kg                    |
| Current                                                                                                                    |                             |
| marking / according to UL 489 / 100%-rated breaker                                                                         | No                          |
| operational current                                                                                                        |                             |
| • at 40 °C                                                                                                                 | 90 A                        |
| • at 45 °C                                                                                                                 | 88 A                        |
| • at 50 °C                                                                                                                 | 86 A                        |
| • at 55 °C                                                                                                                 | 84 A                        |

|                                                                                                                                                                                                                  |                                                                                                                                                                |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>• at 60 °C</li> <li>• at 65 °C</li> <li>• at 70 °C</li> </ul>                                                                                                             | 82 A<br>80 A<br>79 A                                                                                                                                           |
| <b>Switching capacity according to IEC 60947</b>                                                                                                                                                                 |                                                                                                                                                                |
| switching capacity class of the circuit breaker                                                                                                                                                                  | S                                                                                                                                                              |
| design of short-circuit protection                                                                                                                                                                               | For switching power values in DC networks, see the 3VA molded case circuit breaker device manual; link to be found under Service & Support in the last chapter |
| <b>Switching capacity according to UL 489</b>                                                                                                                                                                    |                                                                                                                                                                |
| current breaking capacity <ul style="list-style-type: none"> <li>• at 120 V</li> <li>• at 277 V</li> <li>• at 347 V</li> </ul>                                                                                   | 65 kA<br>25 kA<br>14 kA                                                                                                                                        |
| <b>Adjustable parameters</b>                                                                                                                                                                                     |                                                                                                                                                                |
| adjustable response value setting current (I <sub>r</sub> ) / of the L-trip / with I <sub>2t</sub> characteristic <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>                 | 90 A<br>90 A                                                                                                                                                   |
| adjustable response value delay time (t <sub>r</sub> ) / for L-tripping / with I <sub>2t</sub> characteristic <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>                     | 1 s<br>1 s                                                                                                                                                     |
| adjustable response value setting current (I <sub>i</sub> ) / for I-tripping <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>                                                      | 900 A<br>900 A                                                                                                                                                 |
| adjustable setting current (I <sub>N</sub> ) / for N-tripping <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>                                                                     | 0 A<br>0 A                                                                                                                                                     |
| product function / grounding protection                                                                                                                                                                          | No                                                                                                                                                             |
| <b>Mechanical Design</b>                                                                                                                                                                                         |                                                                                                                                                                |
| product component <ul style="list-style-type: none"> <li>• undervoltage release</li> <li>• voltage trigger</li> <li>• trip indicator</li> </ul>                                                                  | No<br>No<br>No                                                                                                                                                 |
| height [in]                                                                                                                                                                                                      | 5.51 in                                                                                                                                                        |
| height                                                                                                                                                                                                           | 140 mm                                                                                                                                                         |
| width [in]                                                                                                                                                                                                       | 1 in                                                                                                                                                           |
| width                                                                                                                                                                                                            | 25.4 mm                                                                                                                                                        |
| depth [in]                                                                                                                                                                                                       | 3.01 in                                                                                                                                                        |
| depth                                                                                                                                                                                                            | 76.5 mm                                                                                                                                                        |
| <b>Connections</b>                                                                                                                                                                                               |                                                                                                                                                                |
| arrangement of electrical connectors / for main current circuit                                                                                                                                                  | Front connection                                                                                                                                               |
| type of electrical connection / for main current circuit                                                                                                                                                         | nut keeper kit on both ends                                                                                                                                    |
| type of connectable conductor cross-sections / for flat-bar terminal connection / minimum                                                                                                                        | 12 x 1 mm                                                                                                                                                      |
| type of connectable conductor cross-sections / for flat-bar terminal connection / maximum                                                                                                                        | 17 x 6.5 mm                                                                                                                                                    |
| <b>Auxiliary circuit</b>                                                                                                                                                                                         |                                                                                                                                                                |
| number of CO contacts / for auxiliary contacts                                                                                                                                                                   | 0                                                                                                                                                              |
| <b>Accessories</b>                                                                                                                                                                                               |                                                                                                                                                                |
| product extension / optional / motor drive                                                                                                                                                                       | No                                                                                                                                                             |
| <b>Environmental conditions</b>                                                                                                                                                                                  |                                                                                                                                                                |
| protection class IP / on the front                                                                                                                                                                               | IP40                                                                                                                                                           |
| ambient temperature <ul style="list-style-type: none"> <li>• during operation / minimum</li> <li>• during operation / maximum</li> <li>• during storage / minimum</li> <li>• during storage / maximum</li> </ul> | -25 °C<br>70 °C<br>-40 °C<br>80 °C                                                                                                                             |
| reference code / according to IEC 81346-2                                                                                                                                                                        | Q                                                                                                                                                              |
| <b>Approvals / Certificates</b>                                                                                                                                                                                  |                                                                                                                                                                |

## General Product Approval



[Miscellaneous](#)

[Miscellaneous](#)



## General Product Approval

EMV

Test Certificates

[Confirmation](#)



[Type Test Certificates/Test Report](#)

Maritime application

other

Environment



[Miscellaneous](#)

[Confirmation](#)

[Environmental Confirmations](#)

Siemens  
EcoTech



## Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA5190-4ED12-1AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA5190-4ED12-1AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[https://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VA5190-4ED12-1AA0](https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA5190-4ED12-1AA0)

CAX-Online-Generator


<https://www.siemens.com/cax>


Tender specifications

<https://www.siemens.com/specifications>

Characteristic curves

[https://curves.simar.siemens.com/curves/<mmp\\_prod\\_noCOMP='HAUPT'></mmp\\_prod\\_no>](https://curves.simar.siemens.com/curves/<mmp_prod_noCOMP='HAUPT'></mmp_prod_no>)





last modified:

5/9/2025 

