SIEMENS

Data sheet 3LD2165-7UB01



SENTRON, Switch disconnector 3LD, change-over switch, 3-pole, Iu: 25 A, Operating power / at AC-23 A at 400 V: 9.5 kW, molded-plastic encapsulation for metric cable screw connection, knob-operated mechanism, black

Model	
product brand name	SENTRON
product designation	Switch disconnector
design of the product	Selector switch
display version for switch position indicator manual operation	1 ON - 0 OFF - 2 ON
type of switch	Molded-plastic enclosure for metric threaded joint
design of the actuating element	selector switch
color of the actuating element	black
design of handle	knob-operated mechanism, black
type of the driving mechanism motor drive	No
General technical data	
number of poles	3
number of poles note	N + PE
size of switch disconnector	2
mechanical service life (operating cycles) typical	100 000
electrical endurance (operating cycles)	
● at AC-23 A at 690 V	6 000
operating frequency maximum	50 1/h
degree of pollution	3
Voltage	
insulation voltage rated value	690 V
surge voltage resistance rated value	6 kV
operating voltage	
● at AC rated value	690 V
operating frequency rated value	
● minimum	50 Hz
● maximum	60 Hz
Protection class	
protection class IP	IP65
degree of protection NEMA rating	1, 4X, 12
protection class IP on the front	IP65
Dissipation	
power loss [W] for rated value of the current at AC in hot operating state per pole	0.6 W
Main circuit	
operational current	
● at AC-21 at 690 V rated value	25 A
● at AC-21 A at 240 V rated value	25 A

Subject to change without notice
© Copyright Siemens

● at AC-21 A at 400 V rated value	25 A
● at AC-21 A at 440 V rated value	25 A
● at AC-23 A at 400 V rated value	20 A
operating power	
● at AC-23 A at 240 V rated value	5 kW
● at AC-23 A at 400 V rated value	10 kW
● at AC-23 A at 440 V rated value	9.5 kW
● at AC-23 A at 690 V rated value	10 kW
● at AC-3 at 240 V rated value	4 kW
● at AC-3 at 400 V rated value	8 kW
● at AC-3 at 690 V rated value	7.5 kW
Auxiliary circuit	
number of CO contacts for auxiliary contacts	0
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	0
operating voltage of auxiliary contacts at AC maximum	500 V
continuous current of the auxiliary contact rated value	10 A
insulation voltage of the auxiliary switch rated value	500 V
Suitability	
suitability for use main switch	Yes
suitability for use switch disconnector	Yes
suitability for use EMERGENCY OFF switch	No
suitability for use maintenance/repair switch	Yes
Product details	
product feature can be locked into OFF position	No
Accessories	
product extension optional	
● motor drive	No
● voltage trigger	No
number of connectable NC contacts for auxiliary contacts attachable maximum	2
number of connectable NO contacts for auxiliary contacts attachable maximum	4
number of connectable CO contacts for auxiliary contacts attachable maximum	0
Short circuit	
conditional short-circuit current with line-side fuse protection	
● at 690 V by gG fuse rated value	50 kA
let-through current with closed switch	
● at 240 V for combination switch + gG fuse maximum	3.5 kA
● at 440 V for combination switch + gG fuse maximum	3.5 kA
● at 690 V for combination switch + gG fuse maximum permissible	4 kA
I2t value with closed switch	
● at 240 V for combination switch + gG fuse maximum	4 $kA^2 \cdot s$
● at 440 V for combination switch + gG fuse maximum	4 $kA^2 \cdot s$
● at 690 V for combination switch + gG fuse maximum	4 $kA^2 \cdot s$
design of the fuse link	
● for short-circuit protection of the main circuit required	fuse gL/gG: 25 A
● for short-circuit protection of the auxiliary switch required	fuse gL/gG: 10 A
operational current of upstream fuse rated value	25 A
according UL	
operational current at AC according to UL 508/UL 60947-4-1 rated value	25 A
operating voltage at AC at 50/60 Hz according to UL 508/UL 60947-4-1 rated value	600 V
active power [hp] at AC at 480 V according to UL 508/UL 60947-4-1 rated value	10

Subject to change without notice
© Copyright Siemens

active power [hp] at AC at 600 V according to UL 508/UL 60947-4-1 rated value	15
short-time withstand current (SCCR) at 600 V according to UL 508/UL 60947-4-1	5 kA
continuous current of upstream fuse according to UL rated value	50 A
type of fuse according to UL	RK5
Connections	
AWG number as coded connectable conductor cross section solid maximum	
•	8
•	14
type of connectable conductor cross-sections for copper conductor	
• solid	1x (1,5...16mm²)
• finely stranded with core end processing	1x (1,5...10mm²)
• stranded	1x (1,5...16mm²)
type of connectable conductor cross-sections for auxiliary contacts	
• **solid**	lateral auxiliary switch 2x (0,75 ... 2,5mm²), 1x 4mm²; front auxiliary switch 1x (0,75 ... 2,5mm²)
• **finely stranded with core end processing**	lateral auxiliary switch 2x (0,75 ... 1,5mm²), 1x 2,5mm²; front auxiliary switch 1x 2,5mm²
• **stranded**	lateral auxiliary switch 2x (0,75 ... 2,5mm²), 1x 4mm²; front auxiliary switch 1x (0,75 ... 2,5mm²)
type of electrical connection	
• **for main current circuit**	box terminal
• **for auxiliary contacts**	connection terminals
Mechanical Design	
height	188 mm
width	146 mm
depth	149 mm
type of device	fixed mounting
fastening method	Complete unit in enclosure
fastening method	
• 4-hole front mounting	No
• front mounting with central attachment	Yes
• rail mounting	No
Net Weight	882 g
Environmental conditions	
ambient temperature during operation	
• minimum	-25 °C
• maximum	55 °C
ambient temperature during storage	
• minimum	-25 °C
• maximum	55 °C

Approvals Certificates

Environment		**General Product Approval**			
Environmental Con-firmations	Environmental Con-firmations				

General Product Approval

	Miscellaneous		Confirmation		

Subject to change without notice
© Copyright Siemens


Test Certificates	Maritime application	other


Miscellaneous

Confirmation


Further information


Information on the packaging
https://support.industry.siemens.com/cs/ww/en/view/109813875
Information for data generation and storage
https://support.industry.siemens.com/cs/ww/en/view/109995012
Information- and Downloadcenter (Catalogs, Brochures,…)
https://www.siemens.com/lowvoltage/catalogs
Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3LD2165-7UB01
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
https://support.industry.siemens.com/cs/ww/en/ps/3LD2165-7UB01
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3LD2165-7UB01
CAx-Online-Generator
https://www.siemens.com/cax
Tender specifications
https://www.siemens.com/specifications
Kennlinien
https://curves.simaris.siemens.com/curves/3LD2165-7UB01





© Copyright Siemens





last modified: 7/15/2026

Subject to change without notice
© Copyright Siemens

Subject to change without notice
© Copyright Siemens