



SITOP PSU3600 DUAL/1ACDC/2x15VDC/3.5A

SITOP PSU3600 dual stabilized power supply Input: 120-230 V AC Output: 15 V/3,5 A 2x DC two potential-free outputs

General information	
Technical Product Detail Page	https://i.siemens.com/1P6EP3323-0SA00-0BY0
input	
type of the power supply network	1-phase AC or DC
supply voltage at AC	
• minimum rated value	120 V
• maximum rated value	230 V
• initial value	85 V
• full-scale value	264 V
supply voltage at AC	Derating at < 110 V AC/DC: output power max. 100 W
input voltage at DC	88 ... 250 V
wide range input	Yes
buffering time for rated value of the output current in the event of power failure minimum	10 ms
operating condition of the mains buffering	at Vin = 120 V, 40 ms at Vin = 187 V
line frequency	50/60 Hz
line frequency	47 ... 63 Hz
input current	
• at rated input voltage 110 V	1.3 A
• at rated input voltage 120 V	2.2 A
• at rated input voltage 220 V	0.7 A
• at rated input voltage 230 V	1.3 A
current limitation of inrush current at 25 °C maximum	35 A
I ² t value maximum	1 A ² s
fuse protection type	T 3.15 A (not accessible)
fuse protection type in the feeder	Recommended miniature circuit breaker: 6-10 A characteristic C
output	
voltage curve at output	Controlled, isolated DC voltage
number of outputs	2
output voltage at DC rated value	15 V
formula for output voltage	2 x 15 V DC
output voltage	
• at output 1 at DC rated value	15 V
• at output 2 at DC rated value	15 V
output voltage adjustable	Yes; via potentiometer per output
adjustable output voltage	12 ... 28 V
relative overall tolerance of the voltage	1 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.1 %

on slow fluctuation of ohm loading	1 %
residual ripple	
maximum	50 mV
voltage peak	
maximum	150 mV
display version for normal operation	Green LED grün for Vout >10 V (summation display)
type of signal at output	-
behavior of the output voltage when switching on	Overshoot of Vout < 1 %
response delay maximum	0.5 s
output current	
rated value	3.5 A
at output 1 rated value	3.5 A
at output 2 rated value	3.5 A
rated range	0 ... 3.5 A; Output power max. 60 W per output
supplied active power typical	105 W
bridging of equipment	Yes
number of parallel-switched equipment resources for increasing the power	2
efficiency	
efficiency in percent	88 %
power loss [W]	
at rated output voltage for rated value of the output current typical	18 W
protection and monitoring	
design of the overvoltage protection	≤ 35 V
property of the output short-circuit proof	Yes
design of short-circuit protection	Electronic shutdown, automatic restart
response value current limitation	5 A
design of the current limitation	depending on the voltage setting
safety	
galvanic isolation between input and output	Yes
galvanic isolation	Output voltage: SELV, ES1 (IEC 62368-1), DVC As (IEC 61204-7)
operating resource protection class	Class I
leakage current	
maximum	3.5 mA
protection class IP	IP20
EMC	
standard	
for emitted interference	EN 55022 Class B
for mains harmonics limitation	EN 61000-3-2
for interference immunity	EN 61000-6-2
standards, specifications, approvals	
certificate of suitability	
CE marking	Yes
UL approval	Yes; cULus-listed (UL 508, CSA C22.2 No. 107.1), file E197259; outputs NEC Class 2 acc. to UL 1310
EAC approval	Yes
Regulatory Compliance Mark (RCM)	Yes
NEC Class 2	Yes; according to UL1310
type of certification	
CB-certificate	No
standards, specifications, approvals hazardous environments	
certificate of suitability	
IECEX	No
ATEX	No
ULhazloc approval	No
FM registration	No
standards, specifications, approvals marine classification	
shipbuilding approval	No

Marine classification association			
American Bureau of Shipping Europe Ltd. (ABS)	No		
French marine classification society (BV)	No		
Det Norske Veritas (DNV)	No		
Lloyds Register of Shipping (LRS)	No		
ambient conditions			
ambient temperature			
during operation	-25 ... +70 °C; Derating > 60°C: 2%/°K		
during transport	-40 ... +70 °C		
during storage	-40 ... +70 °C		
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation		
connection method			
type of electrical connection	screw terminal		
at input	L1, N, PE: 1 screw terminal each for 0.5 ... 2.5 mm² single-core/finely stranded		
at output	+: 1 screw terminal per output for 0.5 ... 2.5 mm²; -: 2 screw terminals per output for 0.5 ... 2.5 mm²		
for auxiliary contacts	-		
mechanical data			
width × height × depth of the enclosure	42 × 125 × 125 mm		
installation width × mounting height	42 mm × 225 mm		
required spacing			
top	50 mm		
bottom	50 mm		
left	0 mm		
right	0 mm		
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15		
DIN-rail mounting	Yes		
S7 rail mounting	No		
wall mounting	No		
housing can be lined up	Yes		
net weight	0.55 kg		
further information internet links			
internet link			
to website: Industry Mall	https://mall.industry.siemens.com		
to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud		
to web page: power supplies	https://siemens.com/sitop		
to website: CAX-Download-Manager	https://siemens.com/cax		
to website: Industry Online Support	https://support.industry.siemens.com		
additional information			
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)		
security information			
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert . (V4.7)		
Classifications			
		Version	Classification

eClass	16	27-04-07-01
eClass	14	27-04-07-01
eClass	12	27-04-07-01
eClass	9.1	27-04-07-01
eClass	9	27-04-07-01
eClass	8	27-04-90-02
eClass	7.1	27-04-90-02
eClass	6	27-04-90-02
ETIM	10	EC002540
ETIM	9	EC002540
ETIM	8	EC002540
ETIM	7	EC002540
IDEA	4	4130
UNSPSC	15	39-12-10-04

Approvals Certificates

General Product Approval

[Manufacturer Declaration](#)

[Declaration of Conformity](#)



[China RoHS](#)



last modified: 5/5/2026