

Siemens
EcoTech



SIMATIC ET 200SP, relay module normally open, RQ NO-MA4x120VDC...230VAC/5A ST, with manual operation, packing unit VPE 1, suitable for BU type B0 or B1, Module diagnostics

General information	
Product type designation	RQ 4x120 V DC ... 230 V AC/5 A NO MA ST
HW functional status	From FS03
Firmware version	
• FW update possible	Yes
usable BaseUnits	BU type B0, B1
Color code for module-specific color-coded label	CC40
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V13 SP1
• STEP 7 configurable/integrated from version	V5.5 SP3 / -
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.3
Operating mode	
• DQ	Yes
• DQ with energy-saving function	No
• PWM	No
• Oversampling	No
• MSO	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	100 mA; without load
Power loss	
Power loss, typ.	1.5 W
Address area	
Address space per module	
• Inputs	1 byte; + 1 byte for QI information
• Outputs	1 byte
Hardware configuration	
Automatic encoding	Yes

• Mechanical coding element	Yes
• Type of mechanical coding element	type C
Selection of BaseUnit for connection variants	
• 2-wire connection	BU type B1
• 3-wire connection	BU type B0
Digital outputs	
Type of digital output	Relays
Number of digital outputs	4
Current-sinking	Yes
Current-sourcing	Yes
Digital outputs, parameterizable	Yes
Short-circuit protection	No
Switching frequency	
• with resistive load, max.	2 Hz
• with inductive load (acc. to IEC 60947-5-1, DC13), max.	0.5 Hz; provide one freewheeling diode for switching frequencies higher than 0.1 Hz
• with inductive load (acc. to IEC 60947-5-1, AC15), max.	0.5 Hz
• on lamp load, max.	2 Hz
Total current of the outputs	
• Current per channel, max.	5 A
• Current per module, max.	20 A
Total current of the outputs (per module)	
horizontal installation	
— up to 50 °C, max.	20 A
— up to 60 °C, max.	16 A
vertical installation	
— up to 40 °C, max.	20 A
— up to 50 °C, max.	16 A
Relay outputs	
• Number of relay outputs	4
• Rated supply voltage of relay coil L+ (DC)	24 V
• Current consumption of relays (coil current of all relays), max.	40 mA
• external protection for relay outputs	Yes, with miniature fuse max. 6 A tripping current and quick-response tripping characteristic
• Number of operating cycles, max.	7 000 000; see additional description in the manual
Switching capacity of contacts	
— with inductive load, max.	2 A; see additional description in the manual
— with resistive load, max.	5 A; see additional description in the manual
— Thermal continuous current, max.	5 A
— Switching current, min.	100 mA; 5 V DC
— Rated switching voltage (DC)	24 V DC to 120 V DC
— Rated switching voltage (AC)	24V AC to 230V AC
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	200 m
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Substitute values connectable	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnoses	
• Monitoring the supply voltage	Yes
• Wire break	No
• short-circuit	No
• Group error	Yes
Diagnostics indication LED	
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Channel status display	Yes; green LED
• for channel diagnostics	No

• for module diagnostics	Yes; green/red DIAG LED		
Potential separation			
Potential separation channels			
• between the channels	Yes		
• between the channels and backplane bus	Yes		
• between the channels and the power supply of the electronics	Yes		
Permissible potential difference			
between channels and backplane bus/supply voltage	240 V AC		
Isolation			
Isolation tested with	2 500 V DC (type test)		
tested with			
• between channels and backplane bus/supply voltage	2 500 V DC		
• between backplane bus and supply voltage	707 V DC (type test)		
Standards, approvals, certificates			
Suitable for safety functions	No		
Ecological footprint			
• environmental product declaration	Yes		
Global warming potential			
— global warming potential, (total) [CO2 eq]	25.5 kg		
— global warming potential, (during production) [CO2 eq]	3.54 kg		
— global warming potential, (during operation) [CO2 eq]	22.1 kg		
— global warming potential, (after end of life cycle) [CO2 eq]	-0.137 kg		
Ambient conditions			
Ambient temperature during operation			
• horizontal installation, min.	-30 °C		
• horizontal installation, max.	60 °C		
• vertical installation, min.	-30 °C		
• vertical installation, max.	50 °C		
Altitude during operation relating to sea level			
• Installation altitude above sea level, max.	2 000 m; On request: Installation altitudes greater than 2 000 m		
Absolute humidity			
• dew point, min.	-60 °C; suitable for dry room applications		
Dimensions			
Width	20 mm		
Height	73 mm		
Depth	58 mm		
Weights			
Weight, approx.	45 g		
Classifications			
		Version	Classification
	eClass	16	27-24-26-04
	eClass	14	27-24-26-04
	eClass	12	27-24-26-04
	eClass	9.1	27-24-26-04
	eClass	9	27-24-26-04
	eClass	8	27-24-26-04
	eClass	7.1	27-24-26-04
	eClass	6	27-24-26-04
	ETIM	10	EC001599
	ETIM	9	EC001599
	ETIM	8	EC001599
	ETIM	7	EC001599
	IDEA	4	3566

Approvals / Certificates

General Product Approval

[Miscellaneous](#)[Manufacturer Declaration](#)

General Product Approval

For use in hazardous locations

[China RoHS](#)

For use in hazardous locations

Maritime application

[EM](#)[NK / Nippon Kaiji Kyokai](#)

Maritime application

Environment

[CCS \(China Classification Society\)](#)[KR \(Korean Register of Shipping\)](#)Siemens
EcoTech

last modified:

2/1/2026