SIEMENS

Data sheet 3RF2410-2AB55



phase-out type solid-state contactor 3-phase 3RF2 AC 51 / 10 A / 40 °C 48-600 V / 230 V AC 2-phase controlled spring-loaded terminal blocking voltage 1200 V

product brand name	SIRIUS
product designation	solid-state contactor
design of the product	2-pole controlled
product type designation	3RF24
General technical data	
product function	zero-point switching
power loss [W] for rated value of the current	
● at AC in hot operating state	23 W
● at AC in hot operating state per pole	7.67 W
● without load current share typical	3.5 W
insulation voltage rated value	600 V
degree of pollution	3
surge voltage resistance of main circuit rated value	6 kV
protection class IP	IP20
protection class IP on the front according to IEC 60529	IP20
shock resistance according to IEC 60068-2-27	15 g / 11 ms
vibration resistance according to IEC 60068-2-6	2 g
reference code according to IEC 81346-2	Q
Substance Prohibitance (day/month/year)	07/01/2006
SVHC substance name	Lead monoxide (lead oxide) CAS-No. 1317-36-8 Dibutylbis(pentane-2,4-dionato-O,O')tin CAS-No. 22673-19-4
Net Weight	0.261 kg
Main circuit	
number of poles for main current circuit	3
number of NO contacts for main contacts	2
number of NC contacts for main contacts	0
type of voltage of the operating voltage	AC
operating voltage	
● at AC	
— at 50 Hz rated value	48 ... 600 V
— at 60 Hz rated value	48 ... 600 V
operating frequency rated value	50 ... 60 Hz
relative symmetrical tolerance of the operating frequency	10 %
operating range relative to the operating voltage at AC	
● at 50 Hz	40 ... 660 V
● at 60 Hz	40 ... 660 V
operational current	
● at AC-1 at 400 V rated value	10.5 A
● at AC-51 rated value	10.5 A

Subject to change without notice
© Copyright Siemens

● at AC-51 according to IEC 60947-4-3	7 A
● according to UL 508 rated value	7 A
operational current minimum	100 mA
rate of voltage rise at the thyristor for main contacts maximum permissible	500 V/µs
blocking voltage at the thyristor for main contacts maximum permissible	1 200 V
reverse current of the thyristor	10 mA
derating temperature	40 °C
surge current resistance rated value	200 A
I2t value maximum	200 A²·s
Control circuit/ Control	
type of voltage of the control supply voltage	AC
control supply voltage 1 at AC	
● at 50 Hz	180 ... 230 V
● at 60 Hz	180 ... 230 V
control supply voltage at AC	
● at 50 Hz full-scale value for signal<0> recognition	40 V
● at 60 Hz full-scale value for signal<0> recognition	180 V
● initial value for signal <1> detection	180 V
control supply voltage frequency	
● 1 rated value	45 Hz
● 2 rated value	66 Hz
symmetrical line frequency tolerance	5 Hz
control current at minimum control supply voltage	
● at AC	2 mA
control current at AC rated value	15 mA
ON-delay time	40 ms; additionally max. one half-wave
Installation/ mounting/ dimensions	
fastening method side-by-side mounting	Yes
fastening method	screw fixing and snap-on mounting on standard mounting rail 35 mm according to IEC 60715
design of the thread of the screw for securing the equipment	M4
height	95 mm
width	45 mm
depth	96.5 mm
Connections/ Terminals	
product component removable terminal for auxiliary and control circuit	Yes
type of electrical connection	
● for main current circuit	spring-loaded terminals
● for auxiliary and control circuit	spring-loaded terminals
type of connectable conductor cross-sections	
● for main contacts	
— solid	2x (0.5 ... 2.5 mm²)
— finely stranded with core end processing	2x (0.5 ... 1.5 mm²)
— finely stranded without core end processing	2x (0.5 ... 2.5 mm²)
● for AWG cables for main contacts	2x (18 ... 14)
connectable conductor cross-section for main contacts	
● solid or stranded	0.5 ... 2.5 mm²
● finely stranded with core end processing	0.5 ... 1.5 mm²
● finely stranded without core end processing	0.5 ... 2.5 mm²
type of connectable conductor cross-sections	
● for auxiliary and control contacts	
— solid	0.5 ... 1.5 mm²
— finely stranded with core end processing	0.5 ... 2.5 mm²
— finely stranded without core end processing	0.5 ... 2.5 mm²
● for AWG cables for auxiliary and control contacts	1x (20 ... 12)
AWG number as coded connectable conductor cross	14 ... 10

Subject to change without notice
© Copyright Siemens

section for main contacts	
stripped length of the cable	
● for main contacts	10 mm
● for auxiliary and control contacts	10 mm
UL/CSA ratings	
operational current according to UL 508 rated value	7 A
Electrical Safety	
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front
Ambient conditions	
installation altitude at height above sea level maximum	1 000 m
ambient temperature	
● during operation	-25 ... +60 °C
● during storage	-55 ... +80 °C
Electromagnetic compatibility	
conducted interference	
● due to burst according to IEC 61000-4-4	2 kV / 5 kHz, behavior criterion 2
● due to conductor-earth surge according to IEC 61000-4-5	2 kV, behavior criterion 2
● due to conductor-conductor surge according to IEC 61000-4-5	1 kV, behavior criterion 2
● due to high-frequency radiation according to IEC 61000-4-6	140 dBuV in the frequency range 0.15 ... 80 MHz, behavior criterion 1
electrostatic discharge according to IEC 61000-4-2	4 kV contact discharging / 8 kV air discharging, behavior criterion 2
conducted HF interference emissions according to CISPR11	Class A for industrial environment
field-bound HF interference emission according to CISPR11	Class A for industrial environment
Short-circuit protection, design of the fuse link	
manufacturer's article number	
● of full range R fuse link for semiconductor protection at NH design usable	3NE1813-0
● of full range R fuse link for semiconductor protection at cylindrical design usable	5SE1310; Maximum operating voltage 400 V!
● of back-up R fuse link for semiconductor protection at NH design usable	3NE8015-1
● of back-up R fuse link for semiconductor protection at cylindrical design 10 x 38 mm usable	3NC1016
● of back-up R fuse link for semiconductor protection at cylindrical design 14 x 51 mm usable	3NC1420
● of back-up R fuse link for semiconductor protection at cylindrical design 22 x 58 mm usable	3NC2220
manufacturer's article number of the gG fuse at NH design usable	
● up to 460 V	3NA3801; These fuses have a smaller rated current than the semiconductor relays

Approvals Certificates

Environment	General Product Approval				
Environmental Confirmations	EPD	cULus	EAC	CE EG-Konf.	UKCA


EMV	Test Certificates	other			
RCM	Type Test Certificates/Test Report	Confirmation	Miscellaneous	Confirmation	产品合格 QC PASS


Further information

Information on the packaging
https://support.industry.siemens.com/cs/ww/en/view/109813875
Information for data generation and storage
https://support.industry.siemens.com/cs/ww/en/view/109995012


Subject to change without notice
© Copyright Siemens


Information- and Downloadcenter (Catalogs, Brochures,…)
https://www.siemens.com/ic10
Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RF2410-2AB55
Cax online generator
https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RF2410-2AB55
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
https://support.industry.siemens.com/cs/ww/en/ps/3RF2410-2AB55
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RF2410-2AB55&lang=en





Subject to change without notice
© Copyright Siemens





last modified: 4/4/2026

Subject to change without notice
© Copyright Siemens