

Siemens
EcoTech



SIMATIC ET 200SP, BaseUnit BU20-P6+A2+4D, BU type C0, Push-in terminals, with 2 AUX terminals, New load group, WxH: 20 mmx117 mm



General information	
Product type designation	BU type C0
HW functional status	FS10 and higher
Supply voltage	
Rated value (DC)	See manual
• For P1 and P2 bus	24 V
• For AUX bus	24 V; Equal potential group to P1/P2 bus or PE
• for process terminals	24 V
Rated value (AC)	See manual
• For P1 and P2 bus	230 V
• For AUX bus	230 V; Equal potential group to P1/P2 bus or PE
• for process terminals	230 V
external protection for power supply lines	Yes; 10 A miniature circuit breaker with type B or C tripping characteristic for the respective rated supply voltage
Mains filter	
• Integrated	No
Current carrying capacity	
up to 60 °C, max.	10 A
For P1 and P2 bus, max.	10 A
For AUX bus, max.	10 A
For process terminals, max.	5 A; 10 A for process terminals 5 and 6
Hardware configuration	
Automatic encoding	Yes
Slots	
• Number of slots	1
Potential separation	
between backplane bus and supply voltage	Yes
between process terminals and supply voltage	Yes
between power bus and supply voltage	No
Isolation	
Isolation tested with	3 100 V DC
Standards, approvals, certificates	
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	0.873 kg

— global warming potential, (during production) [CO2 eq]	0.866 kg		
— global warming potential, (during operation) [CO2 eq]	0 kg		
— global warming potential, (after end of life cycle) [CO2 eq]	-0.0011 kg		
Ambient conditions			
Ambient temperature during operation			
• horizontal installation, min.	-30 °C		
• horizontal installation, max.	60 °C		
• vertical installation, min.	-30 °C		
• vertical installation, max.	50 °C		
Altitude during operation relating to sea level			
• Installation altitude above sea level, max.	2 000 m; On request: Installation altitudes greater than 2 000 m		
Absolute humidity			
• dew point, min.	-60 °C; suitable for dry room applications		
Accessories			
Color coding labels			
• for process terminals	CC51, CC52		
• for AUX terminals	CC84 to CC86		
• for add-on terminals	does not exist		
Connection method			
Terminals			
• Terminal type	Push-in terminal		
• system-integrated shield connection	Yes; Optional		
• Conductor cross-section, min.	0.14 mm²; AWG 26		
• Conductor cross-section, max.	2.5 mm²; AWG 14		
• Number of process terminals to I/O module	12; Pro slot		
• Number of terminals to AUX bus	0		
• Number of add-on terminals	0		
• Number of terminals with connection to P1 and P2 bus	0; Pro slot		
Dimensions			
Width	20 mm		
Height	117 mm		
Depth	35 mm		
Weights			
Weight, approx.	47 g		
Classifications			
		Version	Classification
	eClass	16	27-24-26-03
	eClass	14	27-24-26-03
	eClass	12	27-24-26-03
	eClass	9.1	27-24-26-03
	eClass	9	27-24-26-03
	eClass	8	27-24-26-03
	eClass	7.1	27-24-26-03
	eClass	6	27-24-26-03
	ETIM	10	EC001598
	ETIM	9	EC001598
	ETIM	8	EC001598
	ETIM	7	EC001598
	IDEA	4	3560
	UNSPSC	15	32-15-17-04
Approvals / Certificates			
General Product Approval			

[Manufacturer Declaration](#)



General Product Approval

For use in hazardous locations



[CCC-Ex](#)

[FM](#)

For use in hazardous locations

Maritime application



[Type Examination Certificate](#)

[Miscellaneous](#)



[CCC-Ex](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



Maritime application

Environment

[CCS \(China Classification Society\)](#)

[KR \(Korean Register of Shipping\)](#)



Siemens
EcoTech



last modified:

2/1/2026