



Figure similar

SIMATIC S7-1500, CM PTP RS422/485 HF Communication module for Serial connection RS422 and RS485, Freeport, 3964 (R), USS, MODBUS RTU Master, Slave, 115200 Kbit/s, 15-Pin D-sub socket

General information	
Product type designation	CM PtP RS 422 / 485 HF
Product function	
• I&M data	Yes; I&M 0
• Fast startup	Yes
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V12 / V12
• STEP 7 configurable/integrated from version	V5.5 SP2 with GSD file
• PROFIBUS from GSD version/GSD revision	- / -
• PROFINET from GSD version/GSD revision	V2.3 / -
Installation type/mounting	
Rail mounting	Yes; S7-1500 mounting rail
Input current	
Current consumption (rated value)	43 mA; From the backplane bus
Power	
Power consumption from the backplane bus	0.65 W
Power loss	
Power loss, typ.	0.6 W
Address area	
Address space per module	
• Inputs	8 byte
Interface types	
RS 485	
• Transmission rate, max.	115.2 kbit/s
• Cable length, max.	1 200 m
RS 422	
• Transmission rate, max.	115.2 kbit/s
• Cable length, max.	1 200 m
• 4-wire full duplex connection	Yes
• 4-wire multipoint connection	No
Protocols	
Integrated protocols	
Freeport	
— Telegram length, max.	4 kbyte
— Bits per character	7 or 8
— Number of stop bits	1 or 2 bit
— Parity	None, even, odd, always 1, always 0, any
3964 (R)	

— Telegram length, max.	4 kbyte		
— Bits per character	7 or 8		
— Number of stop bits	1 or 2 bit		
— Parity	None, even, odd, always 1, always 0, any		
Modbus RTU master			
— Address area	1 to 247, extended 1 to 65535		
— max. number of devices	32		
Modbus RTU device			
— Address area	1 to 247, extended 1 to 65535		
Telegram buffer			
• Buffer memory for telegrams	8 kbyte		
• Number of telegrams which can be buffered	255		
Interrupts/diagnostics/status information			
Diagnostics function	Yes		
Alarms			
• Diagnostic alarm	Yes		
• Hardware interrupt	No		
Diagnoses			
• Wire break	Yes		
Diagnostics indication LED			
• RUN LED	Yes; green LED		
• ERROR LED	Yes; red LED		
• Receive RxD	Yes; Yellow LED		
• Transmit TxD	Yes; Yellow LED		
Potential separation			
between backplane bus and interface	Yes		
Isolation			
Isolation tested with	707 V DC (type test)		
Ambient conditions			
Ambient temperature during operation			
• horizontal installation, min.	0 °C		
• horizontal installation, max.	60 °C		
• vertical installation, min.	0 °C		
• vertical installation, max.	40 °C		
Altitude during operation relating to sea level			
• Installation altitude above sea level, max.	5 000 m; restrictions for installation altitudes > 2 000 m, see ET 200MP system manual		
Decentralized operation			
to SIMATIC S7-300	Yes		
to SIMATIC S7-400	Yes		
to SIMATIC S7-1500	Yes		
to standard PROFINET controller	Yes		
Dimensions			
Width	35 mm		
Height	147 mm		
Depth	127 mm		
Weights			
Weight, approx.	0.22 kg		
Classifications			
		Version	Classification
	eClass	16	27-24-22-08
	eClass	14	27-24-22-08
	eClass	12	27-24-22-08
	eClass	9.1	27-24-22-08
	eClass	9	27-24-22-08
	eClass	8	27-24-22-08
	eClass	7.1	27-24-22-08

eClass	6	27-24-22-08
ETIM	10	EC001423
ETIM	9	EC001423
ETIM	8	EC001423
ETIM	7	EC001423
IDEA	4	3564
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval

[Miscellaneous](#)



[Manufacturer Declaration](#)



General Product Approval

For use in hazardous locations



[China RoHS](#)



[FM](#)



For use in hazardous locations

[FM](#)

[CCC-Ex](#)



[Type Examination Certificate](#)

[Miscellaneous](#)

For use in hazardous locations

Maritime application

[CCC-Ex](#)



[NK / Nippon Kaiji Kyokai](#)

Maritime application



[CCS \(China Classification Society\)](#)

[KR \(Korean Register of Shipping\)](#)

last modified:

10/23/2025