


SCALANCE XR324-12M; managed IE switch, 19" rack; 12x 100/1000 Mbit/s 2-port media modules, electrical or optical; LED diagnostics; error signaling Contact; Select/set pushbutton, PROFINET IO device, network management, Integrated redundancy manager, office features (RSTP, VLAN, IGMP,...) C-PLUG in scope of supply; Power supply 230 V AC; Ports at the back.



product type designation	
product brand name	SCALANCE
product type designation	XR324-12M
Technical Product Detail Page	https://i.siemens.com/1P6GK5324-0GG10-3HR2
transfer rate	
transfer rate	10, 100, 1000 Mbit/s
interfaces / for communication / integrated	
number of 100 Mbit/s ST(BFOC) ports	
• for multimode	24
number of 100 Mbit/s SC ports	
• for multimode	24
interfaces / other	
number of electrical connections	
• for operator console	1
• for signaling contact	1
• for media module	12
• for power supply	1
type of electrical connection	
• for operator console	RJ11
• for signaling contact	2-pole terminal block
• for power supply	2-pole terminal block
design of the removable storage	
• C-PLUG	Yes
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
type of voltage supply / redundant power supply unit	No
type of voltage / 1 / of the supply voltage	AC
• supply voltage / 1 / rated value	230 V
• power loss [W] / 1 / rated value	50 W
• supply voltage / 1 / voltage range	85 ... 264
• consumed current / 1 / maximum	0.8 A
• type of electrical connection / 1 / for power supply	2-pole terminal block
• product component / 1 / fusing at power supply input	Yes
• fuse protection type / 1 / at input for supply voltage	3,15 A / 250 V
ambient conditions	
ambient temperature	

• during operation • during storage • during transport • note	-40 ... +70 °C -40 ... +85 °C -40 ... +85 °C Reduced operating temperature through the use of media modules (-40 °C to +70 °C) or SFP plug-in transceivers (-40 °C to +60 °C). If the device is installed in the vertical position, the maximum operating temperature is reduced to +50 °C.
relative humidity • at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	19-inch rack
number of modular height units / relating to 19-inch cabinet	1
width	483 mm
height	44 mm
depth	305 mm
net weight	5.9 kg
product feature / conformal coating	Yes
fastening method • 19-inch installation • 35 mm DIN-rail mounting • wall mounting • S7-300 rail mounting • S7-1500 rail mounting	When used in shipbuilding, the device must be secured in the 19" rack at four points Yes No No No No
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of <1~0.3~s	100
cascading in cases of star topology	any (depending only on signal propagation time)
product functions / management, configuration, engineering	
product function • CLI • web-based management • MIB support • TRAPs via email • configuration with STEP 7 • RMON • port mirroring • multiport mirroring • CoS • PROFINET IO diagnosis • switch-managed	Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes
PROFINET conformity class	B
protocol / is supported • Telnet • HTTP • HTTPS • TFTP • FTP • BOOTP • GMRP • DCP • LLDP • SNMP v1 • SNMP v2 • SNMP v3 • IGMP (snooping/querier)	Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes
identification & maintenance function • I&M0 - device-specific information	Yes

• I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes
product functions / VLAN	
product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
• VLAN dynamic	Yes
number of VLANs / maximum	255
number of VLANs - dynamic / maximum	255
product functions / DHCP	
product function	
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes
product functions / redundancy	
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• ring redundancy	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure MSTP	Yes
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
• passive listening	Yes
protocol / is supported	
• STP/RSTP	Yes
• STP	Yes
• RSTP	Yes
• MSTP	Yes
• RSTP big network support	Yes
• LACP	Yes
product functions / security	
product function	
• IEEE 802.1x (radius)	Yes
• broadcast/multicast/unicast limiter	Yes
• broadcast blocking	Yes
protocol / is supported	
• SSH	Yes
product functions / time	
product function	
• SICLOCK support	Yes
protocol / is supported	
• NTP	Yes
• SNTP	Yes

• IEEE 1588 profile default	Yes
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• UKCA marking	Yes
• cULus approval	Yes
• KC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
standard	
• for EMC interference emission	EN 61000-6-4:2007 (Class A)
• for immunity to EMC	EN 61000-6-2:2005
• for safety / from CSA and UL	UL 508, CSA C22.2 No. 142-M1987
standards, specifications, approvals / other	
certificate of suitability	
• railway application in accordance with EN 50155	No
• RoHS conformity	Yes
resistance to air pollution / conformity according to ANSI/ISA-71.04	Yes; G3
standards, specifications, approvals / marine classification	
certificate of suitability / shipbuilding approval / note	Certifications marked 'No' are currently under renewal.
Marine classification association	
• Det Norske Veritas (DNV)	No
• Royal Institution of Naval Architects (RINA)	Yes
standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	674.58 kg
• during manufacturing	207 kg
• during operation	466.64999 kg
• after end of life	0.93 kg
product functions / general	
MTBF	15 a
warranty period	5 a
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors	https://support.industry.siemens.com/cs/ww/en/view/109766358
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
• to website: Industrial communication	https://www.siemens.com/simatic-net
• to web page: SiePortal	https://sieportal.siemens.com/
• to website: Image database	https://www.automation.siemens.com/bilddb
• to website: CAX-Download-Manager	https://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)
Approvals / Certificates	

Environmental Product Declaration	
• global warming potential [CO2 eq] / during manufacturing	207 kg
• global warming potential [CO2 eq] / during operation	466.65 kg
• global warming potential [CO2 eq] / after end of life	0.93 kg
• global warming potential [CO2 eq] / total	674.58 kg
Environment	General Product Approval



[Declaration of Con-
formity](#)



General Product Approval	Test Certificates	Maritime application
 RCM	China RoHS	 ABS
	Type Test Certific- ates/Test Report	 BUREAU VERITAS
		 DNV

Maritime application
 LRS
NK / Nippon Kaiji Ky- okai
 RINA

last modified: 4/23/2026 