SIEMENS

## Data sheet 3RT1456-6PP35



power contactor AC-1 275 A / 690 V / 40 °C 3-pole, Uc: 200-277 V AC(50-60 Hz) / DC PLC input 24 V DC drive: electronic auxiliary contacts 2 NO + 2 NC main circuit: busbar control and auxiliary circuit: screw terminal with remaining lifetime indicator

| | |
|---|---|
| **product brand name** | SIRIUS |
| **product designation** | Contactor |
| **product type designation** | 3RT14 |
| **General technical data** | |
| **size of contactor** | S6 |
| **product extension** | |
| ● function module for communication | No |
| ● auxiliary switch | Yes |
| **power loss [W] for rated value of the current** | |
| ● at AC in hot operating state | 86.4 W |
| ● at AC in hot operating state per pole | 28.8 W |
| ● without load current share typical | 2.8 W |
| **type of calculation of power loss current-dependent** | quadratic |
| **insulation voltage** | |
| ● of main circuit with degree of pollution 3 rated value | 1 000 V |
| ● of auxiliary circuit with degree of pollution 3 rated value | 500 V |
| **surge voltage resistance** | |
| ● of main circuit rated value | 8 kV |
| ● of auxiliary circuit rated value | 6 kV |
| **shock resistance at rectangular impulse** | |
| ● at AC | 8,5 g / 5 ms, 4,2 g / 10 ms |
| ● at DC | 8,5 g / 5 ms, 4,2 g / 10 ms |
| **shock resistance with sine pulse** | |
| ● at AC | 13,4 g / 5 ms, 6,5 g / 10 ms |
| ● at DC | 13,4 g / 5 ms, 6,5 g / 10 ms |
| **mechanical service life (operating cycles)** | |
| ● of contactor typical | 10 000 000 |
| ● of the contactor with added electronically optimized auxiliary switch block typical | 5 000 000 |
| ● of the contactor with added auxiliary switch block typical | 10 000 000 |
| **reference code according to IEC 81346-2** | Q |
| **Substance Prohibitance (day/month/year)** | 05/01/2012 |
| **SVHC substance name** | Lead CAS-No. 7439-92-1<br>Lead monoxide (lead oxide) CAS-No. 1317-36-8<br>2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5<br>Melamine CAS-No. 108-78-1 |
| **Net Weight** | 3.631 kg |
| **Ambient conditions** | |
| installation altitude at height above sea level maximum | 2 000 m |


Subject to change without notice
© Copyright Siemens

| | |
|---|---|
| **ambient temperature** | |
| ● during operation | -25 ... +60 °C |
| ● during storage | -55 ... +80 °C |
| **relative humidity minimum** | 10 % |
| **relative humidity at 55 °C according to IEC 60068-2-30 maximum** | 95 % |
| **Main circuit** | |
| **number of poles for main current circuit** | 3 |
| **number of NO contacts for main contacts** | 3 |
| **number of NC contacts for main contacts** | 0 |
| **type of voltage for main current circuit** | AC |
| **operational current** | |
| ● at AC-1 | |
| — up to 690 V at ambient temperature 40 °C rated value | 275 A |
| — up to 690 V at ambient temperature 55 °C rated value | 250 A |
| — up to 690 V at ambient temperature 60 °C rated value | 250 A |
| ● at AC-3 | |
| — at 400 V rated value | 97 A |
| — at 690 V rated value | 97 A |
| minimum cross-section in main circuit at maximum AC-1 rated value | 140 mm² |
| **operational current** | |
| **● at 1 current path at DC-1** | |
| — at 24 V rated value | 250 A |
| — at 60 V rated value | 250 A |
| — at 110 V rated value | 18 A |
| — at 220 V rated value | 3.4 A |
| — at 440 V rated value | 0.8 A |
| — at 600 V rated value | 0.5 A |
| **● with 2 current paths in series at DC-1** | |
| — at 24 V rated value | 250 A |
| — at 60 V rated value | 250 A |
| — at 110 V rated value | 250 A |
| — at 220 V rated value | 20 A |
| — at 440 V rated value | 3.2 A |
| — at 600 V rated value | 1.6 A |
| **● with 3 current paths in series at DC-1** | |
| — at 24 V rated value | 250 A |
| — at 60 V rated value | 250 A |
| — at 110 V rated value | 250 A |
| — at 220 V rated value | 250 A |
| — at 440 V rated value | 11.5 A |
| — at 600 V rated value | 4 A |
| **● at 1 current path at DC-3 at DC-5** | |
| — at 24 V rated value | 250 A |
| — at 60 V rated value | 7.5 A |
| — at 110 V rated value | 2.5 A |
| — at 220 V rated value | 0.6 A |
| — at 440 V rated value | 0.17 A |
| — at 600 V rated value | 0.12 A |
| **● with 2 current paths in series at DC-3 at DC-5** | |
| — at 24 V rated value | 250 A |
| — at 60 V rated value | 250 A |
| — at 110 V rated value | 250 A |
| — at 220 V rated value | 2.5 A |
| — at 440 V rated value | 0.65 A |
| — at 600 V rated value | 0.37 A |


© Copyright Siemens

| | |
|---|---|
| **● with 3 current paths in series at DC-3 at DC-5** | |
| — at 24 V rated value | 250 A |
| — at 60 V rated value | 250 A |
| — at 110 V rated value | 250 A |
| — at 220 V rated value | 250 A |
| — at 440 V rated value | 1.4 A |
| — at 600 V rated value | 0.75 A |
| **no-load switching frequency** | |
| ● at AC | 1 000 1/h |
| ● at DC | 1 000 1/h |
| **operating frequency** | |
| ● at AC-1 maximum | 600 1/h |
| **Control circuit/ Control** | |
| **type of voltage** | AC/DC |
| **type of voltage of the control supply voltage** | AC/DC |
| **control supply voltage at AC** | |
| ● at 50 Hz rated value | 200 ... 277 V |
| ● at 60 Hz rated value | 200 ... 277 V |
| **control supply voltage at DC rated value** | 200 ... 277 V |
| **operating range factor control supply voltage rated value of magnet coil at DC** | |
| ● initial value | 0.8 |
| ● full-scale value | 1.1 |
| **operating range factor control supply voltage rated value of magnet coil at AC** | |
| ● at 50 Hz | 0.8 ... 1.1 |
| ● at 60 Hz | 0.8 ... 1.1 |
| **type of PLC-control input according to IEC 60947-1** | Type 2 |
| **consumed current at PLC-control input according to IEC 60947-1 maximum** | 20 mA |
| **design of the surge suppressor** | with varistor |
| **apparent pick-up power** | |
| **● at minimum rated control supply voltage at AC** | |
| — at 50 Hz | 190 V·A |
| — at 60 Hz | 190 V·A |
| **● at maximum rated control supply voltage at AC** | |
| — at 60 Hz | 280 V·A |
| — at 50 Hz | 280 V·A |
| **apparent pick-up power of magnet coil at AC** | |
| ● at 50 Hz | 280 V·A |
| **inductive power factor with closing power of the coil** | |
| ● at 50 Hz | 0.8 |
| **apparent holding power** | |
| ● at minimum rated control supply voltage at DC | 2.1 V·A |
| ● at maximum rated control supply voltage at DC | 2.8 V·A |
| **apparent holding power** | |
| **● at minimum rated control supply voltage at AC** | |
| — at 50 Hz | 4.3 V·A |
| — at 60 Hz | 4.3 V·A |
| **● at maximum rated control supply voltage at AC** | |
| — at 50 Hz | 5.2 V·A |
| — at 60 Hz | 5.2 V·A |
| **apparent holding power of magnet coil at AC** | |
| ● at 50 Hz | 4.4 V·A |
| **inductive power factor with the holding power of the coil** | |
| ● at 50 Hz | 0.5 |
| **closing power of magnet coil at DC** | 320 W |
| **holding power of magnet coil at DC** | 2.8 W |
| **closing delay** | |
| ● at AC | 35 ... 75 ms |


Subject to change without notice
© Copyright Siemens

| | |
|---|---|
| ● at DC | 35 ... 75 ms |
| **opening delay** | |
| ● at AC | 80 ... 90 ms |
| ● at DC | 80 ... 90 ms |
| **arcing time** | 10 ... 15 ms |
| **control version of the switch operating mechanism** | PLC-IN or Standard A1 - A2 (adjustable) |
| **Auxiliary circuit** | |
| **number of NC contacts for auxiliary contacts** | 2 |
| ● attachable | 4 |
| ● instantaneous contact | 1 |
| **number of NO contacts for auxiliary contacts** | 2 |
| ● attachable | 4 |
| ● instantaneous contact | 1 |
| operational current at AC-12 maximum | 10 A |
| **operational current at AC-15** | |
| ● at 230 V rated value | 6 A |
| ● at 400 V rated value | 3 A |
| ● at 500 V rated value | 2 A |
| ● at 690 V rated value | 1 A |
| **operational current at DC-13** | |
| ● at 24 V rated value | 10 A |
| ● at 48 V rated value | 2 A |
| ● at 60 V rated value | 2 A |
| ● at 110 V rated value | 1 A |
| ● at 125 V rated value | 0.9 A |
| ● at 220 V rated value | 0.3 A |
| ● at 600 V rated value | 0.1 A |
| **contact reliability of auxiliary contacts** | 1 faulty switching per 100 million (17 V, 1 mA) |
| **Short-circuit protection** | |
| design of the miniature circuit breaker for short-circuit protection of the auxiliary circuit up to 230 V | C characteristic: 10 A; 0.4 kA |
| **design of the fuse link** | |
| ● for short-circuit protection of the main circuit | |
| — with type of coordination 1 required | gG: 355 A (690 V, 100 kA) |
| — with type of coordination 2 required | gR: 350 A (690 V, 100 kA) |
| ● for short-circuit protection of the auxiliary switch required | gG: 10 A (500 V, 1 kA) |
| **Installation/ mounting/ dimensions** | |
| **mounting position** | with vertical mounting surface +/-90° rotatable, with vertical mounting surface +/- 22.5° tiltable to the front and back |
| fastening method side-by-side mounting | Yes |
| **fastening method** | screw fixing |
| **height** | 172 mm |
| **width** | 140 mm |
| **depth** | 170 mm |
| **required spacing** | |
| ● with side-by-side mounting | |
| — forwards | 20 mm |
| — upwards | 10 mm |
| — downwards | 10 mm |
| — at the side | 0 mm |
| ● for grounded parts | |
| — forwards | 20 mm |
| — upwards | 10 mm |
| — at the side | 10 mm |
| — downwards | 10 mm |
| ● for live parts | |
| — forwards | 20 mm |
| — upwards | 10 mm |
| — downwards | 10 mm |


Subject to change without notice
© Copyright Siemens

| | |
|---|---|
| — at the side | 10 mm |
| **Connections/ Terminals** | |
| **type of electrical connection** | |
| ● for main current circuit | Connection bar |
| ● for auxiliary and control circuit | screw-type terminals |
| ● at contactor for auxiliary contacts | Screw-type terminals |
| ● of magnet coil | screw terminal |
| **width of connection bar** | 17 mm |
| **thickness of connection bar** | 3 mm |
| **diameter of holes** | 9 mm |
| **number of holes** | 1 |
| **type of connectable conductor cross-sections** | |
| ● for AWG cables for main contacts | 4 ... 250 kcmil |
| **connectable conductor cross-section for main contacts** | |
| ● solid or stranded | 25 ... 120 mm² |
| ● stranded | 25 ... 120 mm² |
| **connectable conductor cross-section for auxiliary contacts** | |
| ● solid or stranded | 0.5 ... 4 mm² |
| ● finely stranded with core end processing | 0.5 ... 2.5 mm² |
| **type of connectable conductor cross-sections** | |
| ● for auxiliary contacts | |
| — solid | 2x (0.5 ... 1.5 mm²), 2x (0.75 ... 2.5 mm²), max. 2x (0.75 ... 4 mm²) |
| — solid or stranded | 2x (0,5 ... 1,5 mm²), 2x (0,75 ... 2,5 mm²), max. 2x (0,75 ... 4 mm²) |
| — finely stranded with core end processing | 2x (0.5 ... 1.5 mm²), 2x (0.75 ... 2.5 mm²) |
| ● for AWG cables for auxiliary contacts | 2x (20 ... 16), 2x (18 ... 14), 1x 12 |
| **AWG number as coded connectable conductor cross section for auxiliary contacts** | 18 ... 14 |
| **Safety related data** | |
| **product function** | |
| ● **mirror contact according to IEC 60947-4-1** | Yes |
| ● **positively driven operation according to IEC 60947-5-1** | No |
| **service life maximum** | 20 a |
| Electrical Safety | |
| **protection class IP on the front according to IEC 60529** | IP00; IP20 with box terminal/cover |
| **touch protection on the front according to IEC 60529** | finger-safe, for vertical contact from the front with box terminal/cover |

**Approvals Certificates**

| Environment | General Product Approval | | | | |
|---|---|---|---|---|---|
| Environmental Confirmations | CCC | cULus | KC | EAC | CE EG-Konf. |


| General Product Approval | EMV | Functional Saftey | Test Certificates | | Maritime application |
|---|---|---|---|---|---|
| UKCA | RCM | Type Examination Certificate | Type Test Certificates/Test Report | Special Test Certificate | DNV |


| Maritime application | other | | | | Railway |
|---|---|---|---|---|---|
| Lloyd's Register LRS | Confirmation | Miscellaneous | Confirmation | 产品合格 QC PASS | Special Test Certificate |


**Further information**


Subject to change without notice
© Copyright Siemens

**Information on the packaging**
https://support.industry.siemens.com/cs/ww/en/view/109813875
**Information for data generation and storage**
https://support.industry.siemens.com/cs/ww/en/view/109995012
**Information- and Downloadcenter (Catalogs, Brochures,…)**
https://www.siemens.com/ic10
**Industry Mall (Online ordering system)**
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RT1456-6PP35
**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**
https://support.industry.siemens.com/cs/ww/en/ps/3RT1456-6PP35
**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**
https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RT1456-6PP35&lang=en
**Cax online generator**
https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT1456-6PP35
**Kennlinien**
https://curves.simaris.siemens.com/curves/3RT1456-6PP35






© Copyright Siemens




**last modified:** 7/18/2026


Subject to change without notice
© Copyright Siemens