

Siemens
EcoTech



AS-Interface module, 4 inputs and 4 outputs, black, spring-loaded terminal (push-in) for input/output, for front plate mounting



product brand name	SIRIUS ACT
product designation	AS-Interface module
product type designation	3SU1
General technical data	
product function	4 DI / 4 DQ
degree of pollution	3
type of voltage	
• of the operating voltage	DC
• of the input voltage	DC
consumed current maximum	150 mA
protection class IP	IP20
shock resistance for railway applications according to EN 61373	Category 1, Class B
vibration resistance for railway applications according to EN 61373	Category 1, Class B
reference code according to IEC 81346-2	K
Substance Prohibitance (day/month/year)	10/01/2014
SVHC substance name	Lead monoxide (lead oxide) CAS-No. 1317-36-8 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5 Melamine CAS-No. 108-78-1 Diboron trioxide CAS-No. 1303-86-2
Net Weight	40.38 g
design of the device type	4 DI / 4 DQ
AS-Interface device profile	S-7.0.E
ID1 code	0...F
number of AS-i devices	1
operating voltage rated value	18 ... 31.6 V
operating voltage 1 at DC rated value	30 V
Communication/ Protocol	
protocol is supported	
• AS-Interface protocol	Yes
• ASIsafe (Safety at work) protocol	No
Inputs/ Outputs	
number of digital inputs	4
• safety-related	0
number of digital outputs	4
Connections/ Terminals	

type of electrical connection	spring-loaded terminal (push-in)		
type of connectable conductor cross-sections			
• solid without core end processing	1x (0.14 ... 0.5 mm²)		
• finely stranded without core end processing	1x (0.2 ... 0.5 mm²)		
• for AWG cables	1x (26 ... 20)		
Product Function			
suitability for use safety-related circuits	No		
Safety related data			
product function suitable for safety function	No		
test wear-related service life necessary	No		
ISO 13849			
category according to ISO 13849-1	4		
device type according to ISO 13849-1	1		
IEC 61508			
hardware fault tolerance according to IEC 61508	1		
Ambient conditions			
ambient temperature			
• during operation	-25 ... +70 °C		
• during storage	-40 ... +80 °C		
environmental category during operation according to IEC 60721	3M6, 3S2, 3B2, 3C3 (without salt spray), 3K6 (with relative humidity of 10 ... 95%, no condensation in operation permitted)		
Installation/ mounting/ dimensions			
fastening method			
• of modules and accessories	Front plate mounting		
• of the AS-i devices	Frontplattenbefestigung		
height	60 mm		
width	23.8 mm		
depth	53.5 mm		
Environmental footprint			
Environmental Product Declaration (EPD)	Yes		
global warming potential [CO2 eq] total	0.787 kg		
global warming potential [CO2 eq] during manufacturing	0.566 kg		
global warming potential [CO2 eq] during operation	0.235 kg		
global warming potential [CO2 eq] after end of life	-0.015 kg		
Approvals Certificates			
Environmental Product Declaration			
• global warming potential [CO2 eq] / during manufacturing	0.566 kg		
• global warming potential [CO2 eq] / during operation	0.235 kg		
• global warming potential [CO2 eq] / after end of life	-0.0145 kg		
• global warming potential [CO2 eq] / total	0.787 kg		
Environment		General Product Approval	
Environmental Confirmations     			
General Product Approval	EMV	Test Certificates	Maritime application
		Type Test Certificates/Test Report	Special Test Certificate
			
Maritime application	other		



[Confirmation](#)



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1400-1EK10-6AA0>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1400-1EK10-6AA0>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1400-1EK10-6AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1400-1EK10-6AA0&lang=en





last modified:

2/4/2026 