



Figure similar

contactor relay, 64E, EN 50011, 6 NO + 4 NC, screw terminal, AC operation, 110 V AC 50/60 Hz

|                                                                         |                                                                          |
|-------------------------------------------------------------------------|--------------------------------------------------------------------------|
| <b>product designation</b>                                              | Auxiliary contactor                                                      |
| <b>product type designation</b>                                         | 3TH4                                                                     |
| <b>size of contactor</b>                                                | 0                                                                        |
| <b>reference code according to IEC 81346-2</b>                          | K                                                                        |
| <b>Substance Prohibition (day/month/year)</b>                           | 12/31/2099                                                               |
| <b>Net Weight</b>                                                       | 0.455 g                                                                  |
| ambient temperature during operation                                    | -25 ... +55 °C                                                           |
| <b>type of voltage of the control supply voltage</b>                    | AC                                                                       |
| <b>control supply voltage at AC</b>                                     |                                                                          |
| • at 50 Hz rated value                                                  | 110 V                                                                    |
| • at 60 Hz rated value                                                  | 110 V                                                                    |
| <b>control supply voltage frequency</b>                                 |                                                                          |
| • 1 rated value                                                         | 50 Hz                                                                    |
| • 2 rated value                                                         | 60 Hz                                                                    |
| <b>number of NC contacts for auxiliary contacts</b>                     | 4                                                                        |
| • delayed switching                                                     | 0                                                                        |
| • lagging switching                                                     | 0                                                                        |
| • make-before-break switching                                           | 0                                                                        |
| <b>number of NO contacts for auxiliary contacts</b>                     | 6                                                                        |
| • delayed switching                                                     | 0                                                                        |
| • leading contact                                                       | 0                                                                        |
| • make-before-break switching                                           | 0                                                                        |
| number of CO contacts for auxiliary contacts                            | 0                                                                        |
| <b>identification number and letter for switching elements</b>          | 64 E                                                                     |
| <b>operational current at AC-15</b>                                     |                                                                          |
| • at 230 V rated value                                                  | 10 A                                                                     |
| • at 400 V rated value                                                  | 6 A                                                                      |
| <b>fastening method</b>                                                 | screw and snap-on mounting onto 35 mm DIN rail according to DIN EN 50022 |
| <b>height</b>                                                           | 78 mm                                                                    |
| <b>width</b>                                                            | 55 mm                                                                    |
| <b>depth</b>                                                            | 102 mm                                                                   |
| type of electrical connection for auxiliary and control circuit         | screw-type terminals                                                     |
| <b>Safety related data</b>                                              |                                                                          |
| product function positively driven operation according to IEC 60947-5-1 | Yes                                                                      |
| <b>B10 value with high demand rate according to SN 31920</b>            | 1 000 000; With 0.3 x I <sub>e</sub>                                     |
| IEC 61508                                                               |                                                                          |
| <b>T1 value</b>                                                         |                                                                          |

- for proof test interval or service life according to IEC 61508

20 a

Electrical Safety

protection class IP on the front according to IEC 60529

IP00; IP20 with screws tightened, even for contacts not in use

#### Approvals Certificates

Environment

General Product Approval

[Environmental Confirmations](#)



Functional Safety

Test Certificates

other

[Type Examination Certificate](#)

[Miscellaneous](#)

[Miscellaneous](#)

[Special Test Certificate](#)

[Type Test Certificates/Test Report](#)

[Confirmation](#)

other

Railway



[Special Test Certificate](#)

#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3TH4364-0AG2>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3TH4364-0AG2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)



[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3TH4364-0AG2&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3TH4364-0AG2&lang=en)

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3TH4364-0AG2>

Characteristic curves

[https://curves.simaris.siemens.com/curves/<mmp\\_prod\\_noCOMP="HAUPT"></mmp\\_prod\\_no>](https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP="HAUPT"></mmp_prod_no>)



---

last modified:

4/2/2025 