SIEMENS

Data sheet 4AV3302-2EB00-0A



Figure similar

POWER SUPPLY; PHASES:3; PN(KW):0,648; UPRI(V):575(600)-500-460(480)- 400(415)-230(240)-200; USEC(V DC):24; ISEC(A DC):27/32,5 (60/40 CEL); F(HZ):50...60; VECTOR GR./SHIELD WNG.:II0 /0; PROTECTION CL.:I; TA/ISOKL:60 /B; W(%):4,2; IP00; TYPE OF TERMINALS:SCREW CONNECTION; INSTALLATION:SCREW; EN 61558-2-6, EN61131-2 >UL/CSA-RECOGNIZED< >SAFETY ISOLATING TRANSFORMER<

General technical data		
product designation		4AV3302-2EB00-0A
product brand name		SIDAC
vector group		Ii0
certificate of suitability		CE
product function		
● temperature monitoring		No
● insulation monitoring		No
● short-circuit and overload proof		No
● varistor protective wiring		Yes
operating resource protection class		I
number of shielding windings		0
Inputs		
phase number of the inputs		3
type of current of the inputs		AC
input voltage		
● _1 rated value	V	575
● _2 rated value	V	500
● _3 rated value	V	460
● _4 rated value	V	400
● _5 rated value	V	230
● _6 rated value	V	200
electrical input frequency		
● minimum	Hz	50
● maximum	Hz	60
input voltage		
● minimum	V	180
● maximum	V	609.5
type of electrical connection at input for main current circuit		screw-type terminals
Outputs		
type of current		
● _1 at output		DC
output voltage		
● _1 rated value	V	24
output voltage of the measurement signal at analog output at DC maximum	V	28.8
output voltage of the measurement signal at analog output at DC minimum	V	20.4

Subject to change without notice
© Copyright Siemens

output current		
● _1 rated value	A	27
type of electrical connection at output for main current circuit		screw-type terminals
relative residual ripple		
● of the output voltage 1 for main current circuit maximum	%	5
Ambient conditions		
thermal class according to IEC 60085		B
ambient temperature rated value	°C	60
protection class IP		IP00
Mechanical data		
fastening method		screws
construction form of the iron core		3UI 90/50
width	mm	216
height	mm	220
depth	mm	158

Certificates/ approvals

General Product Approval	other	Environment
	Confirmation	Environmental Con-firmations

Further information

Information on the packaging
https://support.industry.siemens.com/cs/ww/en/view/109813875
Information for data generation and storage
https://support.industry.siemens.com/cs/ww/en/view/109995012
Information- and Downloadcenter (Catalogs, Brochures,…)
https://www.siemens.com/ic10
Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4AV3302-2EB00-0A
Cax online generator
https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AV3302-2EB00-0A
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
https://support.industry.siemens.com/cs/ww/en/ps/4AV3302-2EB00-0A
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AV3302-2EB00-0A&lang=en

last modified: 6/27/2025

Subject to change without notice
© Copyright Siemens