SIEMENS

Data sheet 6ED1052-1FB08-0BA2



LOGO! 230RCE,logic module, display power supply / I/O: 115 V/230 V/relay, 8 DI/4 DO, memory 400 blocks, modularly expandable, Ethernet, integrated web server, data log, user-defined web pages, standard microSD card for LOGO! Soft Comfort V8.4 or higher, older projects executable cloud connection, MQTT in all LOGO! 8.4 basic units

Display	
with display	Yes
Installation type/mounting	
Mounting	on 35 mm DIN rail, 4 spacing units wide
Supply voltage	
Rated value (DC)	
● 115 V DC	Yes
● 230 V DC	Yes; 240 V DC
permissible range, lower limit (DC)	100 V
permissible range, upper limit (DC)	253 V
Rated value (AC)	
● 115 V AC	Yes
● 230 V AC	Yes; 240 V AC
Line frequency	
● permissible range, lower limit	47 Hz
● permissible range, upper limit	63 Hz
Time of day	
Time switching clocks	
● Number	400; Max. 400, function-specific
● Power reserve	480 h
Digital inputs	
Number of digital inputs	8
Digital outputs	
Number of digital outputs	4; Relays
Short-circuit protection	No; external fusing necessary
Relay outputs	
Switching capacity of contacts	
— with inductive load, max.	3 A
— with resistive load, max.	10 A
EMC	
Emission of radio interference acc. to EN 55 011	
● Limit class B, for use in residential areas	Yes; Radio interference suppression according to EN55011, Limit Value Class B
Standards, approvals, certificates	
Siemens Eco Profile (SEP)	Siemens EcoTech
CE mark	Yes

Subject to change without notice
© Copyright Siemens

CSA approval	Yes; covered by UL cert
UL approval	Yes
FM approval	Yes
developed in accordance with IEC 61131	Yes
according to VDE 0631	Yes
Marine approval	Yes
Ecological footprint	
● environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	124 kg
— global warming potential, (during production) [CO2 eq]	9.93 kg
— global warming potential, (during operation) [CO2 eq]	115 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-0.383 kg
Ambient conditions	
Ambient temperature during operation	
● min.	-20 °C; No condensation
● max.	55 °C
Ambient temperature during storage/transportation	
● min.	-40 °C
● max.	70 °C
Altitude during operation relating to sea level	
● Ambient air temperature-barometric pressure-altitude	Tmin ... Tmax at 1 080 hPa ... 795 hPa (-1 000 m ... +2 000 m)
Dimensions	
Width	71.5 mm; 4 modular widths (MW)
Height	90 mm
Depth	60 mm

Classifications

	Version	Classification
eClass	16	27-24-22-16
eClass	14	27-24-22-16
eClass	12	27-24-22-16
eClass	9.1	27-24-22-16
eClass	9	27-24-22-16
eClass	8	27-24-22-16
eClass	7.1	27-24-22-16
eClass	6	27-24-22-16
ETIM	10	EC001417
ETIM	9	EC001417
ETIM	8	EC001417
ETIM	7	EC001417

Approvals / Certificates

General Product Approval

Manufacturer Declaration

General Product Approval | **For use in hazardous locations**

Manufacturer Declaration | CCC-Ex | FM

© Copyright Siemens

For use in hazard-ous locations	Maritime application				
CCC-Ex	ABS	BUREAU VERITAS	DNV	LRS	NK / Nippon Kaiji Ky-okai

Maritime application		Environment	
CCS (China Classifica-tion Society)	KR (Korean Register of Shipping)	EPD	Siemens EcoTech

last modified: 7/3/2026

Subject to change without notice
© Copyright Siemens