



LOGO! AM2 RTD expansion module, PS: 12/24 V DC, 2AI-50...+200°C
Pt100/1000 for LOGO! 8

Installation type/mounting	
Mounting	on 35 mm DIN rail, 2 spacing units wide
Supply voltage	
Rated value (DC)	
• 12 V DC	Yes; 10.8 V DC to 28.8 V DC
• 24 V DC	Yes; 10.8 V DC to 28.8 V DC
Input current	
Current consumption, typ.	30 mA
Analog inputs	
Number of analog inputs	2; 2 or 3 wire connection
Input ranges	
• Voltage	No
• Current	No
• Resistance thermometer	Yes; For PT100/PT1000 sensors
Input ranges (rated values), voltages	
• 0 to +10 V	No
Input ranges (rated values), currents	
• 0 to 20 mA	No
Input ranges (rated values), resistance thermometer	
• Pt 100	Yes
EMC	
Emission of radio interference acc. to EN 55 011	
• Limit class B, for use in residential areas	Yes
Degree and class of protection	
IP degree of protection	IP20
Standards, approvals, certificates	
CE mark	Yes
CSA approval	Yes
UL approval	Yes
FM approval	Yes
developed in accordance with IEC 61131	Yes
Marine approval	Yes
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	16.5 kg
— global warming potential, (during production) [CO2 eq]	3.22 kg
— global warming potential, (during operation) [CO2	13.4 kg

eq]

— global warming potential, (after end of life cycle)
[CO₂ eq]

-0.124 kg

Ambient conditions

Ambient temperature during operation

- min.
- max.

-20 °C; No condensation

55 °C

Dimensions

Width 35.5 mm

Height 90 mm

Depth 58 mm

Classifications

	Version	Classification
eClass	16	27-24-22-01
eClass	14	27-24-22-01
eClass	12	27-24-22-01
eClass	9.1	27-24-22-01
eClass	9	27-24-22-01
eClass	8	27-24-22-01
eClass	7.1	27-24-22-01
eClass	6	27-24-22-01
ETIM	10	EC001420
ETIM	9	EC001420
ETIM	8	EC001420
ETIM	7	EC001420
IDEA	4	3562
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval

[Miscellaneous](#)[Manufacturer Declaration](#)

EG-Konf.



UL



General Product Approval

[Metrological Approval](#)

RCM



EG-Konf.



General Product Approval

For use in hazardous locations

[China RoHS](#)[Manufacturer Declaration](#)[CCC-Ex](#)

UL

[FM](#)[CCC-Ex](#)**Maritime application**

ABS

BUREAU
VERITAS

DNV



LRS

[NK / Nippon Kaiji Kyokai](#)[CCS \(China Classification Society\)](#)

Maritime application

Environment



last modified:

7/2/2025 