SIEMENS

Data sheet 6EP1333-4BA00



SIMATIC PM 1507/1AC/24VDC/8A

SIMATIC PM 1507 24 V/8 A stabilized power supply for SIMATIC S7-1500 input: 120/230 V AC output: 24 V DC/8 A without Ex approval

General information	
Technical Product Detail Page	https://i.siemens.com/1P6EP1333-4BA00
product brand name	SIMATIC
product type designation	PM 1507
product designation	S7-1500 Power Module
type of current supply	24 V/8 A
input	
type of the power supply network	1-phase AC
phase number	1
voltage curve at input	AC
supply voltage at AC	Automatic range selection
supply voltage	120 V/230 V
input voltage 1 at AC	85 ... 132 V
input voltage 2 at AC	170 ... 264 V
supply voltage	
● at 50 Hz	230 V
● at 60 Hz	120 V
line frequency	50/60 Hz
line frequency	45 ... 65 Hz
wide range input	No
overvoltage overload capability	2.3 × Vin rated, 1.3 ms
buffering time for rated value of the output current in the event of power failure minimum	20 ms
operating condition of the mains buffering	at Vin = 93/187 V
input current	
● at rated input voltage 120 V	3.7 A
● at rated input voltage 230 V	1.7 A
current limitation of inrush current at 25 °C maximum	62 A
duration of inrush current limiting at 25 °C	
● maximum	3 ms
I2t value maximum	12 A²·s
fuse protection type	T 6.3 A/250 V (not accessible)
fuse protection type in the feeder	Recommended miniature circuit breaker: 16 A characteristic B or 10 A characteristic C
output	
voltage curve at output	Controlled, isolated DC voltage
product function output voltage controlled	Yes
product function output voltage stabilized	Yes
output voltage at DC rated value	24 V

Subject to change without notice
© Copyright Siemens

output voltage	
● at output 1 at DC rated value	24 V
output voltage	
● at output 1 at DC	24 V
output voltage adjustable	No
relative overall tolerance of the voltage	1 %
relative control precision of the output voltage	
● on slow fluctuation of input voltage	0.1 %
● on slow fluctuation of ohm loading	0.1 %
residual ripple	
● maximum	50 mV
voltage peak	
● maximum	150 mV
display version for normal operation	LED green for 24 V OK; LED red for error; LED yellow for stand-by
behavior of the output voltage when switching on	No overshoot of Vout (soft start)
response delay maximum	1.5 s
voltage increase time of the output voltage	
● typical	10 ms
output current	
● rated value	8 A
● rated range	0 ... 8 A
supplied active power typical	192 W
short-term overload current	
● on short-circuiting during the start-up typical	35 A
● at short-circuit during operation typical	35 A
duration of overloading capability for excess current	
● on short-circuiting during the start-up	70 ms
● at short-circuit during operation	70 ms
bridging of equipment	Yes
number of parallel-switched equipment resources for increasing the power	2
efficiency	
efficiency in percent	90 %
power loss [W]	
● at rated output voltage for rated value of the output current typical	21 W
closed-loop control	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	0.1 %
relative control precision of the output voltage load step of resistive load 50/100/50 % typical	2 %
relative control precision of the output voltage at load step of resistive load 10/90/10 % typical	3 %
setting time	
● load step 10 to 90% typical	5 ms
● load step 90 to 10% typical	5 ms
● maximum	5 ms
protection and monitoring	
design of the overvoltage protection	Additional control loop, limitation (closed loop control) at < 28.8 V
property of the output short-circuit proof	Yes
design of short-circuit protection	Electronic shutdown, automatic restart
response value current limitation	8.4 ... 9.6 A
● typical	9 A
safety	
galvanic isolation between input and output	Yes
galvanic isolation	Output voltage: SELV, ES1 (IEC 62368-1), DVC As (IEC 61204-7)
operating resource protection class	Class I
leakage current	
● maximum	3.5 mA
● typical	1.3 mA

© Copyright Siemens

protection class IP	IP20
EMC	
standard	
● for emitted interference	EN 55022 Class B
● for mains harmonics limitation	EN 61000-3-2
● for interference immunity	EN 61000-6-2
standards, specifications, approvals	
certificate of suitability	
● CE marking	Yes
● UL approval	Yes; cULus-Listed (UL 508, CSA C22.2 No. 142), File E143289
● UKCA marking	Yes
● EAC approval	Yes
● Regulatory Compliance Mark (RCM)	Yes
● NEC Class 2	No
type of certification	
● BIS	Yes; R-41183539
● CB-certificate	Yes
MTBF at 40 °C	1 362 918 h
standards, specifications, approvals hazardous environments	
certificate of suitability	
● IECEx	No
● ATEX	No
● ULhazloc approval	No
● UKEX	No
● CCC for hazardous zone according to GB standard	No
● FM registration	No
standards, specifications, approvals marine classification	
shipbuilding approval	Yes
Marine classification association	
● American Bureau of Shipping Europe Ltd. (ABS)	Yes
● French marine classification society (BV)	Yes
● Det Norske Veritas (DNV)	Yes
● Lloyds Register of Shipping (LRS)	No
standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
● total	589.1 kg
● during manufacturing	14 kg
● during operation	574.4 kg
● after end of life	0.51 kg
ambient conditions	
ambient temperature	
● during operation	0 ... 60 °C; with natural convection
● in horizontal mounting position during operation	0 ... 60 °C
● in vertical mounting position during operation	0 ... 40 °C
● during transport	-40 ... +85 °C
● during storage	-40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
connection method	
type of electrical connection	Screw-/spring clamp connection
● at input	L, N, PE: 1 screw terminal each for 0.5 ... 2.5 mm²
● at output	L+, M: 2 spring-loaded terminals each for 0.5 to 2.5 mm²
removable terminal at input	Yes
removable terminal at output	Yes
mechanical data	
width × height × depth of the enclosure	75 × 147 × 129 mm
installation width × mounting height	75 mm × 205 mm
required spacing	

Subject to change without notice
© Copyright Siemens

● top	40 mm
● bottom	40 mm
● left	0 mm
● right	0 mm
fastening method	Can be mounted onto S7-1500 rail
● DIN-rail mounting	No
● S7 rail mounting	Yes
● wall mounting	No
housing can be lined up	Yes
net weight	0.74 kg

further information internet links

internet link	
● to website: Industry Mall	https://mall.industry.siemens.com
● to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
● to web page: power supplies	https://siemens.com/sitop
● to website: CAx-Download-Manager	https://siemens.com/cax
● to website: Industry Online Support	https://support.industry.siemens.com
identification link	Yes; acc. to IEC 61406-1:2022

additional information

other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

security information

security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)

Classifications

	Version	Classification
eClass	16	27-04-07-01
eClass	14	27-04-07-01
eClass	12	27-04-07-01
eClass	9.1	27-04-07-01
eClass	9	27-04-07-01
eClass	8	27-04-90-02
eClass	7.1	27-04-90-02
eClass	6	27-04-90-02
ETIM	10	EC002540
ETIM	9	EC002540
ETIM	8	EC002540
ETIM	7	EC002540
IDEA	4	4130
UNSPSC	15	39-12-10-04

Approvals Certificates

Environmental Product Declaration	
● global warming potential [CO2 eq] / during manufacturing	14 kg
● global warming potential [CO2 eq] / during operation	574.4 kg

© Copyright Siemens

• global warming potential [CO2 eq] / after end of life	0.51 kg
• global warming potential [CO2 eq] / total	589.1 kg

Environment



General Product Approval





Manufacturer Declaration





General Product Approval

China RoHS

Declaration of Conformity



Miscellaneous

BIS CRS

For use in hazardous locations

Miscellaneous

For use in hazardous locations





FM

CCC-Ex



Maritime application



Maritime application





last modified: 8/29/2026

© Copyright Siemens