SIEMENS

Data sheet 6EP3344-7SB00-3AX0



SITOP PSU6200/1AC/48VDC/5A

SITOP PSU6200 48 V/5 A stabilized power supply input: 120 - 240 V AC (110-240 V DC) output: 48 V DC/5 A with diagnostic interface

General information	
Technical Product Detail Page	https://i.siemens.com/1P6EP3344-7SB00-3AX0
product brand name	SITOP
product type designation	PSU6200
product designation	Power supply SITOP PSU6200
type of current supply	48 V/5 A
input	
type of the power supply network	1-phase AC or DC
phase number	1
voltage curve at input	AC/DC
supply voltage at AC	
● minimum rated value	120 V
● maximum rated value	240 V
● initial value	85 V
● full-scale value	264 V
supply voltage at DC	110 ... 240 V
input voltage at DC	85 ... 275 V
supply voltage	
● at 50 Hz	240 V
● at 60 Hz	120 V
line frequency	50/60 Hz
line frequency	47 ... 63 Hz
wide range input	Yes
overvoltage overload capability	300 V AC for 30 s
buffering time for rated value of the output current in the event of power failure minimum	46 ms
operating condition of the mains buffering	at Vin = 240 V
input current	
● at rated input voltage 120 V	2.2 A
● at rated input voltage 240 V	1.2 A
current limitation of inrush current at 25 °C maximum	6 A
fuse protection type	5 A
fuse protection type in the feeder	Circuit breaker from 4 A characteristic C/6 A characteristic B to 10 A characteristic C or circuit breaker 3RV2011-1EA10 (setting 4 A) or 3RV2711-1ED10 (UL 489)
output	
voltage curve at output	Controlled, isolated DC voltage
product function output voltage controlled	Yes
product function output voltage stabilized	Yes
number of outputs	1

Subject to change without notice
© Copyright Siemens

output voltage at DC rated value	48 V
output voltage	
● at output 1 at DC rated value	48 V
output voltage	
● at output 1 at DC	48 V
output voltage adjustable	Yes; via potentiometer
adjustable output voltage	48 ... 56 V; max. 240 W (288 W up to 45°C)
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
● on slow fluctuation of input voltage	0.1 %
● on slow fluctuation of ohm loading	0.1 %
residual ripple	
● maximum	50 mV
● typical	30 mV
voltage peak	
● maximum	60 mV
● typical	40 mV
display version for normal operation	Green LED for 48 V OK
type of signal at output	Electronic contact (NO contact, contact rating 30 V DC/0.1 A) for DC O.K. or diagnostic interface
behavior of the output voltage when switching on	Overshoot of Vout < 2 %
response delay maximum	0.5 s
voltage increase time of the output voltage	
● typical	250 ms
output current	
● rated value	5 A
● rated range	0 ... 5 A; 6 A up to +45°C; +60 ... +70 °C: Derating 3%/K
supplied active power typical	240 W
short-term overload current	
● on short-circuiting during the start-up typical	6 A
● at short-circuit during operation typical	6 A
parallel switching of outputs	can be set with DIP switch
bridging of equipment	Yes; switchable characteristic
number of parallel-switched equipment resources for increasing the power	2
efficiency	
efficiency in percent	93.9 %
power loss [W]	
● at rated output voltage for rated value of the output current typical	15 W
● during no-load operation maximum	2.4 W
closed-loop control	
relative control precision of the output voltage at load step of resistive load 10/90/10 % typical	1 %
setting time	
● load step 10 to 90% typical	4 ms
● load step 90 to 10% typical	4 ms
● maximum	6 ms
protection and monitoring	
design of the overvoltage protection	< 60 V
property of the output short-circuit proof	Yes
design of short-circuit protection	Shutdown and periodic restart attempts
● typical	6 A
overcurrent overload capability	
● in normal operation	overload capability 150 % Iout rated up to 5 s/min
safety	
galvanic isolation between input and output	Yes
galvanic isolation	Output voltage: SELV, ES1 (IEC 62368-1), DVC As (IEC 61204-7)
operating resource protection class	Class I

Subject to change without notice
© Copyright Siemens

leakage current	
● maximum	3.5 mA
protection class IP	IP20
EMC	
standard	
● for emitted interference	EN 55022 Class B
● for mains harmonics limitation	EN 61000-3-2
● for interference immunity	EN 61000-6-2
standards, specifications, approvals	
certificate of suitability	
● CE marking	Yes
● UL approval	Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
● UKCA marking	Yes
● EAC approval	Yes
● Regulatory Compliance Mark (RCM)	Yes
● NEC Class 2	No
● SEMI F47	Yes
type of certification	
● BIS	Yes; R-41188271
● CB-certificate	Yes
standards, specifications, approvals hazardous environments	
certificate of suitability	
● IECEx	No
● ATEX	No
● ULhazloc approval	No
● FM registration	No
standards, specifications, approvals marine classification	
shipbuilding approval	Yes
Marine classification association	
● American Bureau of Shipping Europe Ltd. (ABS)	Yes
● French marine classification society (BV)	No
● Det Norske Veritas (DNV)	Yes
● Lloyds Register of Shipping (LRS)	No
standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
● total	403.2 kg
● during manufacturing	23.1 kg
● during operation	379.5 kg
● after end of life	0.38 kg
ambient conditions	
ambient temperature	
● during operation	-30 ... +70 °C; with natural convection a monotonically increasing start-up from -25 °C, safe start-up from -40 °C
● during transport	-40 ... +85 °C
● during storage	-40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
connection method	
type of electrical connection	push-in terminals
● at input	L1/+, L2/N/-, PE: push-in for 0.5 ... 4 mm² single-core/finely stranded
● at output	+1, +2, -1, -2, -3: push-in for 0.5 ... 2.5 mm²
● for auxiliary contacts	13, 14 (alarm signal): 1 push-in terminal each for 0.2 ... 1.5 mm²
mechanical data	
width × height × depth of the enclosure	45 × 135 × 125 mm
installation width × mounting height	45 mm × 225 mm
required spacing	
● top	45 mm
● bottom	45 mm
● left	0 mm

Subject to change without notice
© Copyright Siemens

● right	0 mm
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
● DIN-rail mounting	Yes
● S7 rail mounting	No
● wall mounting	No
housing can be lined up	Yes
net weight	0.9 kg
accessories	
electrical accessories	Buffer module, redundancy module
mechanical accessories	Identification labels SIMATIC ET 200SP 6ES7193-6LF30-0AW0
further information internet links	
internet link	
● to website: Industry Mall	https://mall.industry.siemens.com
● to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
● to web page: power supplies	https://siemens.com/sitop
● to website: CAx-Download-Manager	https://siemens.com/cax
● to website: Industry Online Support	https://support.industry.siemens.com
identification link	Yes; acc. to IEC 61406-1:2022
additional information	
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)

Classifications

	Version	Classification
eClass	16	27-04-07-01
eClass	14	27-04-07-01
eClass	12	27-04-07-01
eClass	9.1	27-04-07-01
eClass	9	27-04-07-01
eClass	8	27-04-90-02
eClass	7.1	27-04-90-02
eClass	6	27-04-90-02
ETIM	10	EC002540
ETIM	9	EC002540
ETIM	8	EC002540
ETIM	7	EC002540
IDEA	4	4130
UNSPSC	15	39-12-10-04

Approvals Certificates

Environmental Product Declaration	
● global warming potential [CO2 eq] / during manufacturing	23.1 kg
● global warming potential [CO2 eq] / during operation	379.5 kg

Subject to change without notice
© Copyright Siemens

• global warming potential [CO2 eq] / after end of life	0.38 kg
• global warming potential [CO2 eq] / total	403.2 kg

Environment

General Product Approval

Manufacturer Declaration

Declaration of Conformity

General Product Approval

Maritime application

China RoHS

BIS CRS

Maritime application

last modified: 8/29/2026

Subject to change without notice
© Copyright Siemens