



AS-i compact module K20 digital A/B slave, 4 DI, IP67 2 x 2 inputs, maximum 200 mA 2 x M12 sockets with Y assignment

General technical data	
design of the product	digital I/O modules for operation in the field, IP67 - K20
Type	4 inputs
design of the slave type	A/B slave
I/O configuration	0
ID/ID2 code	A/2
Number I/O sockets	2
type of electrical connection of the inputs and outputs	M12 screw-type terminals
AS interface total current input max	270 mA
operating voltage according to AS-Interface specification	26.5 ... 31.6 V
Ground terminal	not available
Addressing	using M12 female connector
AS interface Connection Polarity reversal protection	built-in
Sensor supply	
type of voltage supply for sensor supply	using AS-Interface
input voltage	16.5 ... 30 V
property of the sensor supply short-circuit and overload resistant	Yes
ampacity of the sensor supply for all inputs	
• at ambient temperature 40 °C	200 mA
• at ambient temperature 55 °C	150 mA
Inputs	
number of digital inputs	4
type of connection technology	2- and 3-wire technology
Input circuit	PNP transistor
type of voltage of the input voltages	DC
Inputs switching level High min	10 V
input current at digital input	
• for signal <1> minimum	6 mA
• with signal <0> maximum	1.5 mA
Inputs sensor supply using AS-Interface	short-circuit and overload resistant
Inputs socket assignment	
• PIN 1	sensor supply L+
• PIN 2	data input
• PIN 3	sensor supply L-
• PIN 4	data input
design of the pin assignment of the inputs	Y assignment
Outputs	
number of digital outputs	0
Display	

Status display	
• display of I/Os	yellow LED
• display of Uaux	not required
• display of AS-Interface/diagnostics	green/red dual LED

Assignment of the data bits

Assignment of data bits	
• socket	PIN 4 = IN1 (D0), PIN 2 = IN2 (D1)
• socket 2	PIN 4 = IN3 (D2), PIN 2 = IN4 (D3)
• socket 3	not available
• socket 4	not available

Ambient conditions

ambient temperature	
• during operation	-25 ... +70 °C
• during storage	-40 ... +85 °C
protection class IP	IP67

Mechanical data

width	20 mm
height	108 mm
depth	45 mm
fastening method	no mounting plate required
shock resistance	15g / 11 ms

Certificates/ approvals

General Product Approval	EMV
---------------------------------	-----



[KC](#)

Test Certificates	Maritime application	other
--------------------------	-----------------------------	--------------

[Special Test Certificate](#)



[Confirmation](#)

other	Environment	Industrial Communication
--------------	--------------------	---------------------------------

[Miscellaneous](#)

[Environmental Conformations](#)



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK2200-0CQ30-0AA3>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK2200-0CQ30-0AA3>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RK2200-0CQ30-0AA3>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK2200-0CQ30-0AA3&lang=en



last modified:

4/1/2025 