SIEMENS

Data sheet 3RP2535-2AW30



Timing relay, OFF delay with control signal 1 change-over contact, 15 time ranges 0.05 s...100 h 12-240 V DC, Wide voltage range at 50/60 Hz AC with LED, Spring-type terminal (push-in)

product brand name	SIRIUS
product designation	timing relay
design of the product	OFF delay with control signal
product type designation	3RP25
General technical data	
product feature protective coating on printed-circuit board	No
product component	
● relay output	Yes
● semi-conductor output	No
product extension required remote control	No
product extension optional remote control	No
power loss [W] maximum	2 W
insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 rated value	300 V
test voltage for isolation test	2.5 kV
degree of pollution	3
surge voltage resistance rated value	4 000 V
shock resistance according to IEC 60068-2-27	11 g / 15 ms
vibration resistance according to IEC 60068-2-6	10 ... 55 Hz / 0.35 mm
mechanical service life (operating cycles) typical	10 000 000
electrical endurance (operating cycles) at AC-15 at 230 V typical	100 000
adjustable time	0.05 s ... 100 h
relative setting accuracy relating to full-scale value	5 %; +/-
thermal current	5 A
ON period/maximum minimum	35 ms
recovery time	250 ms
reference code according to IEC 81346-2	K
relative repeat accuracy	1 %; +/-
influence of the surrounding temperature	1% in the whole temperature range to the set runtime
power supply influence	1% in the whole voltage range to the set runtime
Substance Prohibitance (day/month/year)	09/12/2014
SVHC substance name	2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5 Melamine CAS-No. 108-78-1 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol CAS-No. 119-47-1
Net Weight	0.104 kg
Control circuit/ Control	
type of voltage of the control supply voltage	AC/DC
control supply voltage at AC	
● at 50 Hz rated value	12 ... 240 V

Subject to change without notice
© Copyright Siemens

● at 60 Hz rated value	12 ... 240 V
control supply voltage 1 at AC	
● at 50 Hz	12 ... 240 V
● at 60 Hz	12 ... 240 V
control supply voltage frequency 1	50 ... 60 Hz
control supply voltage at DC rated value	12 ... 240 V
control supply voltage 1 at DC	12 ... 240 V
operating range factor control supply voltage rated value at DC	
● initial value	0.8
● full-scale value	1.1
operating range factor control supply voltage rated value at AC at 50 Hz	
● initial value	0.85
● full-scale value	1.1
operating range factor control supply voltage rated value at AC at 60 Hz	
● initial value	0.8
● full-scale value	1.1
inrush current peak	
● at 24 V	0.4 A
● at 240 V	5 A
duration of inrush current peak	
● at 24 V	0.3 ms
● at 240 V	0.5 ms
Switching Function	
switching function	
● ON-delay	No
● ON-delay/instantaneous contact	No
● passing make contact	No
● passing make contact/instantaneous contact	No
● OFF delay	No
switching function	
● flashing symmetrically with interval start/instantaneous	No
● flashing symmetrically with interval start	No
● flashing symmetrically with pulse start/instantaneous	No
● flashing symmetrically with pulse start	No
● flashing asymmetrically with interval start	No
● flashing asymmetrically with pulse start	No
switching function	
● star-delta circuit with delay time	No
● star-delta circuit	No
switching function with control signal	
● additive ON-delay	No
● passing break contact	No
● passing break contact/instantaneous	No
● OFF delay	Yes
● OFF delay/instantaneous	No
● pulse delayed	No
● pulse delayed/instantaneous	No
● pulse-shaping	No
● pulse-shaping/instantaneous	No
● additive ON-delay/instantaneous	No
● ON-delay/OFF-delay/instantaneous	No
● passing make contact	No
● passing make contact/instantaneous contact	No
switching function of interval relay with control signal	
● retrotriggerable with deactivated control signal/instantaneous contact	No
● retrotriggerable with switched-on control signal	No

© Copyright Siemens

● retrotriggerable with switched-on control signal/instantaneous contact	No
● retriggerable with deactivated control signal	No
design of the control terminal non-floating	Yes
Short-circuit protection	
design of the fuse link for short-circuit protection of the auxiliary switch required	fuse gL/gG: 4 A
Auxiliary circuit	
material of switching contacts	AgSnO2
number of NC contacts	
● delayed switching	0
● instantaneous contact	0
number of NO contacts	
● delayed switching	0
● instantaneous contact	0
number of CO contacts	
● delayed switching	1
● instantaneous contact	0
operational current of auxiliary contacts at AC-15	
● at 24 V	3 A
● at 250 V	3 A
operational current of auxiliary contacts at DC-13	
● at 24 V	1 A
● at 125 V	0.2 A
● at 250 V	0.1 A
operating frequency with 3RT2 contactor maximum	5 000 1/h
contact reliability of auxiliary contacts	one incorrect switching operation of 100 million switching operations (17 V, 5 mA)
contact rating of auxiliary contacts according to UL	R300 / B300
switching capacity current with inductive load	0.01 ... 3 A
Inputs/ Outputs	
product function	
● at the relay outputs switchover delayed/without delay	No
● non-volatile	No
ampacity of the output relay at DC-13	
● at 24 V	1 A
● at 125 V	0.2 A
Electromagnetic compatibility	
EMC emitted interference according to IEC 61812-1	ambience A (industrial sector)
EMC immunity according to IEC 61812-1	corresponds to degree of severity 3
conducted interference	
● due to burst according to IEC 61000-4-4	2 kV network connection / 1 kV control connection
● due to conductor-earth surge according to IEC 61000-4-5	2 kV
● due to conductor-conductor surge according to IEC 61000-4-5	1 kV
field-based interference according to IEC 61000-4-3	10 V/m
electrostatic discharge according to IEC 61000-4-2	4 kV contact discharge / 8 kV air discharge
Safety related data	
category according to EN 954-1	none
Electrical Safety	
protection class IP on the front according to IEC 60529	IP20
type of insulation	Basic insulation
Connections/ Terminals	
product component removable terminal for auxiliary and control circuit	Yes
type of electrical connection	spring-loaded terminal (push-in)
● for auxiliary and control circuit	spring-loaded terminals (push-in)
type of connectable conductor cross-sections	
● solid	1x (0.5 ... 4 mm²)
● finely stranded with core end processing	1x (0.5 ... 2.5 mm²)

Subject to change without notice
© Copyright Siemens

● finely stranded without core end processing	0.5 ... 4 mm²
● for AWG cables solid	1x (20 ... 12)
● for AWG cables stranded	20 ... 12
connectable conductor cross-section	
● solid	0.5 ... 4 mm²
● finely stranded with core end processing	0.5 ... 2.5 mm²
● finely stranded without core end processing	0.5 ... 4 mm²
AWG number as coded connectable conductor cross section	
● solid	20 ... 12
● stranded	20 ... 12

Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw and snap-on mounting onto 35 mm DIN rail
height	100 mm
width	17.5 mm
depth	90 mm
required spacing	
● with side-by-side mounting	
— forwards	0 mm
— backwards	0 mm
— upwards	0 mm
— downwards	0 mm
— at the side	0 mm
● for grounded parts	
— forwards	0 mm
— backwards	0 mm
— upwards	0 mm
— at the side	0 mm
— downwards	0 mm
● for live parts	
— forwards	0 mm
— backwards	0 mm
— upwards	0 mm
— downwards	0 mm
— at the side	0 mm

Ambient conditions	
installation altitude at height above sea level maximum	2 000 m
ambient temperature	
● during operation	-25 ... +60 °C
● during storage	-40 ... +85 °C
● during transport	-40 ... +85 °C
relative humidity during operation	10 ... 95 %

Approvals Certificates

Environment	General Product Approval

Environmental Confirmations

EMV	Test Certificates	Maritime application

Type Test Certificates/Test Report


Maritime application	other

Subject to change without notice
© Copyright Siemens


Confirmation

Further information

Information on the packaging
https://support.industry.siemens.com/cs/ww/en/view/109813875
Information for data generation and storage
https://support.industry.siemens.com/cs/ww/en/view/109995012
Information- and Downloadcenter (Catalogs, Brochures,…)
https://www.siemens.com/ic10
Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RP2535-2AW30
Cax online generator
https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RP2535-2AW30
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
https://support.industry.siemens.com/cs/ww/en/ps/3RP2535-2AW30
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RP2535-2AW30&lang=en



© Copyright Siemens



last modified: 5/29/2026

© Copyright Siemens