



Figure similar

SITOP PSU6200/1AC/24VDC/5A/EX

SITOP PSU6200 Ex 24 V/5 A stabilized power supply input: 120 - 240 V AC
output: 24 V DC/5 A with coated printed circuit boards

General information

Technical Product Detail Page	https://i.siemens.com/1P6EP3333-7SC00-0AX0
product brand name	SITOP
product type designation	PSU6200
product designation	Power supply SITOP PSU6200
type of current supply	24 V/5 A

input

type of the power supply network	1-phase AC or DC
phase number	1
voltage curve at input	AC/DC
supply voltage at AC	
• minimum rated value	120 V
• maximum rated value	240 V
• initial value	85 V
• full-scale value	264 V
supply voltage at DC	120 ... 240 V
input voltage at DC	99 ... 275 V
supply voltage	
• at 50 Hz	240 V
• at 60 Hz	120 V
line frequency	50/60 Hz
line frequency	47 ... 63 Hz
wide range input	Yes
overvoltage overload capability	300 V AC for 30 s
buffering time for rated value of the output current in the event of power failure minimum	80 ms
operating condition of the mains buffering	at $V_{in} = 240\text{ V}$
input current	
• at rated input voltage 120 V	1.9 A
• at rated input voltage 240 V	1.1 A
current limitation of inrush current at 25 °C maximum	29 A
fuse protection type	3.15 A
fuse protection type in the feeder	Circuit breaker 4 A characteristic C or 6 A characteristic B/C or circuit breaker 3RV2011-1EA10 (setting 4 A) or 3RV2711-1ED10 (UL 489)

output

voltage curve at output	Controlled, isolated DC voltage
product function output voltage controlled	Yes
product function output voltage stabilized	Yes
number of outputs	1

output voltage at DC rated value	24 V
output voltage	
• at output 1 at DC rated value	24 V
output voltage	
• at output 1 at DC	24 V
output voltage adjustable	Yes; via potentiometer
adjustable output voltage	24 ... 28 V; max. 120 W (144 W up to 45°C)
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.1 %
• on slow fluctuation of ohm loading	0.2 %
residual ripple	
• maximum	30 mV
• typical	20 mV
voltage peak	
• maximum	100 mV
• typical	60 mV
display version for normal operation	Green LED for 24 V OK
type of signal at output	Electronic contact (NO contact, contact rating 30 V DC/0.1 A) for DC O.K.
behavior of the output voltage when switching on	Overshoot of $V_{out} < 2 \%$
response delay maximum	0.5 s
voltage increase time of the output voltage	
• typical	100 ms
output current	
• rated value	5 A
• rated range	0 ... 5 A; 6 A up to +45°C; +60 ... +70 °C: Derating 3%/K
supplied active power typical	120 W
short-term overload current	
• on short-circuiting during the start-up typical	6 A
• at short-circuit during operation typical	6 A
bridging of equipment	No
efficiency	
efficiency in percent	90.2 %
power loss [W]	
• at rated output voltage for rated value of the output current typical	13 W
• during no-load operation maximum	2 W
closed-loop control	
relative control precision of the output voltage at load step of resistive load 10/90/10 % typical	2 %
setting time	
• load step 10 to 90% typical	1 ms
• load step 90 to 10% typical	1 ms
• maximum	2 ms
protection and monitoring	
design of the overvoltage protection	< 32 V
property of the output short-circuit proof	Yes
design of short-circuit protection	Shutdown and periodic restart attempts
• typical	6 A
overcurrent overload capability	
• in normal operation	overload capability 150 % I_{out} rated up to 5 s/min
safety	
galvanic isolation between input and output	Yes
galvanic isolation	Output voltage: SELV, ES1 (IEC 62368-1), DVC As (IEC 61204-7)
operating resource protection class	Class I
leakage current	
• maximum	3.5 mA
protection class IP	IP20
EMC	

standard	
• for emitted interference	EN 55022 Class B
• for mains harmonics limitation	EN 61000-3-2
• for interference immunity	EN 61000-6-2
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• UL approval	Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
• UKCA marking	Yes
• EAC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
• NEC Class 2	No
• SEMI F47	Yes
type of certification	
• BIS	Yes; R-41188271
• CB-certificate	Yes
standards, specifications, approvals hazardous environments	
certificate of suitability	
• IECEx	Yes; IECEx Ex ec IIC T3 Gc
• ATEX	Yes; ATEX (EX) II 3G Ex ec IIC T3 Gc
• ULhazloc approval	Yes
• UKEX	Yes
• CCC for hazardous zone according to GB standard	Yes
• FM registration	No
standards, specifications, approvals marine classification	
shipbuilding approval	Yes
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• French marine classification society (BV)	No
• Det Norske Veritas (DNV)	Yes
• Lloyds Register of Shipping (LRS)	No
standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO ₂ eq]	
• total	347.3 kg
• during manufacturing	18 kg
• during operation	328.8 kg
• after end of life	0.3 kg
ambient conditions	
ambient temperature	
• during operation	-30 ... +70 °C; with natural convection a monotonically increasing start-up from -25 °C, safe start-up from -40 °C
• during transport	-40 ... +85 °C
• during storage	-40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
connection method	
type of electrical connection	push-in terminals
• at input	L1/+, L2/N/-, PE: push-in for 0.5 ... 4 mm ² single-core/finely stranded
• at output	+1, +2, -1, -2, -3: push-in for 0.5 ... 2.5 mm ²
• for auxiliary contacts	13, 14 (alarm signal): 1 push-in terminal each for 0.2 ... 1.5 mm ²
mechanical data	
width × height × depth of the enclosure	35 × 135 × 125 mm
installation width × mounting height	35 mm × 225 mm
required spacing	
• top	45 mm
• bottom	45 mm
• left	0 mm
• right	0 mm
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15

• DIN-rail mounting	Yes
• S7 rail mounting	No
• wall mounting	No
housing can be lined up	Yes
net weight	0.7 kg
accessories	
electrical accessories	Buffer module, redundancy module
mechanical accessories	Identification labels SIMATIC ET 200SP 6ES7193-6LF30-0AW0
further information internet links	
internet link	
• to website: Industry Mall	https://mall.industry.siemens.com
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
• to web page: power supplies	https://siemens.com/sitop
• to website: CAX-Download-Manager	https://siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
identification link	Yes; acc. to IEC 61406-1:2022
additional information	
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert . (V4.7)

Classifications

	Version	Classification
eClass	16	27-04-07-01
eClass	14	27-04-07-01
eClass	12	27-04-07-01
eClass	9.1	27-04-07-01
eClass	9	27-04-07-01
eClass	8	27-04-90-02
eClass	7.1	27-04-90-02
eClass	6	27-04-90-02
ETIM	10	EC002540
ETIM	9	EC002540
ETIM	8	EC002540
ETIM	7	EC002540
IDEA	4	4130
UNSPSC	15	39-12-10-04

Approvals Certificates

Environmental Product Declaration	
• global warming potential [CO2 eq] / during manufacturing	18 kg
• global warming potential [CO2 eq] / during operation	328.8 kg
• global warming potential [CO2 eq] / after end of life	0.3 kg
• global warming potential [CO2 eq] / total	347.3 kg

Environment	General Product Approval
-------------	--------------------------



[Manufacturer Declaration](#)



EG-Konf.

[China RoHS](#)



UL

General Product Approval	For use in hazardous locations
--------------------------	--------------------------------



RCM

[BIS CRS](#)



IECEX

[Miscellaneous](#)



ATEX

[CCC-Ex](#)

For use in hazardous locations	Maritime application
--------------------------------	----------------------



UL



ABS



DNV

last modified: 5/5/2026