SIEMENS

Data sheet 7PV1512-1AP30



Timing relay, electronic ON delay 1 change-over contact, 1 time range 0.5...10 s 24/230 V AC and 24 V DC with LED, Screw terminal

product brand name	SIRIUS
product designation	timing relay
design of the product	slow-operating
product type designation	7PV15
General technical data	
product component semi-conductor output	No
product extension required remote control	No
product extension optional remote control	No
power loss [W] maximum	2 W
insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 rated value	300 V
test voltage for isolation test	2.2 kV
degree of pollution	2
surge voltage resistance rated value	4 000 V
test voltage for surge voltage test	4 800 V
shock resistance according to IEC 60068-2-27	11 g / 15 ms
vibration resistance according to IEC 60068-2-6	10 ... 55 Hz: 0.35 mm
mechanical service life (operating cycles) typical	10 000 000
electrical endurance (operating cycles) at AC-15 at 230 V typical	100 000
adjustable time	0.5 ... 10 s
relative setting accuracy relating to full-scale value	5 %; +/-
ON period/maximum minimum	35 ms
recovery time	500 ms
reference code according to IEC 81346-2	K
relative repeat accuracy	2 %; +/-
influence of the surrounding temperature	2% in complete temperature range for the set duration
power supply influence	2% in complete voltage range for the set duration
Substance Prohibitance (day/month/year)	05/01/2012
SVHC substance name	Lead CAS-No. 7439-92-1 Lead monoxide (lead oxide) CAS-No. 1317-36-8 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5 Melamine CAS-No. 108-78-1 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol CAS-No. 119-47-1
Net Weight	0.065 kg
Control circuit/ Control	
type of voltage of the control supply voltage	AC/DC
control supply voltage at AC	
● at 50 Hz rated value	200 ... 240 V
● at 60 Hz rated value	200 ... 240 V
control supply voltage 1 at AC	

Subject to change without notice
© Copyright Siemens

● at 50 Hz	200 ... 240 V
● at 60 Hz	200 ... 240 V
control supply voltage 2 at AC	
● at 50 Hz rated value	24 V
● at 60 Hz rated value	24 V
control supply voltage frequency 1	50 ... 60 Hz
control supply voltage at DC rated value	24 V
control supply voltage 1 at DC rated value	24 V
operating range factor control supply voltage rated value at DC	
● initial value	0.85
● full-scale value	1.1
operating range factor control supply voltage rated value at AC at 50 Hz	
● initial value	0.85
● full-scale value	1.1
operating range factor control supply voltage rated value at AC at 60 Hz	
● initial value	0.85
● full-scale value	1.1
Switching Function	
switching function	
● ON-delay	Yes
● ON-delay/instantaneous contact	No
● passing make contact	No
● passing make contact/instantaneous contact	No
● OFF delay	No
switching function	
● flashing symmetrically with interval start/instantaneous	No
● flashing symmetrically with interval start	No
● flashing symmetrically with pulse start/instantaneous	No
● flashing symmetrically with pulse start	No
● flashing asymmetrically with interval start	No
● flashing asymmetrically with pulse start	No
switching function	
● star-delta circuit with delay time	No
● star-delta circuit	No
switching function with control signal	
● additive ON-delay	No
● passing break contact	No
● passing break contact/instantaneous	No
● OFF delay	No
● OFF delay/instantaneous	No
● pulse delayed	No
● pulse delayed/instantaneous	No
● pulse-shaping	No
● pulse-shaping/instantaneous	No
● additive ON-delay/instantaneous	No
● ON-delay/OFF-delay	No
● ON-delay/OFF-delay/instantaneous	No
● passing make contact	No
● passing make contact/instantaneous contact	No
switching function of interval relay with control signal	
● retrotriggerable with deactivated control signal/instantaneous contact	No
● retrotriggerable with switched-on control signal	No
● retrotriggerable with switched-on control signal/instantaneous contact	No
● retriggerable with deactivated control signal	No
design of the control terminal non-floating	No

© Copyright Siemens

Short-circuit protection	
design of the fuse link for short-circuit protection of the auxiliary switch required	fuse gL/gG: 4 A
Auxiliary circuit	
material of switching contacts	AgSnO2
number of NC contacts	
● delayed switching	0
● instantaneous contact	0
number of NO contacts	
● delayed switching	0
● instantaneous contact	0
number of CO contacts	
● delayed switching	1
● instantaneous contact	0
operational current of auxiliary contacts at AC-15	
● maximum	3 A
● at 24 V	3 A
● at 250 V	3 A
operational current of auxiliary contacts as NC contact at AC-15	
● at 24 V	3 A
● at 250 V	3 A
operational current of auxiliary contacts as NO contact at AC-15	
● at 24 V	3 A
● at 250 V	3 A
operational current of auxiliary contacts at DC-13	1 ... 0.01
operational current of auxiliary contacts at DC-13	
● at 24 V	1 A
● at 125 V	0.22 A
● at 250 V	0.1 A
operating frequency with 3RT2 contactor maximum	5 000 1/h
contact reliability of auxiliary contacts	one incorrect switching operation of 100 million switching operations (17 V, 5 mA)
contact rating of auxiliary contacts according to UL	R150 / B300
switching capacity current with inductive load	0.01 ... 3 A
Inputs/ Outputs	
product function	
● at the relay outputs switchover delayed/without delay	No
● non-volatile	No
ampacity of the output relay at AC-15 at 250 V at 50/60 Hz	3 A
ampacity of the output relay at DC-13	
● at 24 V	1 A
● at 125 V	0.22 A
Electromagnetic compatibility	
EMC immunity according to IEC 61812-1	EN 61000-6-2
conducted interference	
● due to burst according to IEC 61000-4-4	2 kV network connection / 1 kV control connection
● due to conductor-earth surge according to IEC 61000-4-5	2 kV
● due to conductor-conductor surge according to IEC 61000-4-5	1 kV
field-based interference according to IEC 61000-4-3	10 V/m
electrostatic discharge according to IEC 61000-4-2	4 kV contact discharge / 8 kV air discharge
Safety related data	
category according to EN 954-1	none
Electrical Safety	
protection class IP on the front according to IEC 60529	IP20
type of insulation	Basic insulation
Connections/ Terminals	
product component removable terminal for auxiliary and	No

© Copyright Siemens

control circuit	
type of electrical connection	screw terminal
● for auxiliary and control circuit	screw-type terminals
type of connectable conductor cross-sections	
● solid	1x (0.2 ... 2.5 mm²)
● finely stranded with core end processing	1x (0.25 ... 1.5 mm²)
● finely stranded without core end processing	1x (0.2 ... 1.5 mm²)
● for AWG cables solid	1x (24 ... 14)
● for AWG cables stranded	1x (24 ... 14)
connectable conductor cross-section	
● solid	0.2 ... 2.5 m²
● finely stranded with core end processing	0.25 ... 1.5 m²
● finely stranded without core end processing	0.2 ... 1.5 m²
AWG number as coded connectable conductor cross section	
● solid	24 ... 14
● stranded	24 ... 14
Installation/ mounting/ dimensions	
mounting position	any
fastening method	snap-on fastening on 35 mm DIN rail
height	90 mm
width	17.5 mm
depth	66.7 mm
required spacing	
● with side-by-side mounting	
— forwards	0 mm
— backwards	0 mm
— upwards	0 mm
— downwards	0 mm
— at the side	0 mm
● for grounded parts	
— forwards	0 mm
— backwards	0 mm
— upwards	0 mm
— at the side	0 mm
— downwards	0 mm
● for live parts	
— forwards	0 mm
— backwards	0 mm
— upwards	0 mm
— downwards	0 mm
— at the side	0 mm
Ambient conditions	
installation altitude at height above sea level maximum	2 000 m
ambient temperature	
● during operation	-25 ... +55 °C
● during storage	-40 ... +70 °C
● during transport	-40 ... +70 °C
relative humidity during operation	15 ... 85 %
Approvals Certificates	
Environmental Product Declaration	
● global warming potential [CO2 eq] / during manufacturing	1.34 kg
● global warming potential [CO2 eq] / during operation	21.2 kg
● global warming potential [CO2 eq] / after end of life	-0.156 kg
● global warming potential [CO2 eq] / total	22.4 kg
Environment	**General Product Approval**


© Copyright Siemens

Environmental Confirmations

General Product Approval	EMV	Test Certificates	other
		Type Test Certificates/Test Report	Confirmation


Further information

Information on the packaging
https://support.industry.siemens.com/cs/ww/en/view/109813875
Information for data generation and storage
https://support.industry.siemens.com/cs/ww/en/view/109995012
Information- and Downloadcenter (Catalogs, Brochures,…)
https://www.siemens.com/ic10
Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=7PV1512-1AP30
Cax online generator
https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=7PV1512-1AP30
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
https://support.industry.siemens.com/cs/ww/en/ps/7PV1512-1AP30
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=7PV1512-1AP30&lang=en



Alle Bemassungswerte sind in Millimeter (mm) angegeben
All dimensions are in millimeters (mm)

Subject to change without notice
© Copyright Siemens



last modified: 6/1/2026

Subject to change without notice
© Copyright Siemens