

Siemens
EcoTech



Illuminated mushroom pushbutton, 22 mm, round, metal, shiny, green, 40 mm, latching, pull-to-unlatch mechanism, with laser labeling, inscription or symbol
Customer-specific selection with SIRIUS ACT configurator (CIN)



product brand name	SIRIUS ACT
product designation	Mushroom pushbuttons
design of the product	Actuating/signaling element
product type designation	3SU1
product line	Metal, shiny, 22 mm
Enclosure	
number of command points	1
Actuator	
design of the actuating element	illuminated
principle of operation of the actuating element	latching
product extension optional light source	Yes
color of the actuating element	green
material of the actuating element	plastic
shape of the actuating element	round
outer diameter of the actuating element	40 mm
marking of the actuating element	Customized labeling, text or symbols, can only be ordered via SIRIUS ACT configurator/Configuration Identification Number (CIN)
type of unlocking device	pull-to-unlatch mechanism
number of switching positions	2
Front ring	
product component front ring	Yes
design of the front ring	Standard
material of the front ring	Metal, high gloss
color of the front ring	silver
General technical data	
product function	
• EMERGENCY OFF function	No
• EMERGENCY STOP function	No
protection class IP	IP66, IP67, IP69(IP69K)
degree of protection NEMA rating	1, 2, 3, 3R, 4, 4X, 12, 13
shock resistance	
• according to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
vibration resistance	
• according to IEC 60068-2-6	10 ... 500 Hz: 5g
operating frequency maximum	1 800 1/h
mechanical service life (operating cycles) typical	500 000
reference code according to IEC 81346-2	S

Substance Prohibittance (Date)		10/01/2014
Weight		0.067 kg
Ambient conditions		
ambient temperature		
• during operation		-25 ... +70 °C
• during storage		-40 ... +80 °C
environmental category during operation according to IEC 60721		3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%)
Environmental footprint		
Environmental Product Declaration (EPD)		Yes
global warming potential [CO2 eq] total		0.593 kg
global warming potential [CO2 eq] during manufacturing		0.625 kg
global warming potential [CO2 eq] during operation		0.235 kg
global warming potential [CO2 eq] after end of life		-0.267 kg
Siemens Eco Profile (SEP)		Siemens EcoTech
Installation/ mounting/ dimensions		
height		40 mm
width		40 mm
shape of the installation opening		round
mounting diameter		22.3 mm
positive tolerance of installation diameter		0.4 mm
mounting height		27.5 mm
installation width		40 mm
installation depth		24.4 mm
Approvals Certificates		
General Product Approval		Test Certificates
 EG-Konf.		  US
		Type Test Certificates/Test Report Special Test Certificate
Maritime application		other
 LRS		 PRS
 RINA		Confirmation
		
Environment		
		Environmental Confirmations
Further information		
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875		
Information for data generation and storage https://support.industry.siemens.com/cs/ww/en/view/109995012		
Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10		
Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1051-1BA40-0AA0-Z Y19		
Cax online generator http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1051-1BA40-0AA0-Z Y19		
Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3SU1051-1BA40-0AA0-Z Y19		
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1051-1BA40-0AA0-Z Y19&lang=en		

