



Enclosure for command devices, 22 mm, round, Enclosure material metal, enclosure top part gray, 1 control point metal, A=Pushbutton green, 1 NO, screw terminal, floor mounting, label: I, 1xM20 each on top and bottom, Label enclosed

|                                                       |                                    |
|-------------------------------------------------------|------------------------------------|
| product brand name                                    | SIRIUS ACT                         |
| product designation                                   | Enclosures                         |
| product type designation                              | 3SU1                               |
| equipment of commanding and signaling device          | A = Pushbutton                     |
| manufacturer's article number                         |                                    |
| • of supplied contact module at the command point A 2 | <a href="#">3SU1400-2AA10-1BA0</a> |
| • of the supplied holder at the command point A       | <a href="#">3SU1550-0AA10-0AA0</a> |
| • of the supplied actuator at the command point A     | <a href="#">3SU1050-0AB40-0AA0</a> |
| • of supplied empty enclosure                         | <a href="#">3SU1851-0AA00-0AB1</a> |
| • of the supplied accessories at the command point A  | <a href="#">3SU1900-0AF16-0QB0</a> |
| Enclosure                                             |                                    |
| design of the housing                                 | with recess for label              |
| shape of the enclosure front                          | Square                             |
| material of the enclosure                             | metal                              |
| number of command points                              | 1                                  |
| product component                                     |                                    |
| • EMERGENCY STOP device                               | No                                 |
| • protective collar                                   | No                                 |
| color of the enclosure top part                       | grey                               |
| delivery state                                        |                                    |
| • as a kit                                            | No                                 |
| • pre-wired on strip terminal                         | No                                 |
| fastening method of the enclosure                     | Vertical                           |
| Actuator                                              |                                    |
| design of the actuating element                       | Pushbutton                         |
| suitability for use EMERGENCY OFF switch              | No                                 |
| product feature lockout                               | No                                 |
| product extension optional light source               | No                                 |
| color of the actuating element                        | green                              |
| material of the actuating element                     | plastic                            |
| shape of the actuating element                        | round                              |
| number of contact modules                             | 1                                  |
| Front ring                                            |                                    |
| product component front ring                          | Yes                                |
| design of the front ring                              | Standard                           |
| material of the front ring                            | Metal, high gloss                  |
| color of the front ring                               | silver                             |
| Holder                                                |                                    |
| material of the holder                                | Plastic                            |
| Display                                               |                                    |

|                                                                |                                                                                                                                               |
|----------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| number of LED modules                                          | 0                                                                                                                                             |
| <b>General technical data</b>                                  |                                                                                                                                               |
| product function                                               |                                                                                                                                               |
| • positive opening                                             | No                                                                                                                                            |
| • EMERGENCY OFF function                                       | No                                                                                                                                            |
| • EMERGENCY STOP function                                      | No                                                                                                                                            |
| protection class IP                                            | IP66, IP67, IP69(IP69K)                                                                                                                       |
| degree of protection NEMA rating                               | 1, 2, 3, 3R, 4, 4X, 12, 13                                                                                                                    |
| shock resistance                                               |                                                                                                                                               |
| • according to IEC 60068-2-27                                  | sinusoidal half-wave 15g / 11 ms                                                                                                              |
| • for railway applications according to EN 61373               | Category 1, Class B                                                                                                                           |
| vibration resistance                                           |                                                                                                                                               |
| • according to IEC 60068-2-6                                   | 10 ... 500 Hz: 5g                                                                                                                             |
| • for railway applications according to EN 61373               | Category 1, Class B                                                                                                                           |
| reference code according to IEC 81346-2                        | S                                                                                                                                             |
| continuous current of the C characteristic MCB                 | 10 A; for a short-circuit current smaller than 400 A                                                                                          |
| continuous current of the quick DIAZED fuse link               | 10 A                                                                                                                                          |
| continuous current of the DIAZED fuse link gG                  | 10 A                                                                                                                                          |
| Substance Prohibitance (Date)                                  | 10/01/2014                                                                                                                                    |
| SVHC substance name                                            | Lead - 7439-92-1                                                                                                                              |
| Weight                                                         | 540 g                                                                                                                                         |
| operating voltage                                              |                                                                                                                                               |
| • at AC                                                        |                                                                                                                                               |
| — at 50 Hz rated value                                         | 5 ... 500 V                                                                                                                                   |
| — at 60 Hz rated value                                         | 5 ... 500 V                                                                                                                                   |
| • at DC rated value                                            | 5 ... 500 V                                                                                                                                   |
| <b>Communication/ Protocol</b>                                 |                                                                                                                                               |
| design of the interface for communication                      | without                                                                                                                                       |
| <b>Auxiliary circuit</b>                                       |                                                                                                                                               |
| design of the contact of auxiliary contacts                    | Silver alloy                                                                                                                                  |
| number of NC contacts for auxiliary contacts                   | 0                                                                                                                                             |
| number of NO contacts for auxiliary contacts                   | 1                                                                                                                                             |
| <b>Connections/ Terminals</b>                                  |                                                                                                                                               |
| type of electrical connection of modules and accessories       | Screw-type terminal                                                                                                                           |
| type of electrical connection on enclosure                     | Cable routing above and below, both 1 x M20                                                                                                   |
| tightening torque of the screws in the bracket                 | 1 ... 1.2 N·m                                                                                                                                 |
| tightening torque of fixing screws in the enclosure cover      | 1.5 ... 1.7 N·m                                                                                                                               |
| tightening torque with screw-type terminals                    | 0.8 ... 0.9 N·m                                                                                                                               |
| <b>Ambient conditions</b>                                      |                                                                                                                                               |
| ambient temperature                                            |                                                                                                                                               |
| • during operation                                             | -25 ... +70 °C                                                                                                                                |
| • during storage                                               | -40 ... +80 °C                                                                                                                                |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%, no condensation in operation permitted for all devices behind front panel) |
| <b>Environmental footprint</b>                                 |                                                                                                                                               |
| Environmental Product Declaration(EPD)                         | Yes                                                                                                                                           |
| global warming potential [CO2 eq] total                        | 0.593 kg                                                                                                                                      |
| global warming potential [CO2 eq] during manufacturing         | 0.625 kg                                                                                                                                      |
| global warming potential [CO2 eq] during operation             | 0.235 kg                                                                                                                                      |
| global warming potential [CO2 eq] after end of life            | -0.267 kg                                                                                                                                     |
| <b>Installation/ mounting/ dimensions</b>                      |                                                                                                                                               |
| fastening method of modules and accessories                    | Floor mounting                                                                                                                                |
| height                                                         | 89.4 mm                                                                                                                                       |
| width                                                          | 85 mm                                                                                                                                         |
| depth                                                          | 75 mm                                                                                                                                         |
| shape of the installation opening                              | round                                                                                                                                         |
| <b>Accessories</b>                                             |                                                                                                                                               |
| number of labels                                               | 1                                                                                                                                             |
| marking of the name plate for command devices                  | A = I                                                                                                                                         |
| color of the label                                             | A = black                                                                                                                                     |

number of inscription plates

0

## Approvals Certificates

### General Product Approval



### Test Certificates

### Maritime application

### other

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



LRS



PRIS



RINA



### other

### Environment

[Confirmation](#)



Siemens  
EcoTech

[Environmental Confirmations](#)

### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1851-0AB00-2AB1>

Cax online generator




<http://support.automation.siemens.com/WW/CAOrder/default.aspx?lang=en&mlfb=3SU1851-0AB00-2AB1>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1851-0AB00-2AB1>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1851-0AB00-2AB1&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1851-0AB00-2AB1&lang=en)





---

last modified:

7/10/2025 