



SIMATIC DP, ET 200eco PN, IO-Link master, 4IO-L, 4xM12, Degree of protection IP67

General information	
Vendor identification (VendorID)	002AH
Device identifier (DeviceID)	0306H
Product function	
• Isochronous mode	No
• IRT	No
Operating mode	
• IO-Link	Yes
• DI	Yes
• DQ	Yes; max. 100 mA
Supply voltage	
Rated value (DC)	24 V
Reverse polarity protection	Yes
power supply according to NEC Class 2 required	Yes
Load voltage 2L+	
• Rated value (DC)	24 V
• Reverse polarity protection	Yes; against destruction; load increasing
Input current	
Current consumption, typ.	100 mA
from supply voltage 1L+, max.	4 A
from load voltage 2L+, max.	4 A
Encoder supply	
Number of outputs	4
24 V encoder supply	
• Short-circuit protection	Yes; per channel, electronic
• Output current, max.	500 mA; Per channel
Power loss	
Power loss, typ.	4.8 W
IO-Link	
Number of ports	4
• of which simultaneously controllable	4
IO-Link protocol 1.0	Yes
IO-Link protocol 1.1	Yes
Transmission rate	4.8 kBaud (COM1); 38.4 kBaud (COM2), 230 kBaud (COM3)
Size of process data, input per port	32 byte
Size of process data, input per module	128 bytes + 4 bytes PQI
Size of process data, output per port	32 byte
Size of process data, output per module	128 byte
Memory size for device parameter	2 kbyte; for each port
Master backup	Possible with function block IO_LINK_MASTER

Configuration without S7-PCT	Possible; autostart/manual function
Cable length unshielded, max.	20 m
Operating modes	
• IO-Link	Yes
• DI	Yes
• DQ	Yes; max. 100 mA
Connection of IO-Link devices	
• Port type A	Yes; via 3-core cable
• Port type B	Yes; Additional device supply: max. 2 A per port, max. 4 A per module
Interfaces	
Transmission procedure	100BASE-TX
Number of PROFINET interfaces	1
1. Interface	
Interface types	
• M12 port	Yes
• integrated switch	Yes
PROFINET IO Device	
Services	
— IRT with the option "high flexibility"	Yes
Interface types	
M12 port	
• Autonegotiation	Yes
• Autocrossing	Yes
• Transmission rate, max.	100 Mbit/s
Protocols	
Supports protocol for PROFINET IO	Yes
PROFINET CBA	No
PROFIsafe	No
EtherNet/IP	No
Redundancy mode	
Media redundancy	
— MRP	Yes
Open IE communication	
• TCP/IP	No
• SNMP	Yes
• DCP	Yes
• LLDP	Yes
• ping	Yes
• ARP	Yes
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnoses	
• Diagnostic information readable	Yes
• Monitoring the supply voltage	Yes; green "ON" LED
• Short-circuit	Yes; Device supply to M
• Group error	Yes; Red/yellow "SF/MT" LED
Potential separation	
between the load voltages	Yes
between load voltage and all other switching components	No
between Ethernet and electronics	Yes
Isolation	
tested with	
• 24 V DC circuits	707 V DC (type test)
• Test voltage for interface, rms value [Vrms]	1 500 V; According to IEEE 802.3
Degree and class of protection	
IP degree of protection	IP65/67
Standards, approvals, certificates	
Suitable for safety-related tripping of standard modules	No

Use in hazardous areas	
• Explosion protection category for gas	ATEX II 3G Ex nA II T4
• Explosion protection category for dust	ATEX II 3D Ex tc IIIC T90°C Dc
connection method	
Design of electrical connection	3/5-pin M12 round connectors
Dimensions	
Width	30 mm
Height	200 mm
Depth	49 mm
Weights	
Weight, approx.	550 g

Classifications			
		Version	Classification
	eClass	14	27-24-26-08
	eClass	12	27-24-26-08
	eClass	9.1	27-24-26-08
	eClass	9	27-24-26-08
	eClass	8	27-24-26-08
	eClass	7.1	27-24-26-08
	eClass	6	27-24-26-08
	ETIM	10	EC001604
	ETIM	9	EC001604
	ETIM	8	EC001604
	ETIM	7	EC001604
	IDEA	4	3564
	UNSPSC	15	32-15-17-05

Approvals / Certificates	
General Product Approval	



[Miscellaneous](#)

[Manufacturer Declaration](#)



[KC](#)

General Product Approval	EMV	For use in hazardous locations
--------------------------	-----	--------------------------------



[CCC-Ex](#)



For use in hazardous locations	Maritime application
--------------------------------	----------------------

[Miscellaneous](#)



[NK / Nippon Kaiji Kyokai](#)

Maritime application	Industrial Communication
----------------------	--------------------------



[CCS \(China Classification Society\)](#)



[PROFINET](#)

last modified:

4/11/2025

