



SCALANCE XP208, managed IE switch, 8x 10/100 Mbit/s M12 ports, IP65, LED diagnostics, error signaling contact, redundant power supply, IEC 62443-4-2 certified PROFINET IO device, network management, can be operated in redundant ring, dust caps, including electronic manual on CD-ROM, C-plug optional.

product type designation	
product brand name	SCALANCE
product type designation	XP208
transfer rate	
transfer rate	10, 100 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	8; M12
number of 10/100 Mbit/s M12-ports (D-coded)	8
interfaces / other	
number of electrical connections	
• for operator console	1
• for signaling contact	1
• for power supply	2
type of electrical connection	
• for operator console	5 pin M12 socket (A coded)
• for signaling contact	5-pin M12 connector (B-coded)
• for power supply	4-pin M12 plug (A-coded)
design of the removable storage	Yes
• C-PLUG	Yes
product function / device replacement with replacement of the storage medium	Yes
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage / 1 / of the supply voltage	
• supply voltage / 1 / rated value	DC
• power loss [W] / 1 / rated value	24 V
• consumed current / 1 / at rated supply voltage / maximum	5 W
• supply voltage / 1 / rated value	0.2 A
• consumed current / 1 / maximum	19.2 ... 28.8 V
• type of electrical connection / 1 / for power supply	0.21 A
• product component / 1 / fusing at power supply input	4-pin M12 plug (A-coded)
• fuse protection type / 1 / at input for supply voltage	Yes
	5 A / 60 V
ambient conditions	
ambient temperature	
• during operation	-40 ... +70 °C

• during storage	-40 ... +70 °C
• during transport	-40 ... +70 °C
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP65
design, dimensions and weights	
design	compact
width	200 mm
height	200 mm
depth	49 mm
net weight	1.8 kg
material / of the enclosure	Aluminum
fastening method	ET200pro module carrier
• wall mounting	Yes
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of <1~0.3>~s	50
cascading in cases of star topology	any (depending only on signal propagation time)
product function	
• QoS according to DSCP	Yes
product feature	
• Cut Through switching method	No
• Store & Forward switching method	Yes
product functions / management, configuration, engineering	
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• configuration with STEP 7	Yes
• RMON	Yes
• SMTP server	No
• port mirroring	Yes
• multiport mirroring	Yes
• CoS	Yes
• with IRT / PROFINET IO switch	No
• PROFINET IO diagnosis	Yes
• switch-managed	Yes
PROFINET conformity class	B
network load class / according to PROFINET	III
telegram length / for Ethernet / maximum	1518 byte
protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• SFTP	Yes
• BOOTP	No
• GMRP	Yes
• DCP	Yes
• LLDP	Yes
• EtherNet/IP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	

product function		
• port diagnostics	Yes	
• statistics Packet Size	Yes	
• statistics packet type	Yes	
• error statistics	Yes	
• SysLog	Yes	
product functions / VLAN		
product function		
• VLAN - port based	Yes	
• VLAN - protocol-based	No	
• VLAN - IP-based	No	
number of VLANs / maximum	257	
number of VLANs - dynamic / maximum	257	
number of VLANs / at ring redundancy (HRP; MRP; standby link)	257	
product functions / DHCP		
product function		
• DHCP server	Yes	
• DHCP client	Yes	
• DHCP Option 82	Yes	
• DHCP Option 66	Yes	
• DHCP Option 67	Yes	
product functions / redundancy		
protocol / is supported / Media Redundancy Protocol (MRP)	Yes	
product function		
• media redundancy protocol (MRP) with redundancy manager	Yes	
• Media Redundancy Protocol Interconnection (MRP-I)	Yes	
• of the PROFINET IO device / is supported / H-Sync forwarding	Yes	
• of the PROFINET IO device / is supported / PROFINET system redundancy	Yes	
• ring redundancy	Yes	
• high speed redundancy protocol (HRP) with redundancy manager	Yes	
• high speed redundancy protocol (HRP) with standby redundancy	Yes	
• redundancy procedure STP	Yes	
• redundancy procedure RSTP	Yes	
• redundancy procedure RSTP+	Yes	
• redundancy procedure MSTP	Yes	
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No	
• passive listening	Yes	
system modification during operation		
product function / configuration in RUN via CiR/H-CiR	Yes	
product functions / security		
product function		
• IEEE 802.1x (radius)	Yes	
• RADIUS client	Yes	
• broadcast/multicast/unicast limiter	Yes	
• broadcast blocking	Yes	
protocol / is supported		
• SSH	Yes	
• SSL	Yes	
product functions / time		
product function		
• SICLOCK support	Yes	
• NTP-client	Yes	
• SNTP client	Yes	
protocol / is supported		
• NTP	Yes	

• SNTP	Yes
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• UKCA marking	Yes
• cULus approval	Yes
• KC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
standard	
• for EMC interference emission	EN 61000-6-4 (Class A)
• for immunity to EMC	EN 61000-6-2
• for safety / from CSA and UL	UL 60950-1 E115352, CSA C22.2 No. 60950-1
standards, specifications, approvals / hazardous environments	
certificate of suitability	
• ATEX	Yes
• UKEX	Yes
• IECEx	Yes
• ULhazloc approval	Yes
• CCC / for hazardous zone according to GB standard	Yes
• FM registration	Yes
standards, specifications, approvals / other	
certificate of suitability	
• railway application in accordance with EN 50155	No
• railway application in accordance with EN 50124-1	No
• RoHS conformity	Yes
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes
standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	200.66 kg
• during manufacturing	61.47 kg
• during operation	138.92 kg
• after end of life	0.27 kg
product functions / general	
MTBF	67 a
reference temperature / for MTBF determination	40 °C
reference code	
• according to IEC 81346-2	KF
• according to IEC 81346-2:2019	KFE
Warranty period	5 a
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors	https://support.industry.siemens.com/cs/ww/en/view/109766358
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
• to website: Industrial communication	https://www.siemens.com/simatic-net
• to web page: SiePortal	https://sieportal.siemens.com/
• to website: Image database	https://www.automation.siemens.com/bilddb
• to website: CAx-Download-Manager	https://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit

www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under [https://www.siemens.com/cert. \(V4.7\)](https://www.siemens.com/cert. (V4.7))

Approvals / Certificates

General Product Approval



[Declaration of Conformity](#)



[China RoHS](#)



General Product Approval

EMV

For use in hazardous locations

[Miscellaneous](#)

[Declaration of Conformity](#)



[TUEV](#)

[KC](#)



IECEx

For use in hazardous locations



FM

[CCC-Ex](#)

[Type Test Certificates/Test Report](#)



Maritime application

Environment



[NK / Nippon Kaiji Kyokai](#)



Industrial Communication

[PROFINET](#)

last modified:

8/19/2025