



SCALANCE XC208G PoE Manageable Layer 2 IE PoE Switch; IEC 62443-4-2 certified 6x 10/100/1000 Mbps RJ45 PoE ports acc. to IEEE802.3at ; 2 ports of which according to IEEE802.3bt: 2x 10/100/1000 Mbps RJ45; PoE support for 24 V DC Infeed; 120 W PoE power can be distributed among all PoE ports; 1x console port; diagnostics LED; redundant power supply; temperature range -40 °C to +60 °C; mounting on DIN rail/S7 mounting rail /wall; redundancy functions; Office features (RSTP, VLAN, ...); PROFINET device; Ethernet/IP-compliant; C-PLUG slot; IEEE 1588v2 PTP

product type designation	
product brand name	SCALANCE
product type designation	XC208G PoE
transfer rate	
transfer rate	10, 100, 1000 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	8; RJ45
number of 10/100/1000 Mbit/s RJ45 ports	
• with securing collar	2; 4 PoE ports according to IEEE 802.3at (30 W), 2 PoE ports according to IEEE 802.3bt (60 W)
• with securing collar / with PoE	6
interfaces / other	
number of electrical connections	
• for operator console	1
• for signaling contact	1
type of electrical connection	
• for operator console	RJ11
• for signaling contact	2-pole terminal block
• for power supply	4-pole terminal block
design of the removable storage	Yes
• C-PLUG	
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
supplied active power / of PSE / with PoE	
• total / maximum	144 W
type of voltage / 1 / of the supply voltage	
• supply voltage / 1 / rated value	DC
• consumed current / 1 / at rated supply voltage / maximum	24 V
• supply voltage / 1 / rated value	6 A
• consumed current / 1 / maximum	19.2 ... 31.2 V
• fuse protection type / 1 / at input for supply voltage	7.5 A
	15 A / 125 V
ambient conditions	
ambient temperature	
• during operation	-40 ... +60 °C
• during storage	-40 ... +85 °C

• during transport	-40 ... +85 °C
• note	installation position and SFPs used during the operation have to be considered (see manual)
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	compact
width	100 mm
height	147 mm
depth	125 mm
net weight	0.955 kg
product feature / conformal coating	No
material / of the enclosure	Polycarbonate (PC-GF10) / pressure die cast aluminum
fastening method	
• 35 mm DIN-rail mounting	Yes
• wall mounting	Yes
• S7-300 rail mounting	Yes
• S7-1500 rail mounting	Yes
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of <1~0.3~s	50
cascading in cases of star topology	any (depending only on signal propagation time)
product function	
• QoS according to DSCP	Yes
product feature	
• Cut Through switching method	No
• Store & Forward switching method	Yes
product functions / management, configuration, engineering	
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• configuration with STEP 7	Yes
• RMON	Yes
• SMTP server	No
• port mirroring	Yes
• multiport mirroring	Yes
• CoS	Yes
• PROFINET IO diagnosis	Yes
• switch-managed	Yes
PROFINET conformity class	B
network load class / according to PROFINET	III
telegram length / for Ethernet / maximum	10240 byte
protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• SFTP	Yes
• BOOTP	No
• GMRP	Yes
• DCP	Yes
• LLDP	Yes
• EtherNet/IP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes

identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes
product functions / VLAN	
product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
number of VLANs / maximum	257
number of VLANs - dynamic / maximum	257
number of VLANs / at ring redundancy (HRP; MRP; standby link)	257
product functions / DHCP	
product function	
• DHCP server	Yes
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes
product functions / redundancy	
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• Media Redundancy Protocol Interconnection (MRP-I)	Yes
• of the PROFINET IO device / is supported / H-Sync forwarding	Yes
• of the PROFINET IO device / is supported / PROFINET system redundancy	Yes
• ring redundancy	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure RSTP+	Yes
• redundancy procedure MSTP	Yes
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
• passive listening	Yes
protocol / is supported	
• LACP	Yes
system modification during operation	
product function / configuration in RUN via CiR/H-CiR	Yes
product functions / security	
product function	
• IEEE 802.1x (radius)	Yes
• RADIUS client	Yes
• broadcast/multicast/unicast limiter	Yes
• broadcast blocking	Yes
protocol / is supported	
• SSH	Yes
• SSL	Yes

product functions / time	
product function	
• SICLOCK support	Yes
• NTP-client	Yes
• SNTP client	Yes
protocol / is supported	
• NTP	Yes
• SNTP	Yes
• IEEE 1588 profile default	Yes
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• KC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
product conformity / according to EMC-guideline	2014/30/EU
standard	
• for EMC interference emission	EN 61000-6-4, EN 50121-4
• for immunity to EMC	EN 61000-6-2, EN 50121-4
standards, specifications, approvals / hazardous environments	
certificate of suitability	
• ATEX	Yes
• UKEX	Yes
• IECEx	Yes
• CCC / for hazardous zone according to GB standard	Yes
• FM registration	Yes
standards, specifications, approvals / other	
certificate of suitability	
• railway application in accordance with EN 50121-4	Yes
• RoHS conformity	Yes
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes
standards, specifications, approvals / marine classification	
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• French marine classification society (BV)	Yes
• Chinese Classification Society (CCS)	Yes
• Det Norske Veritas (DNV)	Yes
• Korean Register of Shipping (KRS)	Yes
• Lloyds Register of Shipping (LRS)	Yes
• Nippon Kaiji Kyokai (NK)	Yes
• Polski Rejestr Statków (PRS)	Yes
• Royal Institution of Naval Architects (RINA)	Yes
standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	942.3 kg
• during manufacturing	63.42 kg
• during operation	878.11 kg
• after end of life	0.76 kg
product functions / general	
MTBF	42 a
reference code	
• according to IEC 81346-2	KF
• according to IEC 81346-2:2019	KFE
Warranty period	5 a
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors	https://support.industry.siemens.com/cs/ww/en/view/109766358
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud

- to website: Industrial communication
- to web page: SiePortal
- to website: Image database
- to website: CAx-Download-Manager
- to website: Industry Online Support

<https://www.siemens.com/simatic-net>
<https://sieportal.siemens.com/>
<https://www.automation.siemens.com/bilddb>
<https://www.siemens.com/cax>
<https://support.industry.siemens.com>

security information

security information

Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Approvals / Certificates

General Product Approval



EG-Konf.



[China RoHS](#)



[Miscellaneous](#)



RCM

General Product Approval	EMV	For use in hazardous locations
--------------------------	-----	--------------------------------

[TUEV](#)

[KC](#)



[FM](#)

[CCC-Ex](#)

For use in hazardous locations	Maritime application
--------------------------------	----------------------



UL



ABS



BUREAU
VERITAS



DNV



LRS

[NK / Nippon Kaiji Kyokai](#)

Maritime application	Environment	Industrial Communication
----------------------	-------------	--------------------------



PRS



[CCS \(China Classification Society\)](#)



[PROFINET](#)

last modified:

8/19/2025