


product type designation	PROFIBUS FC Robust Cable
product description	Special bus cable (2-core), sold by the meter, unassembled
	PROFIBUS FC robust bus cable with PUR outer sheath for use in environments exposed to chemicals and mechanical loads, 2-core shielded, Sold by the meter delivery unit max. 1000 m minimum order quantity 20 m.
suitability for use	For use in chemically and mechanically demanding environments
cable designation	02YSY (ST) C11Y 1x2x0,64/2,55-150 VI KF 40 FR
wire length	sold by the meter
electrical data	
attenuation factor per length	
• at 9.6 kHz / maximum	0.0025 dB/m
• at 38.4 kHz / maximum	0.004 dB/m
• at 4 MHz / maximum	0.022 dB/m
• at 16 MHz / maximum	0.042 dB/m
impedance	
• rated value	150 Ω
• at 9.6 kHz	270 Ω
• at 38.4 kHz	185 Ω
• at 3 MHz ... 20 MHz	150 Ω
relative symmetrical tolerance	
• of the characteristic impedance at 9.6 kHz	10 %
• of the characteristic impedance at 38.4 kHz	10 %
• of the characteristic impedance at 3 MHz ... 20 MHz	10 %
loop resistance per length / maximum	110 mΩ/m
shield resistance per length / maximum	9.5 Ω/km
capacity per length / at 1 kHz	28.5 pF/m
operating voltage	
• RMS value	80 V
mechanical data	
number of electrical cores	2
design of the shield	Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires
type of electrical connection / FastConnect	Yes
outer diameter	
• of inner conductor	0.65 mm
• of the wire insulation	2.55 mm
• of the inner sheath of the cable	5.4 mm
• of cable sheath	8 mm
symmetrical tolerance of the outer diameter / of cable sheath	0.4 mm
material	
• of the wire insulation	polyethylene (PE)
• of the inner sheath of the cable	PVC
• of cable sheath	PUR (TPE-U)

color	<ul style="list-style-type: none"> • of the insulation of data wires • of cable sheath 	red/green Violet
bending radius	<ul style="list-style-type: none"> • with single bend / minimum permissible • with multiple bends / minimum permissible 	75 mm 150 mm
tensile load / maximum		100 N
weight per length		71 kg/km
ambient conditions		
ambient temperature	<ul style="list-style-type: none"> • during operation • during storage • during transport • during installation • note 	-40 ... +60 °C -40 ... +60 °C -40 ... +60 °C -40 ... +60 °C Electrical properties measured at 20 °C, tests according to DIN 47250 part 4 respectively DIN VDE 0472
fire behavior		flame resistant according to IEC 60332-1
class of burning behaviour / according to EN 13501-6		Fca
chemical resistance	<ul style="list-style-type: none"> • to mineral oil • to grease • to water 	oil resistant according to IEC 60811-2-1 (7x24h/90°C) resistant conditional resistance
radiological resistance / to UV radiation		resistant
product features, product functions, product components / general		
product feature	<ul style="list-style-type: none"> • halogen-free • silicon-free 	No Yes
standards, specifications, approvals		
UL/ETL listing / 300 V Rating		Yes; c(UL)us, CMX
UL/ETL style / 600 V Rating		No
certificate of suitability	<ul style="list-style-type: none"> • EAC approval • CE marking • RoHS conformity 	Yes Yes Yes
Marine classification association	<ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • Det Norske Veritas (DNV) • Germanische Lloyd (GL) • Lloyds Register of Shipping (LRS) • Nippon Kaiji Kyokai (NK) • Polski Rejestr Statków (PRS) 	No No No No No No No
reference code	<ul style="list-style-type: none"> • according to IEC 81346-2 • according to IEC 81346-2:2019 	WG WGB
further information / internet links		
internet link	<ul style="list-style-type: none"> • to website: Selection guide for cables and connectors • to web page: selection aid TIA Selection Tool • to web page: SiePortal • to website: Image database • to website: CAx-Download-Manager • to website: Industry Online Support 	
	https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://sieportal.siemens.com/ https://www.automation.siemens.com/bilddb https://www.siemens.com/cax https://support.industry.siemens.com	
security information		
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is	

necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Approvals / Certificates

General Product Approval

[Manufacturer Declaration](#)



[Declaration of Conformity](#)



[Fire safety / Physical security](#)

General Product Approval

Environment

[China RoHS](#)



[Environmental Confirmations](#)

last modified:

6/27/2025