



LED cover for position switch Metal 3SE51 2 LEDs, yellow/green, 110-230 V AC  
Color turquoise

|                                                                   |                                                                                    |
|-------------------------------------------------------------------|------------------------------------------------------------------------------------|
| product designation                                               | cover with LED 230 V AC, for wide enclosures for position switch, metal, turquoise |
| product type designation                                          | 3SE5                                                                               |
| <b>General technical data</b>                                     |                                                                                    |
| degree of pollution                                               | class 3                                                                            |
| protection class IP                                               | IP66/IP67                                                                          |
| shock resistance                                                  |                                                                                    |
| • according to IEC 60068-2-27                                     | 30g / 11 ms                                                                        |
| vibration resistance according to IEC 60068-2-6                   | 0.35 mm/5g                                                                         |
| Substance Prohibitance (Date)                                     | 07/01/2006                                                                         |
| Weight                                                            | 0.08 kg                                                                            |
| length of the sensor                                              | 78 mm                                                                              |
| width of the sensor                                               | 56 mm                                                                              |
| <b>Ambient conditions</b>                                         |                                                                                    |
| ambient temperature                                               |                                                                                    |
| • during operation                                                | -25 ... +60 °C                                                                     |
| • during storage                                                  | -40 ... +90 °C                                                                     |
| explosion protection category for dust                            | none                                                                               |
| <b>Enclosure</b>                                                  |                                                                                    |
| design of the housing                                             | block, wide                                                                        |
| coating of the enclosure                                          | cathodic dip coating                                                               |
| <b>Drive Head</b>                                                 |                                                                                    |
| design of the actuating element                                   | Other, without, cover                                                              |
| <b>Installation/ mounting/ dimensions</b>                         |                                                                                    |
| mounting position                                                 | any                                                                                |
| fastening method                                                  | screw fixing                                                                       |
| <b>Supply voltage</b>                                             |                                                                                    |
| type of voltage of the supply voltage of the optional LED display | AC                                                                                 |
| supply voltage of LED                                             |                                                                                    |
| •                                                                 | 230 V                                                                              |
| design of the interface for safety-related communication          | without                                                                            |
| <b>Communication/ Protocol</b>                                    |                                                                                    |
| design of the interface                                           | without                                                                            |
| <b>Approvals Certificates</b>                                     |                                                                                    |
| General Product Approval                                          | Functional Safety                                                                  |



| Test Certificates                                  | other                                                                             | Environment                                                                 |
|----------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------|
| <a href="#">Type Test Certificates/Test Report</a> |  | <a href="#">Confirmation</a><br><a href="#">Environmental Confirmations</a> |

#### Further information

##### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

##### Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5120-3AA00>

##### Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5120-3AA00>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SE5120-3AA00>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SE5120-3AA00&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5120-3AA00&lang=en)



last modified:

4/2/2025 