

Siemens  
EcoTech



Illuminated pushbutton, 22 mm, round, metal, shiny, yellow, pushbutton, raised, momentary contact type



|                                                    |                                  |
|----------------------------------------------------|----------------------------------|
| product brand name                                 | SIRIUS ACT                       |
| product designation                                | Illuminated pushbuttons          |
| design of the product                              | Actuating/signaling element      |
| product type designation                           | 3SU1                             |
| product line                                       | Metal, shiny, 22 mm              |
| <b>Enclosure</b>                                   |                                  |
| number of command points                           | 1                                |
| <b>Actuator</b>                                    |                                  |
| design of the actuating element                    | Raised button                    |
| principle of operation of the actuating element    | momentary contact type           |
| product extension optional                         |                                  |
| • light source                                     | Yes                              |
| • contact module                                   | Yes                              |
| color of the actuating element                     | yellow                           |
| material of the actuating element                  | plastic                          |
| shape of the actuating element                     | round                            |
| outer diameter of the actuating element            | 29.5 mm                          |
| <b>Front ring</b>                                  |                                  |
| product component front ring                       | Yes                              |
| design of the front ring                           | Standard                         |
| material of the front ring                         | Metal, high gloss                |
| color of the front ring                            | silver                           |
| <b>General technical data</b>                      |                                  |
| protection class IP                                | IP66, IP67, IP69(IP69K)          |
| degree of protection NEMA rating                   | 1, 2, 3, 3R, 4, 4X, 12, 13       |
| shock resistance                                   |                                  |
| • according to IEC 60068-2-27                      | sinusoidal half-wave 15g / 11 ms |
| vibration resistance                               |                                  |
| • according to IEC 60068-2-6                       | 10 ... 500 Hz: 5g                |
| operating frequency maximum                        | 3 600 1/h                        |
| mechanical service life (operating cycles) typical | 3 000 000                        |
| reference code according to IEC 81346-2            | S                                |
| Substance Prohibitance (Date)                      | 10/01/2014                       |
| Weight                                             | 0.037 kg                         |
| <b>Safety related data</b>                         |                                  |
| proportion of dangerous failures                   |                                  |
| • with low demand rate according to SN 31920       | 20 %                             |

|                                                                                                                |           |
|----------------------------------------------------------------------------------------------------------------|-----------|
| <ul style="list-style-type: none"> <li>• with high demand rate per NC contact according to SN 31920</li> </ul> | 20 %      |
| <ul style="list-style-type: none"> <li>• with high demand rate per NO contact according to SN 31920</li> </ul> | 50 %      |
| <b>B10 value with high demand rate according to SN 31920</b>                                                   | 3 000 000 |
| <b>failure rate [FIT] with low demand rate per NC contact according to SN 31920</b>                            | 100 FIT   |
| <b>IEC 61508</b>                                                                                               |           |
| T1 value for proof test interval or service life according to IEC 61508                                        | 20 a      |

#### Ambient conditions

|                                                                      |                                                                    |
|----------------------------------------------------------------------|--------------------------------------------------------------------|
| <b>ambient temperature</b>                                           |                                                                    |
| <ul style="list-style-type: none"> <li>• during operation</li> </ul> | -25 ... +70 °C                                                     |
| <ul style="list-style-type: none"> <li>• during storage</li> </ul>   | -40 ... +80 °C                                                     |
| environmental category during operation according to IEC 60721       | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |

#### Environmental footprint

|                                                        |                 |
|--------------------------------------------------------|-----------------|
| Environmental Product Declaration (EPD)                | Yes             |
| global warming potential [CO2 eq] total                | 0.593 kg        |
| global warming potential [CO2 eq] during manufacturing | 0.625 kg        |
| global warming potential [CO2 eq] during operation     | 0.235 kg        |
| global warming potential [CO2 eq] after end of life    | -0.267 kg       |
| Siemens Eco Profile (SEP)                              | Siemens EcoTech |

#### Installation/ mounting/ dimensions

|                                                    |         |
|----------------------------------------------------|---------|
| <b>height</b>                                      | 29.5 mm |
| <b>width</b>                                       | 29.5 mm |
| <b>shape of the installation opening</b>           | round   |
| <b>mounting diameter</b>                           | 22.3 mm |
| <b>positive tolerance of installation diameter</b> | 0.4 mm  |
| <b>mounting height</b>                             | 16.2 mm |
| <b>installation width</b>                          | 29.5 mm |
| <b>installation depth</b>                          | 24.3 mm |

#### Approvals Certificates

|                                 |                          |
|---------------------------------|--------------------------|
| <b>General Product Approval</b> | <b>Test Certificates</b> |
|---------------------------------|--------------------------|



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

|                             |              |                    |
|-----------------------------|--------------|--------------------|
| <b>Maritime application</b> | <b>other</b> | <b>Environment</b> |
|-----------------------------|--------------|--------------------|



[Confirmation](#)

**Siemens EcoTech**



#### Environment



[Environmental Confirmations](#)

#### Further information

**Information on the packaging**

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

**Information for data generation and storage**

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<https://www.siemens.com/ic10>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1051-0BB30-0AA0>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1051-0BB30-0AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1051-0BB30-0AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1051-0BB30-0AA0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1051-0BB30-0AA0&lang=en)



last modified:

5/17/2025 