

Siemens  
EcoTech



Illuminated pushbutton, 22 mm, round, metal, shiny, white, pushbutton, flat, momentary contact type, with holder, 1 NO+1 NC, LED module with integrated LED 230 V AC, screw terminal



|                                                 |                                    |
|-------------------------------------------------|------------------------------------|
| product brand name                              | SIRIUS ACT                         |
| product designation                             | Illuminated pushbuttons            |
| design of the product                           | Complete unit                      |
| product type designation                        | 3SU1                               |
| product line                                    | Metal, shiny, 22 mm                |
| manufacturer's article number                   |                                    |
| • of supplied contact module at position 1      | <a href="#">3SU1400-1AA10-1FA0</a> |
| • of supplied LED module                        | <a href="#">3SU1401-1BF60-1AA0</a> |
| • of the supplied holder                        | <a href="#">3SU1550-0AA10-0AA0</a> |
| • of the supplied actuator                      | <a href="#">3SU1051-0AB60-0AA0</a> |
| number of command points                        | 1                                  |
| Actuator                                        |                                    |
| design of the actuating element                 | Button, flat                       |
| principle of operation of the actuating element | momentary contact type             |
| product extension optional light source         | Yes                                |
| color of the actuating element                  | white                              |
| material of the actuating element               | plastic                            |
| shape of the actuating element                  | round                              |
| outer diameter of the actuating element         | 29.45 mm                           |
| number of contact modules                       | 1                                  |
| Front ring                                      |                                    |
| product component front ring                    | Yes                                |
| design of the front ring                        | Standard                           |
| material of the front ring                      | Metal, high gloss                  |
| color of the front ring                         | silver                             |
| Holder                                          |                                    |
| material of the holder                          | Plastic                            |
| Display                                         |                                    |
| number of LED modules                           | 1                                  |
| General technical data                          |                                    |
| product function positive opening               | Yes                                |
| product component light source                  | Yes                                |
| insulation voltage rated value                  | 320 V                              |
| degree of pollution                             | 3                                  |
| type of voltage of the operating voltage        | AC/DC                              |
| surge voltage resistance rated value            | 4 kV                               |
| protection class IP                             | IP66, IP67, IP69(IP69K)            |

|                                                              |                                                                                                                 |
|--------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|
| protection class IP of the terminal                          | IP20, clamping screw tightened                                                                                  |
| degree of protection NEMA rating                             | 1, 2, 3, 3R, 4, 4X, 12, 13                                                                                      |
| shock resistance                                             |                                                                                                                 |
| • according to IEC 60068-2-27                                | sinusoidal half-wave 15g / 11 ms                                                                                |
| vibration resistance                                         |                                                                                                                 |
| • according to IEC 60068-2-6                                 | 10 ... 500 Hz: 5g                                                                                               |
| operating frequency maximum                                  | 3 600 1/h                                                                                                       |
| mechanical service life (operating cycles) typical           | 3 000 000                                                                                                       |
| electrical endurance (operating cycles) typical              | 10 000 000                                                                                                      |
| thermal current                                              | 10 A                                                                                                            |
| reference code according to IEC 81346-2                      | S                                                                                                               |
| continuous current of the C characteristic MCB               | 10 A; for a short-circuit current smaller than 400 A                                                            |
| continuous current of the quick DIAZED fuse link             | 10 A                                                                                                            |
| continuous current of the DIAZED fuse link gG                | 10 A                                                                                                            |
| Substance Prohibitance (Date)                                | 10/01/2014                                                                                                      |
| SVHC substance name                                          | Lead monoxide (lead oxide) - 1317-36-8<br>2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one - 71868-10-5 |
| Weight                                                       | 89 g                                                                                                            |
| operating voltage                                            |                                                                                                                 |
| • at AC                                                      |                                                                                                                 |
| — at 50 Hz rated value                                       | 5 ... 500 V                                                                                                     |
| — at 60 Hz rated value                                       | 5 ... 500 V                                                                                                     |
| • at DC rated value                                          | 5 ... 500 V                                                                                                     |
| <b>Power Electronics</b>                                     |                                                                                                                 |
| contact reliability                                          | One maloperation per 100 million (17 V, 5 mA), one maloperation per 10 million (5 V, 1 mA)                      |
| <b>Supply voltage</b>                                        |                                                                                                                 |
| type of voltage of the supply voltage of the light source    | AC                                                                                                              |
| supply voltage of the light source at AC                     |                                                                                                                 |
| • at 50 Hz rated value                                       | 230 V                                                                                                           |
| • at 60 Hz rated value                                       | 230 V                                                                                                           |
| <b>Control circuit/ Control</b>                              |                                                                                                                 |
| inrush current of LED module maximum                         | 3 A                                                                                                             |
| <b>Auxiliary circuit</b>                                     |                                                                                                                 |
| design of the contact of auxiliary contacts                  | Silver alloy                                                                                                    |
| number of NC contacts for auxiliary contacts                 | 1                                                                                                               |
| number of NO contacts for auxiliary contacts                 | 1                                                                                                               |
| <b>Connections/ Terminals</b>                                |                                                                                                                 |
| type of electrical connection                                | screw terminal                                                                                                  |
| • of modules and accessories                                 | Screw-type terminal                                                                                             |
| type of connectable conductor cross-sections                 |                                                                                                                 |
| • solid with core end processing                             | 2x (0.5 ... 0.75 mm²)                                                                                           |
| • solid without core end processing                          | 2x (1.0 ... 1.5 mm²)                                                                                            |
| • finely stranded with core end processing                   | 2x (0.5 ... 1.5 mm²)                                                                                            |
| • finely stranded without core end processing                | 2x (1,0 ... 1,5 mm²)                                                                                            |
| • for AWG cables                                             | 2x (18 ... 14)                                                                                                  |
| tightening torque of the screws in the bracket               | 1 ... 1.2 N·m                                                                                                   |
| tightening torque with screw-type terminals                  | 0.8 ... 0.9 N·m                                                                                                 |
| <b>Lamp</b>                                                  |                                                                                                                 |
| type of light source                                         | LED                                                                                                             |
| color of the light source                                    | white                                                                                                           |
| light intensity                                              | 900 ... 1 400 mcd                                                                                               |
| <b>Safety related data</b>                                   |                                                                                                                 |
| product function suitable for safety function                | Yes                                                                                                             |
| test wear-related service life necessary                     | Yes                                                                                                             |
| proportion of dangerous failures                             |                                                                                                                 |
| • with low demand rate according to SN 31920                 | 20 %                                                                                                            |
| • with high demand rate per NC contact according to SN 31920 | 20 %                                                                                                            |
| • with high demand rate per NO contact according to SN 31920 | 50 %                                                                                                            |

|                                                                              |           |
|------------------------------------------------------------------------------|-----------|
| B10 value with high demand rate according to SN 31920                        | 3 000 000 |
| failure rate [FIT] with low demand rate per NC contact according to SN 31920 | 100 FIT   |
| ISO 13849                                                                    |           |
| device type according to ISO 13849-1                                         | 3         |
| IEC 61508                                                                    |           |
| safety device type according to IEC 61508-2                                  | Type A    |
| T1 value for proof test interval or service life according to IEC 61508      | 20 a      |

#### Ambient conditions

|                                                                |                                                                                                                                          |
|----------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|
| ambient temperature                                            |                                                                                                                                          |
| • during operation                                             | -25 ... +70 °C                                                                                                                           |
| • during storage                                               | -40 ... +80 °C                                                                                                                           |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3K6 (with relative air humidity of 10 ... 95%, no condensation in operation permitted for all devices behind front panel) |

#### Environmental footprint

|                                                        |                 |
|--------------------------------------------------------|-----------------|
| Environmental Product Declaration (EPD)                | Yes             |
| global warming potential [CO2 eq] total                | 0.593 kg        |
| global warming potential [CO2 eq] during manufacturing | 0.625 kg        |
| global warming potential [CO2 eq] during operation     | 0.235 kg        |
| global warming potential [CO2 eq] after end of life    | -0.267 kg       |
| Siemens Eco Profile (SEP)                              | Siemens EcoTech |

#### Installation/ mounting/ dimensions

|                                             |                      |
|---------------------------------------------|----------------------|
| fastening method                            | front plate mounting |
| • of modules and accessories                | Front plate mounting |
| height                                      | 40 mm                |
| width                                       | 30 mm                |
| shape of the installation opening           | round                |
| mounting diameter                           | 22.3 mm              |
| positive tolerance of installation diameter | 0.4 mm               |
| mounting height                             | 11 mm                |
| installation width                          | 29.5 mm              |
| installation depth                          | 71.7 mm              |

#### Approvals Certificates

|                          |                   |
|--------------------------|-------------------|
| General Product Approval | Test Certificates |
|--------------------------|-------------------|



[Type Test Certificates/Test Report](#)

|                   |                      |       |
|-------------------|----------------------|-------|
| Test Certificates | Maritime application | other |
|-------------------|----------------------|-------|

[Special Test Certificate](#)



[Confirmation](#)

#### Environment



[Environmental Confirmations](#)

#### Further information


Information on the packaging  
<https://support.industry.siemens.com/cs/ww/en/view/109813875>  
 Information for data generation and storage  
<https://support.industry.siemens.com/cs/ww/en/view/109995012>  
 Information- and Downloadcenter (Catalogs, Brochures,...)  
<https://www.siemens.com/ic10>


<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1156-0AB60-1FA0>

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1156-0AB60-1FA0>

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1156-0AB60-1FA0>

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1156-0AB60-1FA0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1156-0AB60-1FA0&lang=en)





last modified:

7/22/2025 ↻