



circular conduc. terminal TA2.2 50...240 mm² large with auxiliary conductor voltage tap 3 units accessory for: plug-in/withdrawable unit 3VA12

Model		
product brand name	SETRON	
product designation	circular conductor terminal	
accessories	Wire connector	
General technical data		
designation / of the terminal	TA2.2	
type of electrical connection / with control wire tap	Yes	
Connections according IEC		
connectable conductor cross-section		
• for copper cable / stranded / minimum	50 mm²	
• for copper cable / stranded / maximum	240 mm²	
• for aluminum cable / stranded / minimum	50 mm²	
• for aluminum cable / stranded / maximum	240 mm²	
stripped length	30,5 mm	
tightening torque / when using copper cables		
• stranded	50 - 240 mm²: 31.1 Nm	
• finely stranded	50 - 185 mm²: 31.1 Nm	
• finely stranded / with core end processing	50 - 185 mm²: 31.1 Nm	
Connetctions according UL		
permissible temperature / of connectable conductor / according to UL 486A-486B	75 °C	
stripped length	1.2 in	
connectable conductor cross-section		
• for copper cable / stranded / minimum	2 AWG	
• for copper cable / stranded / maximum	350 kcmil	
• for aluminum cable / stranded / minimum	2 AWG	
• for aluminum cable / stranded / maximum	350 kcmil	
tightening torque / when using copper cables		
• stranded	2 AWG - 350 kcmil: 275 lb-in	
Certificates		
General Product Approval	EMV	Maritime application
 EG-Konf.		Miscellaneous
	 RCM	 LRS
other	Environment	

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9253-0JC13>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9253-0JC13>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9253-0JC13

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

8/8/2025 

