

circular conduc. terminal TA1.2 35...185 mm² with auxiliary conductor voltage tap 3 units accessory for: 3VA12



Model		
product brand name	SETRON	
product designation	Circular conductor terminal voltage tap 3 units	
accessories	Wire connector	
General technical data		
designation / of the terminal	TA1.2	
type of electrical connection / with control wire tap	Yes	
Connections according IEC		
connectable conductor cross-section		
• for copper cable / stranded / minimum	50 mm²	
• for copper cable / stranded / maximum	185 mm²	
• for aluminum cable / stranded / minimum	50 mm²	
• for aluminum cable / stranded / maximum	185 mm²	
stripped length	20 mm	
tightening torque / when using copper cables		
• stranded	50 - 185 mm²: 22.6 Nm	
• finely stranded	95 - 150 mm²: 22.6 Nm	
• finely stranded / with core end processing	35 - 120 mm²: 22.6 Nm	
Connetctions according UL		
permissible temperature / of connectable conductor / according to UL 486A-486B	75 °C	
stripped length	0.8 in	
Certificates		
General Product Approval	EMV	Test Certificates



[Miscellaneous](#)



[Type Test Certificates/Test Report](#)

Maritime application	other	Environment		
	Confirmation	Miscellaneous	Environmental Confirmations	Environmental Confirmations

Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9253-0JG12>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9253-0JG12>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9253-0JG12

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

8/8/2025 

