

Data sheet

3RV2926-0D

| | | |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| product brand name | | door-coupling rotary operating mechanism IP64 for circuit breaker size S00...S3 without handle, 330 mm shaft !!! product phase-out !!! successor type is 3RV2926-1B drilling pattern changes |
| product designation | | door-coupling rotary operating mechanism |
| design of the product | | standard |
| suitability for use | | Circuit breaker S00, S0, S2, S3 |
| General technical data | | |
| certificate of suitability | | CE / UL / CSA |
| size of the circuit-breaker | | S00, S0, S2, S3 |
| product feature can be locked into OFF position | | Yes |
| operating frequency maximum | | 15 1/h |
| Substance Prohibitance (Date) | | 07/01/2006 |
| Net Weight | | 0.126 kg |
| control version of the switch operating mechanism | | long shaft |
| Ambient conditions | | |
| ambient temperature | | |
| • during operation | | |
| -20 ... +70 °C | | |
| • during storage | | |
| -50 ... +80 °C | | |
| Actuator | | |
| product feature interlock | | Yes |
| color of the actuating element | | black |
| Installation/ mounting/ dimensions | | |
| mounting position | | any |
| fastening method | | screw fixing |
| height | | 66 mm |
| width | | 66 mm |
| depth | | 50 mm |
| length | | 130 mm |
| diameter | | 22.5 mm |
| required spacing | | |
| • for grounded parts | | |
| — forwards | | |
| — backwards | | |
| — upwards | | |
| — at the side | | |
| — downwards | | |
| 0 mm | | |
| Further information | | |
| Information on the packaging | | |
| https://support.industry.siemens.com/cs/ww/en/view/109813875 | | |
| Information for data generation and storage | | |
| https://support.industry.siemens.com/cs/ww/en/view/109995012 | | |
| Information- and Downloadcenter (Catalogs, Brochures,...) | | |
| https://www.siemens.com/ic10 | | |
| Industry Mall (Online ordering system) | | |
| https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV2926-0D | | |
| Cax online generator | | |
| https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV2926-0D | | |
| Service&Support (Manuals, Certificates, Characteristics, FAQs,...) | | |
| https://support.industry.siemens.com/cs/ww/en/ps/3RV2926-0D | | |
| Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) | | |
| https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV2926-0D&lang=en | | |

last modified:

4/17/2025 