

## Data sheet

## 6AG1055-4MH08-2BA1



Figure similar

SIPLUS LOGO! TDE based on 6ED1055-4MH08-0BA1 with conformal coating, -25...+60 °C, start up -20 °C, 6-line, 3 background colors 2 Ethernet ports, installation accessories for LOGO! 8

General information	
Product type designation	Text display
Suitability for use based on	Can be used with LOGO! 8 and higher <a href="#">6ED1055-4MH08-0BA1</a>
Display	
Design of display	FSTN
Line display	
• Number of lines	6
• Number of characters per line	20
Backlighting	
• Type of backlighting	LED
Control elements	
Keyboard fonts	
• System keys	Yes
— Number of configurable system keys	0
• alphanumeric keyboard	No
Installation type/mounting	
Wall mounting/direct mounting	No
Supply voltage	
Type of supply voltage	AC/DC
Rated value (DC)	12 V; 12/24 V DC, 24 V AC
Power loss	
Power loss, typ.	1.8 W; Power supply: 24 V DC
Interrupts/diagnostics/status information	
Diagnostics function	No
Degree and class of protection	
IP (at the front)	IP65
Standards, approvals, certificates	
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO <sub>2</sub> eq]	43 kg
— global warming potential, (during production) [CO <sub>2</sub> eq]	8.5 kg
— global warming potential, (during operation) [CO <sub>2</sub> eq]	34.5 kg
— global warming potential, (after end of life cycle) [CO <sub>2</sub> eq]	-0.065 kg
Ambient conditions	
Ambient temperature during operation	

• min.	-25 °C; = Tmin; Startup @ -20 °C
• max.	60 °C; = Tmax; Tmax: >55 °C application of max. 1 Industrial Ethernet interface
• At cold restart, min.	-20 °C; incl. condensation / frost permitted (no commissioning under condensation conditions)
<b>Ambient temperature during storage/transportation</b>	
• min.	-40 °C
• max.	70 °C
<b>Altitude during operation relating to sea level</b>	
• Installation altitude above sea level, max.	5 000 m
• Ambient air temperature-barometric pressure-altitude	Tmin ... Tmax at 1 140 hPa ... 795 hPa (-1 000 m ... +2 000 m) // Tmin ... (Tmax - 10 K) at 795 hPa ... 658 hPa (+2 000 m ... +3 500 m) // Tmin ... (Tmax -20 K) at 658 hPa ... 540 hPa (+3 500 m ... +5 000 m)
<b>Relative humidity</b>	
• With condensation, tested in accordance with IEC 60068-2-38, max.	100 %; RH incl. condensation / frost (no commissioning in bedewed state), horizontal installation
<b>Resistance</b>	
<b>Coolants and lubricants</b>	
— Resistant to commercially available coolants and lubricants	Yes; Incl. diesel and oil droplets in the air
<b>Use in stationary industrial systems</b>	
— to biologically active substances according to EN 60721-3-3	Yes; Class 3B2 mold, fungus and dry rot spores (with the exception of fauna); Class 3B3 on request
— to chemically active substances according to EN 60721-3-3	Yes; Class 3C4 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *
— to mechanically active substances according to EN 60721-3-3	Yes; Class 3S4 incl. sand, dust, *
<b>Use on ships/at sea</b>	
— to biologically active substances according to EN 60721-3-6	Yes; Class 6B2 mold and fungal spores (excluding fauna); Class 6B3 on request
— to chemically active substances according to EN 60721-3-6	Yes; Class 6C3 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *
— to mechanically active substances according to EN 60721-3-6	Yes; Class 6S3 incl. sand, dust; *
<b>Usage in industrial process technology</b>	
— Against chemically active substances acc. to EN 60654-4	Yes; Class 3 (excluding trichlorethylene)
— Environmental conditions for process, measuring and control systems acc. to ANSI/ISA-71.04	Yes; Level GX group A/B (excluding trichlorethylene; harmful gas concentrations up to the limits of EN 60721-3-3 class 3C4 permissible); level LC3 (salt spray) and level LB3 (oil)
<b>Remark</b>	
— Note regarding classification of environmental conditions acc. to EN 60721, EN 60654-4 and ANSI/ISA-71.04	* The supplied plug covers must remain in place over the unused interfaces during operation!
<b>Conformal coating</b>	
• Coatings for printed circuit board assemblies acc. to EN 61086	Yes; Class 2 for high reliability
• Protection against fouling acc. to EN 60664-3	Yes; Type 1 protection
• Military testing according to MIL-I-46058C, Amendment 7	Yes; Discoloration of coating possible during service life
• Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A	Yes; Conformal coating, Class A
<b>configuration / header</b>	
<b>Configuration software</b>	
• Configuration tool	LOGO! Soft Comfort V8
<b>Accessories</b>	
belongs to product	LOGO!
<b>Mechanics/material</b>	
Design of housing	plastic
<b>Dimensions</b>	
Width	128.2 mm
Height	86 mm
Depth	38.7 mm
Overall depth	38.7 mm
<b>Weights</b>	
Weight, approx.	220 g
<b>Scope of supply</b>	

Delivery quantity in pieces

1

### Classifications

	Version	Classification
eClass	14	27-33-02-03
eClass	12	27-33-02-03
eClass	9.1	27-33-02-03
eClass	9	27-33-02-03
eClass	8	27-24-23-04
eClass	7.1	27-24-23-04
eClass	6	27-24-23-04
ETIM	10	EC001426
ETIM	9	EC001426
ETIM	8	EC001426
ETIM	7	EC001426
IDEA	4	6679
UNSPSC	15	43-21-19-06

### Approvals / Certificates

#### General Product Approval

EMV



[Manufacturer Declaration](#)



[China RoHS](#)



### Environment



last modified:

10/9/2024