



SITOP Battery module/24V/1.2AH

SITOP battery module 24 V/1.2 Ah with maintenance-free sealed lead-acid batteries for SITOP DC UPS module 6 A

electrical data

end-of-charge voltage at DC	
• at -10 °C recommended	29 V
• at 0 °C recommended	28.4 V
• at 10 °C recommended	27.8 V
• at 20 °C recommended	27.3 V
• at 30 °C recommended	26.8 V
• at 40 °C recommended	26.6 V
• at 50 °C recommended	26.3 V

output

battery capacity	1.2 A·h
output current in buffering mode maximum	3.6 A
peak current	7.5 A
charging current maximum	0.3 A
output voltage at DC rated value	24 V

interfaces

communication function	No
------------------------	----

protection and monitoring

design of short-circuit protection	Battery fuse 7.5 A/32 V (solid-state circuitry blade-type fuse + support)
design of the overload protection	Valve control

safety

operating resource protection class	Class III
protection class IP	IP00

standards, specifications, approvals

certificate of suitability	
• CE marking	Yes
• UL approval	Yes; cURus-Recognized (UL 1778, CSA C22.2 No. 107.1), File E219627
• EAC approval	Yes

standards, specifications, approvals hazardous environments

certificate of suitability	
• ATEX	No
• cCSAus, Class 1, Division 2	No

standards, specifications, approvals marine classification

shipbuilding approval	Yes
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• Det Norske Veritas (DNV)	Yes

standards, specifications, approvals Environmental Product Declaration

Environmental Product Declaration	Yes
global warming potential [CO ₂ eq]	

• total	6.7 kg
• during manufacturing	4.1 kg
• during operation	1.8 kg
• after end of life	0.26 kg
ambient conditions	
ambient condition	For storage, mounting and operation of lead-acid batteries, the relevant DIN/VDE regulations or country-specific regulations (e.g. VDE 0510 Part 2/EN 50272-2) must be observed. You must ensure that the battery site is sufficiently ventilated. Possible sources of ignition must be at least 50 cm away.
ambient temperature	
• during operation	-15 ... +50
• during transport	-20 ... +50
• during storage	-20 ... +50
relative temporary capacity loss at 20 °C in a month typical	3 %
service life	
service life of energy storage	
• typical	capacity falls to 80 % of original capacity (according to EUROBAT)
• at 20 °C typical	4 a
• at 30 °C typical	2 a
• at 40 °C typical	1 a
• at 50 °C typical	0.5 a
note	Along with the storage and operating temperature, other factors such as the duration of the storage period and the charge status during storage have a decisive influence on the possible useful life. Batteries should therefore be stored as briefly as possible, always fully charged, and within the temperature range 0 to +20 °C.
connection method	
type of electrical connection	spring-loaded terminals
• for UPS module	1 screw terminal each for 0.08 ... 2.5 mm ² for + BAT and - BAT
mechanical data	
width × height × depth of the enclosure	96 × 106 × 108 mm
installation width × mounting height	116 mm × 126 mm
fastening method	snaps onto DIN rail EN 60715 35x7.5/15 or keyhole mounting for hooking in to M4 screws
• DIN-rail mounting	Yes
• S7 rail mounting	No
• wall mounting	Yes
net weight	1.8 kg
number of cells	12
accessories	
product component included	Accessories pack with solid-state circuitry fuse 7.5 A
further information internet links	
internet link	
• to website: Industry Mall	https://mall.industry.siemens.com
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
• to web page: power supplies	https://siemens.com/sitop
• to website: CAx-Download-Manager	https://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
additional information	
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available

and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under [https://www.siemens.com/cert. \(V4.7\)](https://www.siemens.com/cert. (V4.7))

Classifications

	Version	Classification
eClass	14	27-05-04-03
eClass	12	27-05-04-03
eClass	9.1	27-05-04-03
eClass	9	27-05-04-03
eClass	8	27-05-04-03
eClass	7.1	27-05-04-03
eClass	6	27-05-04-90
ETIM	10	EC000357
ETIM	9	EC000357
ETIM	8	EC000357
ETIM	7	EC000357
UNSPSC	15	26-11-17-01

Approvals Certificates

General Product Approval



[Manufacturer Declaration](#)

[Declaration of Conformity](#)



[Declaration of Conformity](#)



General Product Approval	Maritime application	Dangerous goods	Environment
Miscellaneous			Dangerous goods information Transport Information 

last modified:

4/9/2025 