



SCALANCE X308-2, managed plus IE switch, 2x 1000 Mbit/s MM SC 1x 10/100/1000 Mbit/s and 7x 10/100 Mbit/s RJ45 ports, LED diagnostics, error signalling contact with select/set pushbutton, PROFINET IO device, network management, integrated redundancy manager, office features (RSTP, VLAN, IGMP,...) C-PLUG in scope of supply.

product type designation	
product brand name	SCALANCE
product type designation	X308-2
transfer rate	
transfer rate	10, 100, 1000 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	8
number of 10/100 Mbit/s RJ45 ports	
• with securing collar	7
number of 10/100/1000 Mbit/s RJ45 ports	
• with securing collar	1
number of 1000 Mbit/s SC ports	
• for multimode	2
transmission method / of the optical interface	1000BaseFX
interfaces / other	
number of electrical connections	
• for signaling contact	1
• for power supply	1
type of electrical connection	
• for signaling contact	2-pole terminal block
• for power supply	4-pole terminal block
design of the removable storage	
• C-PLUG	Yes
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage supply / redundant power supply unit	No
type of voltage / 1 / of the supply voltage	
• supply voltage / 1 / rated value	DC
• power loss [W] / 1 / rated value	24 V
• supply voltage / 1 / rated value	9.6 W
• consumed current / 1 / maximum	18 ... 32 V
• type of electrical connection / 1 / for power supply	0.4 A
• product component / 1 / fusing at power supply input	4-pole terminal block
• fuse protection type / 1 / at input for supply voltage	Yes
	F 3 A / 32 V
ambient conditions	

ambient temperature		
● during operation	-10 ... +60 °C	
● during storage	-40 ... +70 °C	
● during transport	-40 ... +70 °C	
relative humidity		
● at 25 °C / without condensation / during operation / maximum	95 %	
protection class IP	IP30	
design, dimensions and weights		
design	compact	
width	120 mm	
height	125 mm	
depth	123 mm	
net weight	1.4 kg	
fastening method	When used in shipbuilding, installation on a 35 mm standard mounting rail is not permitted.	
● 19-inch installation	No	
● 35 mm DIN-rail mounting	Yes	
● wall mounting	Yes	
● S7-300 rail mounting	Yes	
● S7-1500 rail mounting	No	
product features, product functions, product components / general		
cascading in the case of a redundant ring / at reconfiguration time of <1~0.3>~s	100	
cascading in cases of star topology	any (depending only on signal propagation time)	
product functions / management, configuration, engineering		
product function		
● CLI	Yes	
● web-based management	Yes	
● MIB support	Yes	
● TRAPs via email	Yes	
● configuration with STEP 7	Yes	
● RMON	Yes	
● port mirroring	Yes	
● multiport mirroring	Yes	
● CoS	Yes	
● PROFINET IO diagnosis	Yes	
● switch-managed	Yes	
PROFINET conformity class	B	
protocol / is supported		
● Telnet	Yes	
● HTTP	Yes	
● HTTPS	Yes	
● TFTP	Yes	
● FTP	Yes	
● BOOTP	Yes	
● GMRP	Yes	
● DCP	Yes	
● LLDP	Yes	
● SNMP v1	Yes	
● SNMP v2	Yes	
● SNMP v3	Yes	
● IGMP (snooping/querier)	Yes	
identification & maintenance function		
● I&M0 - device-specific information	Yes	
● I&M1 - higher level designation/location designation	Yes	
product functions / diagnostics		
product function		
● port diagnostics	Yes	
● statistics Packet Size	Yes	
● statistics packet type	Yes	

• error statistics	Yes
• SysLog	Yes
product functions / VLAN	
product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
• VLAN dynamic	Yes
number of VLANs / maximum	255
number of VLANs - dynamic / maximum	255
product functions / DHCP	
product function	
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes
product functions / redundancy	
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• ring redundancy	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure MSTP	Yes
• passive listening	Yes
protocol / is supported	
• STP/RSTP	Yes
• STP	Yes
• RSTP	Yes
• MSTP	Yes
• RSTP big network support	Yes
• LACP	Yes
product functions / security	
product function	
• IEEE 802.1x (radius)	Yes
• broadcast/multicast/unicast limiter	Yes
• broadcast blocking	Yes
protocol / is supported	
• SSH	Yes
product functions / time	
product function	
• SICLOCK support	Yes
protocol / is supported	
• NTP	Yes
• SNTP	Yes
• IEEE 1588 profile default	No
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• UKCA marking	Yes
• KC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
standard	
• for EMC interference emission	EN 61000-6-4:2007 (Class A)
• for immunity to EMC	EN 61000-6-2:2005
• for safety / from CSA and UL	UL 60950-1, CSA C22.2 No. 60950-1

standards, specifications, approvals / hazardous environments

certificate of suitability

- ATEX
- UKEX
- IECEx
- ULhazloc approval
- CCC / for hazardous zone according to GB standard
- FM registration

Yes
Yes
Yes
Yes
Yes
Yes

standards, specifications, approvals / other

certificate of suitability

- railway application in accordance with EN 50155
- RoHS conformity

No
Yes

resistance to air pollution / conformity according to ANSI/ISA-71.04

Yes; G3

standards, specifications, approvals / marine classification

Marine classification association

- Det Norske Veritas (DNV)
- Royal Institution of Naval Architects (RINA)

No
Yes

product functions / general

MTBF

25 a

reference code

- according to IEC 81346-2
- according to IEC 81346-2:2019

KF
KFE

Warranty period

5 a

product function / is supported / identification link

Yes; acc. to IEC 61406-1:2022

further information / internet links

internet link

- to website: Selection guide for cables and connectors
- to web page: selection aid TIA Selection Tool
- to website: Industrial communication
- to web page: SiePortal
- to website: Image database
- to website: CAx-Download-Manager
- to website: Industry Online Support

<https://support.industry.siemens.com/cs/ww/en/view/109766358>
<https://www.siemens.com/tstcloud>
<https://www.siemens.com/simatic-net>
<https://sieportal.siemens.com/>
<https://www.automation.siemens.com/bilddb>
<https://www.siemens.com/cax>
<https://support.industry.siemens.com>

security information

security information

Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Approvals / Certificates

General Product Approval



[Declaration of Conformity](#)



[China RoHS](#)

[Miscellaneous](#)

General Product Approval

EMV

For use in hazardous locations



[KC](#)



IECEx



[FM](#)

[CCC-Ex](#)

[Test Certificates](#)

[Maritime application](#)

[Type Test Certificates/Test Report](#)



ABS



BUREAU
VERITAS



DNV



LRS

[NK / Nippon Kaiji Kyōkai](#)

[Maritime application](#)



PRS



RINA

last modified:

8/8/2025