

Data sheet

6GK5308-2QG10-2AA2



SCALANCE X308-2M PoE; managed IE switch, compact; 4x 10/100/1000 Mbit/s for RJ45 ports electrical with PoE; 2x 100/1000 Mbit/s for 2-port media modules, electrical or optical; LED diagnostics, error signaling Contact with select/set pushbutton, PROFINET IO device, network management, Integrated redundancy manager, office features (RSTP, VLAN, IGMP,..) C-plug in scope of supply.

product type designation	
product brand name	SCALANCE
product type designation	X308-2M PoE
transfer rate	
transfer rate	10, 100, 1000 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
• for Power-over-Ethernet / for network components or terminal equipment	4
number of 10/100/1000 Mbit/s RJ45 ports	
• with securing collar	4
interfaces / for communication / plug-in	
number of 10/100/1000 Mbit/s RJ45 ports	4
• with securing collar	4
• for VD mode of operation / with securing collar	4
number of 10/100/1000 Mbit/s M12-ports (X-coded)	4
number of 100 Mbit/s SC-RJ-ports / for POF FOC	4
number of 100 Mbit/s ST(BFOC) ports	
• for multimode	4
• for single mode (LD)	4
number of 100 Mbit/s SC ports	
• for multimode	4
• for single mode (LD)	4
• for single mode (LH+)	4
number of 1000 Mbit/s SC ports	
• for multimode	4
• for single mode (LD)	4
• for single mode (LH)	4
• for single mode (LH+)	4
number of 100 Mbit/s LC ports	
• for multimode	4
• for single mode (LD)	4
• for single mode (LH+)	4
• for single mode (ELH200)	4
number of 1000 Mbit/s LC ports	
• for multimode	4
• for single mode (LD)	4
• for single mode (LH)	4
• for single mode (LH+)	4
• for single mode (ELH)	4

number of electrical connections	4
interfaces / other	
number of electrical connections	
• for SFP	4
• for signaling contact	1
• for media module	2
• for power supply	1
type of electrical connection	
• for signaling contact	2-pole terminal block
• for power supply	4-pole terminal block
design of the removable storage	
• C-PLUG	Yes
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage supply / redundant power supply unit	No
supplied active power / of PSE / with PoE	
• per port / maximum	15.4 W
• total / maximum	30.8 W
type of voltage / 1 / of the supply voltage	
• supply voltage / 1 / rated value	DC
• power loss [W] / 1 / rated value	24 V
• supply voltage / 1 / rated value	17 W
• consumed current / 1 / maximum	19.2 ... 28.8 V
• consumed current / 1 / maximum	2 A
• type of electrical connection / 1 / for power supply	4-pole terminal block
• product component / 1 / fusing at power supply input	Yes
• fuse protection type / 1 / at input for supply voltage	F 3 A / 32 V
ambient conditions	
ambient temperature	
• during operation	-40 ... +60 °C
• during storage	-40 ... +70 °C
• during transport	-40 ... +70 °C
• note	With vertical installation, the maximum operating temperature is reduced to 60 °C.
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	compact
width	120 mm
height	125 mm
depth	124 mm
net weight	1.15 kg
fastening method	When using SFP plug transceivers, only horizontal mounting is permitted; when used in shipbuilding, installation on a 35 mm standard mounting rail is not permitted
• 19-inch installation	No
• 35 mm DIN-rail mounting	Yes
• wall mounting	Yes
• S7-300 rail mounting	Yes
• S7-1500 rail mounting	No
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of <1~0.3>~s	100
cascading in cases of star topology	any (depending only on signal propagation time)
product feature	
• Store & Forward switching method	Yes
product functions / management, configuration, engineering	

product function		
• CLI	Yes	
• web-based management	Yes	
• MIB support	Yes	
• TRAPs via email	Yes	
• configuration with STEP 7	Yes	
• RMON	Yes	
• port mirroring	Yes	
• multiport mirroring	Yes	
• CoS	Yes	
• PROFINET IO diagnosis	Yes	
• switch-managed	Yes	
PROFINET conformity class	B	
protocol / is supported		
• Telnet	Yes	
• HTTP	Yes	
• HTTPS	Yes	
• TFTP	Yes	
• FTP	Yes	
• BOOTP	Yes	
• GMRP	Yes	
• DCP	Yes	
• LLDP	Yes	
• SNMP v1	Yes	
• SNMP v2	Yes	
• SNMP v3	Yes	
• IGMP (snooping/querier)	Yes	
identification & maintenance function		
• I&M0 - device-specific information	Yes	
• I&M1 - higher level designation/location designation	Yes	
product functions / diagnostics		
product function		
• port diagnostics	Yes	
• statistics Packet Size	Yes	
• statistics packet type	Yes	
• error statistics	Yes	
• SysLog	Yes	
product functions / VLAN		
product function		
• VLAN - port based	Yes	
• VLAN - protocol-based	No	
• VLAN - IP-based	No	
• VLAN dynamic	Yes	
number of VLANs / maximum	255	
number of VLANs - dynamic / maximum	255	
product functions / DHCP		
product function		
• DHCP client	Yes	
• DHCP Option 82	Yes	
• DHCP Option 66	Yes	
• DHCP Option 67	Yes	
product functions / redundancy		
protocol / is supported / Media Redundancy Protocol (MRP)	Yes	
product function		
• media redundancy protocol (MRP) with redundancy manager	Yes	
• ring redundancy	Yes	
• high speed redundancy protocol (HRP) with redundancy manager	Yes	
• high speed redundancy protocol (HRP) with standby redundancy	Yes	

• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure MSTP	Yes
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
• passive listening	Yes
protocol / is supported	
• STP/RSTP	Yes
• STP	Yes
• RSTP	Yes
• MSTP	Yes
• RSTP big network support	Yes
• LACP	Yes
product functions / security	
product function	
• IEEE 802.1x (radius)	Yes
• broadcast/multicast/unicast limiter	Yes
• broadcast blocking	Yes
protocol / is supported	
• SSH	Yes
product functions / time	
product function	
• SICLOCK support	Yes
protocol / is supported	
• NTP	Yes
• SNTP	Yes
• IEEE 1588 profile default	Yes
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• UKCA marking	Yes
• KC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
standard	
• for EMC interference emission	EN 61000-6-4:2007 (Class A)
• for immunity to EMC	EN 61000-6-2:2005
• for safety / from CSA and UL	UL 60950-1, CSA C22.2 No. 60950-1
standards, specifications, approvals / hazardous environments	
certificate of suitability	
• ATEX	Yes
• UKEX	Yes
• IECEx	Yes
• ULhazloc approval	Yes
• CCC / for hazardous zone according to GB standard	Yes
• FM registration	Yes
standards, specifications, approvals / other	
certificate of suitability	
• railway application in accordance with EN 50155	No
• RoHS conformity	Yes
resistance to air pollution / conformity according to ANSI/ISA-71.04	Yes; G3
standards, specifications, approvals / marine classification	
Marine classification association	
• Det Norske Veritas (DNV)	No
• Royal Institution of Naval Architects (RINA)	Yes
product functions / general	
MTBF	33 a
reference code	
• according to IEC 81346-2	KF

• according to IEC 81346-2:2019	KFE
Warranty period	5 a
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022
further information / internet links	
internet link	<ul style="list-style-type: none"> • to website: Selection guide for cables and connectors • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to web page: SiePortal • to website: Image database • to website: CAx-Download-Manager • to website: Industry Online Support
https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://www.siemens.com/simatic-net https://sieportal.siemens.com/ https://www.automation.siemens.com/bilddb https://www.siemens.com/cax https://support.industry.siemens.com	

security information	
security information	<p>Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)</p>

Approvals / Certificates		
General Product Approval	EMV	For use in hazardous locations
 EG-Konf.	Declaration of Conformity	 RCM
		 IECEx

For use in hazardous locations	Test Certificates	Maritime application
 FM	CCC-Ex	Type Test Certificates/Test Report

Maritime application	
 Lloyd's Register	NK / Nippon Kaiji Kyokai

last modified:	8/19/2025 
----------------	---