

Data sheet

6XV1870-2B

product description



Flexible bus cable (4-core), sold by the meter, unassembled

Industrial Ethernet FC TP flexible cable, GP 2x2 (PROFINET Type B), TP installation cable with flexible cores, PROFINET type B, 4-core, shielded, CAT 5e, sold by the meter, delivery unit max. 2500 m minimum order quantity 20 m.

suitability for use

For occasionally moved machine parts

cable designation

SF/UTP, 2YY (ST) CY 2x2x0,75/1,5-100 LI GN

wire length

sold by the meter

electrical data

attenuation factor per length

- at 10 MHz / maximum 0.06 dB/m
- at 100 MHz / maximum 0.21 dB/m

impedance

- at 1 MHz ... 100 MHz 100 Ω

relative symmetrical tolerance

- of the characteristic impedance at 1 MHz ... 100 MHz 5 %

near-end crosstalk per length

- at 1 MHz ... 100 MHz 0.5 dB/m

transfer impedance per length / at 10 MHz

20 mΩ/m

loop resistance per length / maximum

120 mΩ/m

operating voltage

- RMS value 80 V

NVP value in percent

69 %

mechanical data

number of electrical cores

4

design of the shield

SF/UTP, overlapped aluminum-clad foil, sheathed in a protective braided shield of tinned copper wires

type of electrical connection / FastConnect

Yes

core diameter

- of AWG22 insulated conductor 0.75 mm

outer diameter

- of inner conductor 0.75 mm
- of the wire insulation 1.5 mm
- of the inner sheath of the cable 3.9 mm
- of cable sheath 6.5 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.2 mm

material

- of the wire insulation polyethylene (PE)
- of the inner sheath of the cable PVC
- of cable sheath PVC

color

- of the insulation of data wires white/yellow/blue/orange
- of cable sheath green

bending radius

• with single bend / minimum permissible	32.5 mm
• with multiple bends / minimum permissible	52 mm
tensile load / maximum	150 N
weight per length	68 kg/km
ambient conditions	
ambient temperature	
• during operation	-25 ... +75 °C
• during storage	-25 ... +75 °C
• during transport	-25 ... +75 °C
• during installation	-10 ... +60 °C
• note	Electrical properties measured at 20 °C, tests according to DIN VDE 0472
fire behavior	flame resistant according to UL 1685 (CSA FT 4)
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	
• to mineral oil	oil resistant according to IEC 60811-404 (7x24h/90°C)
• to grease	Conditional resistance
• to water	conditional resistance
radiological resistance / to UV radiation	resistant
product features, product functions, product components / general	
product feature	
• halogen-free	No
• PoE capability	Yes
• PoE+ capability	Yes
• silicon-free	Yes
wire length / for Industrial Ethernet	
• with 100BaseTX	85 m
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; c(ETL)us, CMG / (ETL)us PLTC / Sun Res / OIL RES
UL/ETL style / 600 V Rating	Yes; cRUs AWM 21694 AWM I A/B 60°C 600V FT2
certificate of suitability	
• EAC approval	Yes
• CE marking	Yes
• RoHS conformity	Yes
standard for structured cabling	Cat5e
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No
• French marine classification society (BV)	No
• Det Norske Veritas (DNV)	No
• Germanische Lloyd (GL)	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	No
• Polski Rejestr Statków (PRS)	No
reference code	
• according to IEC 81346-2	WG
• according to IEC 81346-2:2019	WGB
standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	0.92 kg
• during manufacturing	0.83 kg
• during operation	0.02 kg
• after end of life	0.07 kg
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors	https://support.industry.siemens.com/cs/ww/en/view/109766358
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
• to web page: SiePortal	https://sieportal.siemens.com/
• to website: Image database	https://www.automation.siemens.com/bilddb
• to website: CAx-Download-Manager	https://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

security information

security information

Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Approvals / Certificates

General Product Approval

[Manufacturer Declaration](#)



[Declaration of Conformity](#)



[China RoHS](#)

General Product Approval

Environment

Industrial Communication

[Fire safety / Physical security](#)



[Environmental Confirmations](#)

[PROFINET](#)

last modified:

9/13/2025