



Pump control panel, Size 1, Three phase full voltage, Solid-state overload relay, OLR amp range 0.75-3.4A, 208VAC 60Hz coil, Standard type contactor, 3A circuit breaker, HOA Sel Sw. <(>&<)> Start P.B., Enclosure NEMA type 3/3R, Weather proof outdoor use

|                                                                         |                                     |
|-------------------------------------------------------------------------|-------------------------------------|
| product brand name                                                      | Class 87                            |
| design of the product                                                   | Pump control panel with MCP         |
| special product feature                                                 | ESP200 overload relay               |
| <b>General technical data</b>                                           |                                     |
| weight [lb]                                                             | 47 lb(av)                           |
| Height x Width x Depth [in]                                             | 29 × 20 × 8 in                      |
| touch protection against electrical shock                               | NA for enclosed products            |
| installation altitude [ft] at height above sea level maximum            | 6560 ft                             |
| ambient temperature [°F]                                                |                                     |
| • during storage                                                        | -22 ... +149 °F                     |
| • during operation                                                      | -4 ... +104 °F                      |
| ambient temperature                                                     |                                     |
| • during storage                                                        | -30 ... +65 °C                      |
| • during operation                                                      | -20 ... +40 °C                      |
| country of origin                                                       | USA                                 |
| <b>Horsepower ratings</b>                                               |                                     |
| yielded mechanical performance [hp] for 3-phase AC motor                |                                     |
| • at 200/208 V rated value                                              | 0.5 hp                              |
| • at 220/230 V rated value                                              | 0.5 hp                              |
| • at 460/480 V rated value                                              | 1 hp                                |
| • at 575/600 V rated value                                              | 1 hp                                |
| <b>Contactor</b>                                                        |                                     |
| size of contactor                                                       | NEMA controller size 1              |
| number of NO contacts for main contacts                                 | 3                                   |
| operating voltage for main current circuit at AC at 60 Hz maximum       | 600 V                               |
| operational current at AC at 600 V rated value                          | 27 A                                |
| mechanical service life (operating cycles) of the main contacts typical | 10000000                            |
| <b>Auxiliary contact</b>                                                |                                     |
| number of NC contacts at contactor for auxiliary contacts               | 0                                   |
| number of NO contacts at contactor for auxiliary contacts               | 1                                   |
| number of total auxiliary contacts maximum                              | 8                                   |
| contact rating of auxiliary contacts of contactor according to UL       | 10A@600VAC (A600), 5A@600VDC (P600) |
| <b>Coil</b>                                                             |                                     |
| type of voltage of the control supply voltage                           | AC                                  |
| control supply voltage                                                  |                                     |
| • at DC rated value                                                     | 0 ... 0 V                           |
| • at AC at 50 Hz rated value                                            | 0 ... 0 V                           |
| • at AC at 60 Hz rated value                                            | 208 ... 208 V                       |
| holding power at AC minimum                                             | 8.6 W                               |

|                                                                                                                    |                                                  |
|--------------------------------------------------------------------------------------------------------------------|--------------------------------------------------|
| apparent pick-up power of magnet coil at AC                                                                        | 218 VA                                           |
| apparent holding power of magnet coil at AC                                                                        | 25 VA                                            |
| operating range factor control supply voltage rated value of magnet coil                                           | 0.85 ... 1.1                                     |
| percentual drop-out voltage of magnet coil related to the input voltage                                            | 50 %                                             |
| ON-delay time                                                                                                      | 19 ... 29 ms                                     |
| OFF-delay time                                                                                                     | 10 ... 24 ms                                     |
| <b>Overload relay</b>                                                                                              |                                                  |
| product function                                                                                                   |                                                  |
| • overload protection                                                                                              | Yes                                              |
| • phase failure detection                                                                                          | Yes                                              |
| • asymmetry detection                                                                                              | Yes                                              |
| • ground fault detection                                                                                           | Yes                                              |
| • test function                                                                                                    | Yes                                              |
| • external reset                                                                                                   | Yes                                              |
| reset function                                                                                                     | Manual, automatic and remote                     |
| trip class                                                                                                         | CLASS 5 / 10 (factory set) / 20 / 30             |
| adjustable current response value current of the current-dependent overload release                                | 0.75 ... 3.4 A                                   |
| tripping time at phase-loss maximum                                                                                | 3 s                                              |
| relative repeat accuracy                                                                                           | 1 %                                              |
| product feature protective coating on printed-circuit board                                                        | Yes                                              |
| number of NC contacts of auxiliary contacts of overload relay                                                      | 1                                                |
| number of NO contacts of auxiliary contacts of overload relay                                                      | 1                                                |
| operational current of auxiliary contacts of overload relay                                                        |                                                  |
| • at AC at 600 V                                                                                                   | 5 A                                              |
| • at DC at 250 V                                                                                                   | 1 A                                              |
| contact rating of auxiliary contacts of overload relay according to UL                                             | 5A@600VAC (B600), 1A@250VDC (R300)               |
| insulation voltage (Ui)                                                                                            |                                                  |
| • with single-phase operation at AC rated value                                                                    | 600 V                                            |
| • with multi-phase operation at AC rated value                                                                     | 300 V                                            |
| <b>Enclosure</b>                                                                                                   |                                                  |
| degree of protection NEMA rating of the enclosure                                                                  | NEMA Type 3R                                     |
| design of the housing                                                                                              | Weather proof for outdoor use                    |
| <b>Standard Control Devices</b>                                                                                    |                                                  |
| product component Hand-Off-Auto selector switch                                                                    | Yes                                              |
| type of Hand-Off-Auto selector switch                                                                              | 30mm metal housing with matte finish             |
| product component start push button                                                                                | Yes                                              |
| type of start push button                                                                                          | 30mm metal housing with matte finish             |
| <b>Circuit Breaker</b>                                                                                             |                                                  |
| type of the motor protection                                                                                       | Motor circuit protector (magnetic trip only)     |
| operational current of motor circuit breaker rated value                                                           | 3 A                                              |
| adjustable current response value current of instantaneous short-circuit trip unit                                 | 10 ... 35 A                                      |
| <b>Mounting/wiring</b>                                                                                             |                                                  |
| mounting position                                                                                                  | Vertical                                         |
| fastening method                                                                                                   | Surface mounting and installation                |
| type of electrical connection for supply voltage line-side                                                         | Box lug                                          |
| type of connectable conductor cross-sections at line-side for AWG cables single or multi-stranded                  | 1x (14 AWG ... 10 AWG) or 1x (12 AWG ... 10 AWG) |
| temperature of the conductor for supply maximum permissible                                                        | 75 °C                                            |
| material of the conductor for supply                                                                               | AL or CU                                         |
| type of electrical connection for load-side outgoing feeder                                                        | Screw-type terminals                             |
| tightening torque [lbf-in] for load-side outgoing feeder                                                           | 20 ... 24 lbf-in                                 |
| type of connectable conductor cross-sections for AWG cables for load-side outgoing feeder single or multi-stranded | 2x (14 ... 10 AWG)                               |
| temperature of the conductor for load-side outgoing feeder maximum permissible                                     | 75 °C                                            |
| material of the conductor for load-side outgoing feeder                                                            | CU                                               |
| type of electrical connection of magnet coil                                                                       | Screw-type terminals                             |
| tightening torque [lbf-in] at magnet coil                                                                          | 5 ... 12 lbf-in                                  |

|                                                                                                                               |                                                     |
|-------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------|
| type of connectable conductor cross-sections of magnet coil for AWG cables single or multi-stranded                           | 2x (16 ... 12 AWG)                                  |
| temperature of the conductor at magnet coil maximum permissible                                                               | 75 °C                                               |
| material of the conductor at magnet coil                                                                                      | CU                                                  |
| type of electrical connection at contactor for auxiliary contacts                                                             | Screw-type terminals                                |
| tightening torque [lbf-in] at contactor for auxiliary contacts                                                                | 10 ... 15 lbf-in                                    |
| type of connectable conductor cross-sections at contactor for AWG cables for auxiliary contacts single or multi-stranded      | 1x (12 AWG), 2x (16 ... 14 AWG), 2x (18 ... 16 AWG) |
| temperature of the conductor at contactor for auxiliary contacts maximum permissible                                          | 75 °C                                               |
| material of the conductor at contactor for auxiliary contacts                                                                 | CU                                                  |
| type of electrical connection at overload relay for auxiliary contacts                                                        | Screw-type terminals                                |
| tightening torque [lbf-in] at overload relay for auxiliary contacts                                                           | 7 ... 10 lbf-in                                     |
| type of connectable conductor cross-sections at overload relay for AWG cables for auxiliary contacts single or multi-stranded | 2x (20 ... 14 AWG)                                  |
| temperature of the conductor at overload relay for auxiliary contacts maximum permissible                                     | 75 °C                                               |
| material of the conductor at overload relay for auxiliary contacts                                                            | CU                                                  |
| <b>Short-circuit current rating</b>                                                                                           |                                                     |
| design of the short-circuit trip                                                                                              | Instantaneous trip circuit breaker                  |
| maximum short-circuit current breaking capacity (Icu)                                                                         |                                                     |
| • at 240 V                                                                                                                    | 100 kA                                              |
| • at 480 V                                                                                                                    | 100 kA                                              |
| • at 600 V                                                                                                                    | 25 kA                                               |
| certificate of suitability                                                                                                    | NEMA ICS 2; UL 508                                  |
| <b>Further information</b>                                                                                                    |                                                     |

**Industrial Controls - Product Overview (Catalogs, Brochures,...)**

[www.usa.siemens.com/iccatalog](http://www.usa.siemens.com/iccatalog)

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:87DUB6MD>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**



<https://support.industry.siemens.com/cs/US/en/ps/US2:87DUB6MD>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=US2:87DUB6MD&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:87DUB6MD&lang=en)


**Certificates/approvals**

<https://support.industry.siemens.com/cs/US/en/ps/US2:87DUB6MD/certificate>



| OUTLINE DIMENSIONS  |       |       |       |          |           |           |
|---------------------|-------|-------|-------|----------|-----------|-----------|
| A                   | B     | C     |       |          |           |           |
| 28.50               | 20.00 | 8.06  |       |          |           |           |
| MOUNTING DIMENSIONS |       |       |       |          |           |           |
| D                   | E     | F     | G     | H        |           |           |
| 24.00               | 6.50  | 10.00 | 27.10 | 7.00     |           |           |
| CONDUIT KNOCKOUTS   |       |       |       |          |           |           |
| I                   | J     | K     | L     | M        | N         | O         |
| 5.50                | 8.50  | 11.50 | 14.50 | 1.12-875 | 1.96-1.71 | 1.35-1.12 |

A5E51602383A/E87010A0546-T005-A4



D63677012

