



circuit breaker 3VA2 IEC Frame 160 breaking capacity class C Icu=110 kA @ 415 V 3-pole, line protection ETU850, LSI, In=100 A overload protection Ir=40 A...100 A short-circuit protection Isd=0.6..10x In, li=1.5..12x In neutral conductor protection optionally with external current transformer, up to 160% terminal connection

Model	
product brand name	SENTRON
product designation	Molded case circuit breaker
design of the product	Line protection
design of the overcurrent release	ETU850
protection function of the overcurrent release	LSI
number of poles	3
General technical data	
insulation voltage / rated value	800 V
operating voltage / at AC / rated value	690 V
power loss [W] / maximum	10 W
power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	3.33 W
mechanical service life (operating cycles) / typical	25 000
electrical endurance (operating cycles) / at AC-1 / at 380/415 V	14 000
electrical endurance (operating cycles) / at AC-1 / at 690 V	9 800
product feature / for neutral conductors / upgradable/retrofitable / short-circuit and overload proof	Yes
ground-fault monitoring version	Without
product function	
• communication function	Yes
• other measurement function	Yes
Net Weight	2.5 kg
Current	
operational current	
• at 40 °C	100 A
• at 45 °C	100 A
• at 50 °C	100 A
• at 55 °C	100 A
• at 60 °C	100 A
• at 65 °C	100 A
• at 70 °C	100 A
Switching capacity according to IEC 60947	
switching capacity class of the circuit breaker	C
maximum short-circuit current breaking capacity (Icu)	
• at 240 V	150 kA

• at 415 V • at 440 V • at 500 V • at 690 V	110 kA 110 kA 85 kA 3 kA
operating short-circuit current breaking capacity (Ics)	
• at 240 V • at 415 V • at 440 V • at 500 V • at 690 V	150 kA 110 kA 110 kA 85 kA 2.5 kA
short-circuit current making capacity (Icm)	
• at 240 V • at 415 V • at 440 V • at 500 V • at 690 V	330 kA 242 kA 242 kA 187 kA 3.7 kA
Adjustable parameters	
product feature / for L-tripping / can be switched on/off	No
adjustable response value setting current (I _r) / of the L-trip / with I _{2t} characteristic	
• minimum • maximum	40 A 100 A
adjustable response value delay time (t _r) / for L-tripping / with I _{2t} characteristic	
• minimum • maximum	0.5 s 25 s
adjustable response value setting current (I _{sd}) / of S-trip / with I _{0t} characteristic	
• minimum • maximum	60 A 1 000 A
adjustable response value setting current (I _{sd}) / of S-trip / with I _{2t} characteristic	
• minimum • maximum	60 A 1 000 A
adjustable response value delay time (t _{sd}) / for S-tripping / with I _{0t} characteristic	
• minimum • maximum	0.05 s 0.5 s
adjustable response value delay time (t _{sd}) / for S-tripping / with I _{2t} characteristic	
• minimum • maximum	0.05 s 0.5 s
adjustable response value setting current (I _i) / for I-tripping	
• minimum • maximum	150 A 1 200 A
adjustable setting current (I _{nN}) / for N-tripping	
• minimum • maximum	20 A 160 A
design of the N-conductor protection	adjustable OFF; 20% to 160%
product function / grounding protection	No
Mechanical Design	
product component	
• undervoltage release • voltage trigger • trip indicator	No No No
height [in]	7.13 in
height	181 mm
width [in]	4.13 in
type of connectable conductor cross-sections / of the round conductor terminal / stranded	1 x (6 - 120 mm ²)
width	105 mm

depth [in]	3.39 in					
depth	86 mm					
Connections						
arrangement of electrical connectors / for main current circuit	Front terminal					
type of electrical connection / for main current circuit	double-sided box terminal					
design of the surface / of the connections / on the top of the switch (N, 1, 3, 5)	tin					
design of the surface / of the connections / on the bottom of the switch (N, 2, 4, 6)	tin					
Auxiliary circuit						
number of CO contacts / for auxiliary contacts	0					
Accessories						
product extension / optional / motor drive	Yes					
Environmental conditions						
protection class IP / on the front	IP40					
ambient temperature						
• during operation / minimum	-25 °C					
• during operation / maximum	70 °C					
• during storage / minimum	-40 °C					
• during storage / maximum	80 °C					
Environmental footprint						
global warming potential [CO2 eq] / total	61.814 kg					
global warming potential [CO2 eq] / during manufacturing	14.6 kg					
global warming potential [CO2 eq] / during operation	48.9 kg					
global warming potential [CO2 eq] / after end of life	-2.2 kg					
Siemens Eco Profile (SEP)	Siemens EcoTech					
reference code / according to IEC 81346-2	Q					
Approvals / Certificates						
General Product Approval						
 CCC  EG-Konf. Confirmation  VDE Miscellaneous 						
General Product Approval	EMV	Test Certificates	Maritime application			
	 RCM	Miscellaneous	Type Test Certificates/Test Report	Special Test Certificate	 ABS	
Maritime application					other	
 BUREAU VERITAS	 DNV	 LRS	 RMRS	CCS (China Classification Society)	 产品合格 QC PASS	
other	Dangerous goods	Environment				
Confirmation	Miscellaneous	Transport Information	 EPD	 Siemens EcoTech		Environmental Confirmations
Environment						

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA2110-7KP36-0AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA2110-7KP36-0AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA2110-7KP36-0AA0

CAX-Online-Generator


<https://www.siemens.com/cax>


Tender specifications

<https://www.siemens.com/specifications>

Characteristic curves

https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP='HAUPT'></mmp_prod_no>





last modified:

4/3/2025 

