



shunt trip left 24 V AC 50/60 Hz / 24-30 V DC accessory for: 3VA1 and 3VA20-26

Model	
product brand name	SETRON
product designation	Auxiliary release
accessories	Auxiliary release
General technical data	
degree of pollution	3
overvoltage category	III
apparent power consumption / maximum	30 VA
consumed active power / at DC / maximum	45 W
Voltage	
surge voltage resistance	4 kV
Mechanical Design	
height	65.1 mm
width	25.7 mm
number of slots	3
depth	31.2 mm
net weight	91 g
Net Weight	84 g
tightening torque / with screw-type terminals / minimum	0.4 N·m
tightening torque / with screw-type terminals / maximum	0.5 N·m
Connections according IEC	
stripped length	10 mm
connectable conductor cross-section	0.5 ... 1.5
• minimum	
• maximum	
AWG number / as coded connectable conductor cross section / for auxiliary contacts	
• minimum	
• maximum	16
Connections according UL	
stripped length [in]	0.4 in
tightening torque [lbf·in] / with screw-type terminals / minimum	3.5 lbf·in
tightening torque [lbf·in] / with screw-type terminals / maximum	4.4 lbf·in
Certificates	
General Product Approval	EMV

[Confirmation](#)[Miscellaneous](#)**Test Certificates****Maritime application****other****Environment**[Type Test Certificates/Test Report](#)[Confirmation](#)[Miscellaneous](#)**Environment**[Environmental Confirmations](#)[Environmental Confirmations](#)**Further information****Information on the packaging**<https://support.industry.siemens.com/cs/ww/en/view/109813875>**Information for data generation and storage**<https://support.industry.siemens.com/cs/ww/en/view/109995012>**Information- and Downloadcenter (Catalogs, Brochures,...)**<https://www.siemens.com/lowvoltage/catalogs>**Industry Mall (Online ordering system)**<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9988-0BL30>**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**<https://support.industry.siemens.com/cs/ww/en/ps/3VA9988-0BL30>**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9988-0BL30**CAX-Online-Generator**<https://www.siemens.com/cax>**Tender specifications**<https://www.siemens.com/specifications>



