



LOGO! CMK2000 Communication module for integrating the LOGO! 8 "in the building system bus KNX;" connection 24 V DC 0.04A 1 RJ45 port for Ethernet 50 communication objects time-of-day synchronization Configuration/diagnostics via web interface

General information	
Firmware version	
• FW update possible	Yes
Installation type/mounting	
Mounting	on 35 mm DIN rail, 4 spacing units wide
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Input current	
Current consumption, max.	0.04 A
Power loss	
Power loss, max.	1.1 W
Memory	
Flash	Yes
Time of day	
Clock synchronization	
• supported	Yes
Interfaces	
Number of industrial Ethernet interfaces	1; Ethernet, 1 port, RJ45
Number of other interfaces	1; EIB/KNX
Transmission rate, max.	100 Mbit/s over Ethernet, 9 600 bit/s over KNX
Design of plug-in connection	KNX terminal 0.6 mm ² - 1.0 mm ²
Protocols	
EIB/KNX	Yes
Web server	
• supported	Yes
Communication functions	
S7 basic communication	
• supported	No
LOGO! communication	
• supported	Yes
Interrupts/diagnostics/status information	
Diagnostics indication LED	
• RUN/STOP LED	Yes
EMC	
Emission of radio interference acc. to EN 55 011	
• Limit class B, for use in residential areas	Yes; In accordance with EN 61000-6-3

Degree and class of protection			
IP degree of protection	IP20		
Standards, approvals, certificates			
CE mark	Yes		
CSA approval	Yes		
UL approval	Yes		
cULus	Yes		
FM approval	No		
RCM (formerly C-TICK)	No		
KC approval	Yes		
EAC (formerly Gost-R)	Yes		
according to VDE 0631	No		
Marine approval	No		
Ambient conditions			
Ambient temperature during operation			
• min.	0 °C		
• max.	55 °C		
Ambient temperature during storage/transportation			
• min.	-40 °C		
• max.	70 °C		
Relative humidity			
• Operation, max.	95 %		
Connection method			
Design of electrical connection for supply voltage	2 screw-type terminals: L+, M 0.5 mm² - 2.5 mm² Screw-type terminal: FE 0.5 mm² ... 6.0 mm²		
Dimensions			
Width	71.5 mm; 4TE		
Height	90 mm		
Depth	58.5 mm		
Weights			
Weight, approx.	0.14 kg		
Classifications			
		Version	Classification
	eClass	14	27-24-22-08
	eClass	12	27-24-22-08
	eClass	9.1	27-24-22-08
	eClass	9	27-24-22-08
	eClass	8	27-24-22-08
	eClass	7.1	27-24-22-08
	eClass	6	27-24-22-08
	ETIM	10	EC001423
	ETIM	9	EC001423
	ETIM	8	EC001423
	ETIM	7	EC001423
	IDEA	4	3564
	UNSPSC	15	32-15-17-05
Approvals / Certificates			
General Product Approval		EMV	

[Manufacturer Declaration](#)



[KC](#)



last modified: 3/12/2024