



SIMATIC ET 200SP, Digital input module, DI 8x 24V DC Basic, type 2 (IEC 61131), sink input, (PNP, P-reading), Packing unit: 10 pieces, fits to BU-type A0, Colour Code CC01, input delay time 0,05..20ms, module diagnostics for: supply voltage

General information	
Product type designation	DI 8x24VDC BA
HW functional status	FS03
Firmware version	V0.0
• FW update possible	No
usable BaseUnits	BU type A0
Color code for module-specific color identification plate	CC01
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V14
• STEP 7 configurable/integrated from version	V5.5 SP3 / -
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.3
Operating mode	
• DI	Yes
• Counter	No
• Oversampling	No
• MSI	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	70 mA; All channels are supplied from the encoder supply
Encoder supply	
Number of outputs	8
Output voltage, min.	19.2 V
Short-circuit protection	Yes; per module
24 V encoder supply	
• 24 V	Yes
• Short-circuit protection	Yes
• Output current per channel, max.	700 mA
• Output current per module, max.	700 mA
Power loss	
Power loss, typ.	1.6 W; 24 V, 8 inputs supplied via encoder supply
Address area	

Address space per module	
• Inputs	1 byte
Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	Type A
Selection of BaseUnit for connection variants	
• 1-wire connection	BU type A0
• 2-wire connection	BU type A0
• 3-wire connection	BU type A0 with AUX terminals
• 4-wire connection	BU type A0 + Potential distributor module
Digital inputs	
Number of digital inputs	8
Digital inputs, parameterizable	Yes
Source/sink input	P-reading
Input characteristic curve in accordance with IEC 61131, type 1	Yes
Input characteristic curve in accordance with IEC 61131, type 2	Yes
Input characteristic curve in accordance with IEC 61131, type 3	Yes
Input voltage	
• Rated value (DC)	24 V
• for signal "0"	-30 to +5 V
• for signal "1"	+11 to +30V
Input current	
• for signal "1", typ.	6.8 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	Yes; 0.05 / 0.1 / 0.4 / 0.8 / 1.6 / 3.2 / 12.8 / 20 ms (in each case + delay of 30 to 500 µs, depending on line length)
— at "0" to "1", min.	0.05 ms
— at "0" to "1", max.	20 ms
— at "1" to "0", min.	0.05 ms
— at "1" to "0", max.	20 ms
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Encoder	
Connectable encoders	
• 2-wire sensor	Yes
— permissible quiescent current (2-wire sensor), max.	2 mA
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnoses	
• Diagnostic information readable	Yes
• Monitoring the supply voltage	Yes
— parameterizable	Yes
• Monitoring of encoder power supply	No
• Wire-break	No
• Short-circuit	No
• Group error	Yes
Diagnostics indication LED	
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Channel status display	Yes; green LED
• for channel diagnostics	No
• for module diagnostics	Yes; green/red DIAG LED
Potential separation	
Potential separation channels	
• between the channels	No

• between the channels and backplane bus • between the channels and the power supply of the electronics	Yes No			
Isolation				
Isolation tested with		707 V DC (type test)		
Standards, approvals, certificates				
Suitable for safety functions		No		
Ecological footprint				
• environmental product declaration		Yes		
Global warming potential				
— global warming potential, (total) [CO2 eq]		15.9 kg		
— global warming potential, (during production) [CO2 eq]		3.69 kg		
— global warming potential, (during operation) [CO2 eq]		12.7 kg		
— global warming potential, (after end of life cycle) [CO2 eq]		-0.495 kg		
Ambient conditions				
Ambient temperature during operation				
• horizontal installation, min. • horizontal installation, max. • vertical installation, min. • vertical installation, max.		-30 °C; < 0 °C as of FS03 60 °C -30 °C; < 0 °C as of FS03 50 °C		
Altitude during operation relating to sea level				
• Installation altitude above sea level, max.		5 000 m; Restrictions for installation altitudes > 2 000 m, see manual		
Dimensions				
Width		15 mm		
Height		73 mm		
Depth		58 mm		
Weights				
Weight, approx.		28 g		
Classifications				
			Version	Classification
		eClass	14	27-24-26-04
		eClass	12	27-24-26-04
		eClass	9.1	27-24-26-04
		eClass	9	27-24-26-04
		eClass	8	27-24-26-04
		eClass	7.1	27-24-26-04
		eClass	6	27-24-26-04
		ETIM	10	EC001599
		ETIM	9	EC001599
		ETIM	8	EC001599
		ETIM	7	EC001599
		IDEA	4	3566
		UNSPSC	15	32-15-17-05
Approvals / Certificates				
General Product Approval				
 EG-Konf. Miscellaneous  Manufacturer Declaration China RoHS  RCM				
Maritime application		Environment		



last modified:

10/23/2025 