

Siemens
EcoTech



SIMATIC DP, electronic module for ET 200SP, F-DI 8x 24 V DC HF, 15 mm width, up to PLe (ISO 13849-1)/ SIL3 (IEC 61508)



Figure similar

General information	
Product type designation	F-DI 8x24VDC HF
Firmware version	V2.0
• FW update possible	Yes
usable BaseUnits	BU type A0
Color code for module-specific color identification plate	CC01
Product function	
• I&M data	Yes; I&M0 to I&M3
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	SIMATIC Safety V17 with HSP 0360 or higher
• STEP 7 configurable/integrated from version	as 6ES7136-6BA00-0CA0
• PROFINET from GSD version/GSD revision	GSDML V2.35
Operating mode	
• DI	Yes
CiR - Configuration in RUN	
Reparameterization possible in RUN	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
power supply according to NEC Class 2 required	No
Input current	
Current consumption, max.	40 mA; without load
Encoder supply	
Number of outputs	8
Short-circuit protection	Yes; Electronic (response threshold 0.7 A to 1.8 A)
Output current	
• up to 60 °C, max.	0.3 A
24 V encoder supply	
• 24 V	Yes; min. L+ (-1.5 V)
• Short-circuit protection	Yes; Electronic (response threshold 0.7 A to 1.8 A)
• Output current per channel, max.	300 mA
• Output current per module, max.	800 mA; Total current of all encoders
Power loss	

Power loss, typ.	2 W
Address area	
Address space per module	
• Inputs	7 byte; S7-300/400F CPU, 6 byte
• Outputs	5 byte; S7-300/400F CPU, 4 byte
Hardware configuration	
Automatic encoding	Yes
• Electronic coding element type F	Yes
Digital inputs	
Number of digital inputs	8
Digital inputs, parameterizable	Yes
Source/sink input	Yes; P-reading
Input characteristic curve in accordance with IEC 61131, type 1	Yes
Input voltage	
• Rated value (DC)	24 V
• for signal "0"	-30 to +5 V
• for signal "1"	+15 to +30 V
Input current	
• for signal "1", typ.	3.7 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	Yes
— at "0" to "1", min.	0.4 ms
— at "0" to "1", max.	20 ms
— at "1" to "0", min.	0.4 ms
— at "1" to "0", max.	20 ms
for technological functions	
— parameterizable	No
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	500 m
Interrupts/diagnostics/status information	
Diagnostics function	Yes; See Chapter "Alarms/diagnostic messages" in the manual
Alarms	
• Diagnostic alarm	Yes
• Hardware interrupt	No
Diagnostics indication LED	
• RUN LED	Yes; green LED
• ERROR LED	Yes; red LED
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Channel status display	Yes; green LED
• for channel diagnostics	Yes; red LED
• for module diagnostics	Yes; green/red DIAG LED
Potential separation	
Potential separation channels	
• between the channels	No
• between the channels and backplane bus	Yes
• between the channels and the power supply of the electronics	No
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Siemens Eco Profile (SEP)	Siemens EcoTech
Suitable for safety functions	Yes
Ecological footprint	
• environmental product declaration	Yes; type II acc. to ISO 14021
Global warming potential	
— global warming potential, (total) [CO2 eq]	52 kg
— global warming potential, (during production) [CO2]	6.8 kg

eq]																																											
— global warming potential, (during operation) [CO2 eq]	45.8 kg																																										
— global warming potential, (after end of life cycle) [CO2 eq]	-0.628 kg																																										
Highest safety class achievable in safety mode																																											
• Performance level according to ISO 13849-1	PLe																																										
• Category according to ISO 13849-1	Cat. 4																																										
• SIL acc. to IEC 61508	SIL 3																																										
Probability of failure (for service life of 20 years and repair time of 100 hours)																																											
— Low demand mode: PFDavg in accordance with SIL3	< 2.00E-05																																										
— High demand/continuous mode: PFH in accordance with SIL3	< 1.00E-09 1/h																																										
Ambient conditions																																											
Ambient temperature during operation																																											
• horizontal installation, min.	0 °C																																										
• horizontal installation, max.	60 °C																																										
• vertical installation, min.	0 °C																																										
• vertical installation, max.	50 °C																																										
Altitude during operation relating to sea level																																											
• Installation altitude above sea level, max.	4 000 m; restrictions for installation altitudes > 2 000 m, see ET 200SP system manual																																										
Dimensions																																											
Width	15 mm																																										
Height	73 mm																																										
Depth	58 mm																																										
Weights																																											
Weight, approx.	29 g																																										
Classifications																																											
	<table><tr><th></th><th>Version</th><th>Classification</th></tr><tr><td>eClass</td><td>14</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>12</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>9.1</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>9</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>8</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>7.1</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>6</td><td>27-24-26-04</td></tr><tr><td>ETIM</td><td>10</td><td>EC001599</td></tr><tr><td>ETIM</td><td>9</td><td>EC001599</td></tr><tr><td>ETIM</td><td>8</td><td>EC001599</td></tr><tr><td>ETIM</td><td>7</td><td>EC001599</td></tr><tr><td>IDEA</td><td>4</td><td>3566</td></tr><tr><td>UNSPSC</td><td>15</td><td>32-15-17-05</td></tr></table>		Version	Classification	eClass	14	27-24-26-04	eClass	12	27-24-26-04	eClass	9.1	27-24-26-04	eClass	9	27-24-26-04	eClass	8	27-24-26-04	eClass	7.1	27-24-26-04	eClass	6	27-24-26-04	ETIM	10	EC001599	ETIM	9	EC001599	ETIM	8	EC001599	ETIM	7	EC001599	IDEA	4	3566	UNSPSC	15	32-15-17-05
	Version	Classification																																									
eClass	14	27-24-26-04																																									
eClass	12	27-24-26-04																																									
eClass	9.1	27-24-26-04																																									
eClass	9	27-24-26-04																																									
eClass	8	27-24-26-04																																									
eClass	7.1	27-24-26-04																																									
eClass	6	27-24-26-04																																									
ETIM	10	EC001599																																									
ETIM	9	EC001599																																									
ETIM	8	EC001599																																									
ETIM	7	EC001599																																									
IDEA	4	3566																																									
UNSPSC	15	32-15-17-05																																									
Approvals / Certificates																																											
General Product Approval																																											
Miscellaneous	Manufacturer Declaration																																										
																																											
																																											
	KC																																										
General Product Approval	For use in hazardous locations																																										



RCM



UL

[CCC-Ex](#)

[FM](#)



ATEX

[Type Examination Certificate](#)

For use in hazardous locations

Functional Safety

Maritime application

[Miscellaneous](#)



IECEX

[Type Examination Certificate](#)

[TUEV](#)



ABS



BUREAU
VERITAS

Maritime application



DNV



LRS

[NK / Nippon Kaiji Kyokai](#)



RINA

[CCS \(China Classification Society\)](#)



KR
KOREAN REGISTER

Environment

Industrial Communication

Siemens
EcoTech



[PROsafe](#)

last modified:

10/23/2025