

Siemens
EcoTech



SIMATIC DP, Electronics module f. ET200SP, F-RQ 1x 24 V DC/24...230VAC/5A ST, 20 mm overall width, 1 relay output (2 NO) Summation output current 5 A, load voltage 24 V DC and 24...230 V AC, Can be used up to PL E (ISO 13849-1: 2008)/ SIL 3 (IEC 61508: 2010) if control takes place by (e.g. 6ES7136-6DB00-0CA0) F-DQ

General information

Product type designation	F-RQ 24 ... 48VDC/24 ... 230VAC/5A ST
usable BaseUnits	BU type F0
Color code for module-specific color identification plate	CC42
Product function	
• I&M data	Yes; I&M0 to I&M3
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V13
• STEP 7 configurable/integrated from version	V5.5 SP4 and higher
• PROFINET from GSD version/GSD revision	V2.31

Supply voltage

Rated value (DC)	24 V; Coil voltage
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
power supply according to NEC Class 2 required	No

Power

Power consumption from the backplane bus	100 mW
--	--------

Power loss

Power loss, typ.	1 W
------------------	-----

Address area

Address space per module	
• Inputs	1 byte

Hardware configuration

Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	type C

Digital outputs

Type of digital output	Relays
Number of digital outputs	1
Limitation of inductive shutdown voltage to	No
Controlling a digital input	Yes
Switching capacity of the outputs	
• with resistive load, max.	5 A
• on lamp load, max.	25 W
Switching frequency	
• with resistive load, max.	2 Hz

• with inductive load, max.	0.1 Hz; See data in manual
• with inductive load (acc. to IEC 60947-5-1, DC13), max.	0.1 Hz
• with inductive load (acc. to IEC 60947-5-1, AC15), max.	2 Hz
Total current of the outputs (per module)	
horizontal installation	
— up to 40 °C, max.	5 A; note derating data in the manual
— up to 50 °C, max.	4 A; note derating data in the manual
— up to 60 °C, max.	3 A; note derating data in the manual
vertical installation	
— up to 50 °C, max.	3 A; note derating data in the manual
Relay outputs	
• Number of relay outputs	1; 2 NO contacts
• Rated supply voltage of relay coil L+ (DC)	24 V
• Current consumption of relays (coil current of all relays), max.	70 mA
• external protection for relay outputs	yes; 6 A, see data in manual
• Relay approved acc. to UL 508	Yes; Pilot Duty B300, R300
Switching capacity of contacts	
— with inductive load, max.	see additional description in the manual
— with resistive load, max.	see additional description in the manual
— Thermal continuous current, max.	5 A
— Switching current, min.	1 mA
— Switching current after exceeding 300 mA, min.	10 mA
— Switching current after exceeding 300 mA, max.	5 A
— Rated switching voltage (DC)	24 V
— Rated switching voltage (AC)	230 V
Cable length	
• shielded, max.	500 m; for load contacts
• unshielded, max.	300 m; for load contacts
• Control cable (input), max.	10 m
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Diagnostics indication LED	
• RUN LED	Yes; green/red DIAG LED
• Channel status display	Yes; green LED
Potential separation	
Potential separation channels	
• between the channels	Yes; for SELV / PELV only
• between the channels and backplane bus	Yes
• between the channels and the power supply of the electronics	Yes
Permissible potential difference	
between channels and backplane bus/supply voltage	250 V AC (reinforced insulation)
Isolation	
Isolation tested with	2 545 V DC/2 s (routine test)
Overvoltage category	III (according to IEC/EN 61131-2:2007 and EN 298:2022), II (according to IEC 61131-2:2017 and IEC 61010-2-201)
tested with	
• between channels and backplane bus/supply voltage	DC 2 545 V 2 s (routine test), impulse voltage test DC 7 200 V / 5 positive and 5 negative pulses (type test)
• between backplane bus and supply voltage	707 V DC (type test)
Standards, approvals, certificates	
Siemens Eco Profile (SEP)	Siemens EcoTech
Suitable for safety functions	Yes
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	52 kg
— global warming potential, (during production) [CO2 eq]	6.8 kg

— global warming potential, (during operation) [CO2 eq]	45.8 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-0.628 kg
Highest safety class achievable in safety mode	
• Performance level according to ISO 13849-1	PLe
• Category according to ISO 13849-1	4
• SIL acc. to IEC 61508	SIL 3
Probability of failure (for service life of 20 years and repair time of 100 hours)	
— Low demand mode: PFDavg in accordance with SIL2	< 1.00E-04, function test 1x per year
— Low demand mode: PFDavg in accordance with SIL3	< 1.00E-05, function test 1x per month
— High demand/continuous mode: PFH in accordance with SIL2	< 1.00E-08 1/h, function test 1x per year
— High demand/continuous mode: PFH in accordance with SIL3	< 6.00E-09 1/h, function test 1x per month
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	0 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	0 °C
• vertical installation, max.	50 °C
Dimensions	
Width	20 mm
Height	73 mm
Depth	58 mm
Weights	
Weight, approx.	56 g
Classifications	

	Version	Classification
eClass	14	27-24-26-04
eClass	12	27-24-26-04
eClass	9.1	27-24-26-04
eClass	9	27-24-26-04
eClass	8	27-24-26-04
eClass	7.1	27-24-26-04
eClass	6	27-24-26-04
ETIM	10	EC001599
ETIM	9	EC001599
ETIM	8	EC001599
ETIM	7	EC001599
IDEA	4	3566
UNSPSC	15	32-15-17-05

Approvals / Certificates	
General Product Approval	



[Miscellaneous](#)

[China RoHS](#)

[Manufacturer Declaration](#)



General Product Approval	For use in hazardous locations	Functional Safety	Maritime application
--------------------------	--------------------------------	-------------------	----------------------



[FM](#)

[TUEV](#)

[Type Examination Certificate](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)

Maritime application

Environment



Siemens
EcoTech



last modified:

10/23/2025 