

## Data sheet

6GK5738-1GY00-0AB0

### product type designation



### W738-1 M12 (USA)

IWLAN client, SCALANCE W738-1 M12, 1 radio, 2 N-CON antenna port, iFeatures support via KEY-PLUG, IEEE 802.11a/b/g/h/n, 2.4/5 GHz, gross data rate 300 Mbps, 2x M12 max. 100 Mbps, PoE integrated 2-port switch, redundant 24 V DC, M12 A-coded IP65, -20... 60°C, plug slot WPA2/802.11i/e, observe national approvals! CERT ID: MSN65-W1-M12-E2 FCC ID: LYHMSN65V1 scope of delivery: manuals on CD-ROM, German/English; M12 sealing caps, for operation in the USA.

Technical Product Detail Page

<https://i.siemens.com/1P6GK5738-1GY00-0AB0>

### transfer rate

#### transfer rate

- with WLAN / maximum
- for Industrial Ethernet

300 Mbit/s

10, 100 Mbit/s

### interfaces

#### number of electrical connections

- for network components or terminal equipment
- for power supply
- for redundant voltage supply

2

1

1

#### type of electrical connection

- for network components or terminal equipment
- for power supply

M12 interface (4-pole, D-coded), PoE

M12 interface (4-pole, A-coded)

### memory

#### design of the removable storage

- C-PLUG
- KEY-PLUG

Yes

Yes

### interfaces / wireless

#### number of radio cards / permanently installed

1

#### transmission mode / for multiple input multiple output (MIMO)

2x2

#### number of spatial streams

2

#### number of electrical connections / for external antenna(s)

2

#### type of electrical connection / for external antenna(s)

N-Connect (socket)

#### product feature / external antenna can be mounted directly on device

Yes

### supply voltage, current consumption, power loss

#### type of voltage / of the supply voltage

DC

#### supply voltage

- from Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af

48 V

#### consumed current

- at DC / at 24 V / typical
- with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical

0.25 A

0.125 A

#### power loss [W]

- at DC / at 24 V / typical
- with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical

6 W

6 W

#### supply voltage / 1

• from M12 Power Connector (A-coded) for redundant power supply	16.8 V
<b>supply voltage / 2</b>	
• from M12 Power Connector (A-coded) for redundant power supply	31.2 V
<b>ambient conditions</b>	
ambient temperature	
• during operation	-20 ... +60 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
ambient condition / for operation	When used under hazardous conditions (Zone 2), the SCALANCE W778-1 M12 or W738-1 M12 product must be installed in an housing with at least IP54 degree of protection according to EN 60529 within the scope of EN 50021.
protection class IP	IP65
<b>design, dimensions and weights</b>	
width	140 mm
height	160 mm
depth	45 mm
width / of the enclosure / without antenna	140 mm
height / of the enclosure / without antenna	149 mm
depth / of the enclosure / without antenna	45 mm
net weight	0.95 kg
fastening method	35 mm DIN rail mounting only per accessories
• S7-300 rail mounting	No
• S7-1500 rail mounting	No
• 35 mm DIN-rail mounting	Yes
• wall mounting	Yes
<b>radio frequencies</b>	
operating frequency	
• for WLAN in 2.4 GHz frequency band	2.41 ... 2.48 GHz; depending on the country approvals
• for WLAN in 5 GHz frequency band	4.9 ... 5.8 GHz; depending on the country approvals
<b>product features, product functions, product components / general</b>	
product function / Access Point Mode	No
product function / client Mode	Yes
product function	
• iPCF client	Yes; Only in combination with the 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures'
• iPCF-MC client	Yes; Only in combination with 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures'
number of iPCF-capable radio modules	1
product function / iREF	No
product function / iPRP	Yes; In combination with the 'KEY-PLUG W780 iFeatures' only
<b>product functions / management, configuration, engineering</b>	
number of manageable IP addresses / in client	8
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• configuration with STEP 7	Yes
• configuration with STEP 7 in the TIA Portal	Yes
• operation with IWLAN controller	No
• operation with Enterasys WLAN controller	No
• WDS	No
protocol / is supported	
• Address Resolution Protocol (ARP)	Yes
• ICMP	Yes
• Telnet	Yes
• HTTP	Yes

• HTTPS	Yes
• TFTP	Yes
• DCP	Yes
• LLDP	No
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022
<b>product functions / diagnostics</b>	
product function	
• PROFINET IO diagnosis	Yes
• link check	No
• connection monitoring IP-Alive	No
• SysLog	Yes
protocol / is supported	
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
<b>product functions / VLAN</b>	
product function	
• function VLAN with IWLAN	No
<b>product functions / DHCP</b>	
product function	
• DHCP client	Yes
• DHCP server	Yes
• DHCP Option 82	Yes
<b>product functions / redundancy</b>	
protocol / is supported	
• STP/RSTP	Yes
• MSTP	Yes
• RSTP	Yes
<b>product functions / security</b>	
product function	
• ACL - MAC-based	Yes
• management security, ACL-IP based	Yes
• IEEE 802.1x (radius)	Yes
• NAT/NAPT	Yes
• access protection according to IEEE802.11i	Yes
• WPA/WPA2	Yes
• TKIP/AES	Yes
protocol / is supported	
• SSH	Yes
• RADIUS	Yes
<b>product functions / time</b>	
protocol / is supported	
• NTP	Yes
• SNTP	Yes
• SIMATIC time synchronization (SIMATIC Time)	Yes
<b>standards, specifications, approvals</b>	
standard	
• for FM	FM 3611: Class I, Division 2, Groups A,B,C,D, T4 / Class 1, Zone 2, Group IIC, T4, FM16US0205X
• for safety / from CSA and UL	UL 61010-2-201 E85972, CSA C22.2 no. 60950-1
certificate of suitability	
• EC Declaration of Conformity	Yes
• CE marking	Yes
• C-Tick	Yes
• E1 approval	Yes
• railway application in accordance with EN 50155	No

• NEMA TS2	No
• IEC 61375	No
• IEC 61850-3	No
• NEMA4X	No
• Power-over-Ethernet according IEEE802.3at for type 1 and IEEE802.3af	No
• Power-over-Ethernet according to IEEE802.3at for type 2	No
standard for wireless communication	
• IEEE 802.11a	Yes
• IEEE 802.11b	Yes
• IEEE 802.11e	Yes
• IEEE 802.11g	Yes
• IEEE 802.11h	Yes
• IEEE 802.11i	Yes
• IEEE 802.11n	Yes
wireless approval	You will find the current list of countries at: <a href="http://www.siemens.de/funkzulassungen">www.siemens.de/funkzulassungen</a>
<b>standards, specifications, approvals / marine classification</b>	
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No
• French marine classification society (BV)	Yes
• DNV GL	No
• Korean Register of Shipping (KRS)	Yes
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	No
• Polski Rejestr Statkow (PRS)	No
• Royal Institution of Naval Architects (RINA)	No
<b>standards, specifications, approvals / hazardous environments</b>	
standard / for hazardous zone	EN 60079-15:2005, EN 60079-0:2006, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
• from CSA and UL	ANSI/ISA 12.12.01-2013, CAN/CSA C22.2 No.213-M1987, Cl. 1, div. 2, GP. A, B, C, D, T4 / Cl. 1, Zone 2, GP IIC E240480
certificate of suitability / CCC / for hazardous zone according to GB standard	Yes; GB3836.1, GB3836.8
• as marking	Ex nA IIC T4 Gc
<b>standards, specifications, approvals / Environmental Product Declaration</b>	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	199.95 kg
• during manufacturing	33.7 kg
• during operation	166.06 kg
• after end of life	0.19 kg
<b>further information / internet links</b>	
internet link	
• to website: Selection guide for cables and connectors	<a href="https://support.industry.siemens.com/cs/ww/en/view/109766358">https://support.industry.siemens.com/cs/ww/en/view/109766358</a>
• to web page: selection aid TIA Selection Tool	<a href="https://www.siemens.com/tstcloud">https://www.siemens.com/tstcloud</a>
• to web page: WLAN country approval	<a href="https://www.siemens.com/wireless-approvals">https://www.siemens.com/wireless-approvals</a>
• to the website: IWLAN	<a href="https://www.siemens.com/iwlan">https://www.siemens.com/iwlan</a>
• to website: Industrial communication	<a href="https://www.siemens.com/simatic-net">https://www.siemens.com/simatic-net</a>
• to web page: SiePortal	<a href="https://sieportal.siemens.com/">https://sieportal.siemens.com/</a>
• to website: Image database	<a href="https://www.automation.siemens.com/bilddb">https://www.automation.siemens.com/bilddb</a>
• to website: CAx-Download-Manager	<a href="https://www.siemens.com/cax">https://www.siemens.com/cax</a>
• to website: Industry Online Support	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>
<b>security information</b>	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is

necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit [www.siemens.com/cybersecurity-industry](http://www.siemens.com/cybersecurity-industry). Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under [https://www.siemens.com/cert. \(V4.7\)](https://www.siemens.com/cert. (V4.7))

## Approvals / Certificates

### General Product Approval

[Declaration of Conformity](#)



[Manufacturer Declaration](#)

China RoHS



### For use in hazardous locations



[CCC-Ex](#)

IECEx

Radio Equipment Type Approval Certificate

[Miscellaneous](#)



### Maritime application



### Maritime application



LRS

[NK / Nippon Kaiji Kyokai](#)



### Railway

[Confirmation](#)



### Environment

last modified:

10/29/2025