

Siemens
EcoTech



AS-Interface module, 2 safe inputs, black, Spring-type terminal (Push-in), for input/output, for floor mounting



product brand name	SIRIUS ACT
product designation	AS-Interface module
product type designation	3SU1
General technical data	
product function	2F-DI
degree of pollution	3
type of voltage	
• of the operating voltage	DC
• of the input voltage	DC
consumed current maximum	60 mA
protection class IP	IP20
shock resistance for railway applications according to EN 61373	Category 1, Class B
vibration resistance for railway applications according to EN 61373	Category 1, Class B
reference code according to IEC 81346-2	K
Substance Prohibittance (Date)	10/01/2014
SVHC substance name	Lead - 7439-92-1 Lead monoxide (lead oxide) - 1317-36-8 Diboron trioxide - 1303-86-2
Net Weight	40 g
design of the device type	2 F-DI
AS-Interface device profile	S-0.B.F
ID1 code	0...F
number of AS-i devices	1
operating voltage rated value	18 ... 31.6 V
operating voltage 1 at DC rated value	30 V
Communication/ Protocol	
protocol is supported	
• AS-Interface protocol	Yes
• ASIsafe (Safety at work) protocol	Yes
Inputs/ Outputs	
number of digital inputs	0
• safety-related	2
number of digital outputs	0
Connections/ Terminals	
type of electrical connection	spring-loaded terminal (push-in)
type of connectable conductor cross-sections	

• solid without core end processing • finely stranded without core end processing • for AWG cables	1x (0.14 ... 0.5 mm²) 1x (0.2 ... 0.5 mm²) 1x (26 ... 20)	
Product Function		
suitability for use safety-related circuits	Yes	
Safety related data		
product function suitable for safety function	Yes	
safe state	off	
test wear-related service life necessary	No	
category according to EN 954-1	4	
average diagnostic coverage level (DCavg)	99 %	
IEC 62061		
SIL Claim Limit (subsystem) according to EN 62061	SIL CL 3	
Safety Integrity Level (SIL) according to IEC 62061	SIL 3	
PFHD with high demand rate according to IEC 62061	0 1/h	
ISO 13849		
performance level (PL) according to ISO 13849-1	PL e	
category according to ISO 13849-1	4	
device type according to ISO 13849-1	1	
IEC 61508		
Safety Integrity Level (SIL) • according to IEC 61508	SIL 3	
safety device type according to IEC 61508-2	Type B	
PFHD with high demand rate according to IEC 61508	0 1/h	
PFDavg with low demand rate according to IEC 61508	5E-6	
Safe failure fraction (SFF)	99 %	
hardware fault tolerance according to IEC 61508	1	
T1 value of service life according to IEC 61508	20 a	
Ambient conditions		
ambient temperature • during operation • during storage	-25 ... +70 °C -40 ... +80 °C	
environmental category during operation according to IEC 60721	3M6, 3S2, 3B2, 3C3 (without salt spray), 3K6 (with relative humidity of 10 ... 95%, no condensation in operation permitted)	
Environmental footprint		
Environmental Product Declaration (EPD)	Yes	
global warming potential [CO2 eq] total	0.787 kg	
global warming potential [CO2 eq] during manufacturing	0.566 kg	
global warming potential [CO2 eq] during operation	0.235 kg	
global warming potential [CO2 eq] after end of life	-0.015 kg	
Siemens Eco Profile (SEP)	Siemens EcoTech	
Installation/ mounting/ dimensions		
fastening method • of modules and accessories • of the AS-i devices	Floor mounting Floor mounting	
height	54.6 mm	
width	25.9 mm	
depth	32.5 mm	
Approvals Certificates		
General Product Approval	EMV	Test Certificates
 EG-Konf.   c UL us   RCM		Special Test Certificate
Test Certificates	Maritime application	other

other	Environment	Industrial Communication
-------	-------------	--------------------------

[Confirmation](#)



Siemens
EcoTech



[Environmental Confirmations](#)



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1400-2EA10-6AA0>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1400-2EA10-6AA0>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1400-2EA10-6AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1400-2EA10-6AA0&lang=en





last modified:

11/21/2025