

## Data sheet

3RK1902-2NC10

bus cable for PROFINET pre-assembled on two sides 4-core, shielded pre-assembled with 2 x M12 D-encoded, angled length 10 m

General technical data		
product description		M12 plug, angled on M12 plug, angled
wire length	m	10
cable designation		BUS: 2x2xAWG22/7 9YH(ST)C11Y
General technical data		
ampacity per pin maximum	A	4
operating voltage		
• at DC maximum	V	60
• at AC maximum	V	60
surge voltage resistance rated value	kV	1.5
impedance		
• at 100 MHz rated value	Ω	100
attenuation factor per length		
• at 4 MHz maximum	dB/m	0.041
• at 10 MHz maximum	dB/m	0.065
• at 16 MHz maximum	dB/m	0.083
• at 100 MHz maximum	dB/m	0.22
Mechanical data		
connector type		Plug / Plug
connector coding of the M12 circular connector		D
number of electrical cores		4
type of cable outlet		angled
number of poles		4
color		
• of cable sheath		green
• of the insulation of data wires		yellow, white, orange, blue
material		
• of cable sheath		Polyurethane
• of the wire insulation		Polonium
• of the enclosure		Thermoplastic polyurethane
design of the shield		Shielding braid of tinned copper wire
type of strain relief		molded
bending radius		
• with single bend minimum permissible	mm	33.5
• with multiple bends minimum permissible	mm	100.5
number of bending cycles		2 000 000
mechanical service life (mating cycles)		100
outer diameter		
• of inner conductor	mm	0.75
• of the cable	mm	6.7
symmetrical tolerance of the outer diameter of the cable	mm	0.2
conductor cross section rated value	mm <sup>2</sup>	0.34
type of plug interlock		M12 x 1 thread
cable end components		populated on both sides
Ambient conditions		
chemical resistance		
• to mineral oil		conditional, must be checked relative to the application
• to water		conditional, must be checked relative to the application

• to grease		conditional, must be checked relative to the application
<b>degree of pollution</b>		3
<b>Certificates/ approvals</b>		
<b>certificate of suitability</b>		
• CSA approval		No
• RoHS conformity		Yes
• UL approval		No
• CCC		No
• IEC approval		Yes
• cUL approval		No
• C-Tick		No

#### Further information

##### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

##### Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK1902-2NC10>

##### Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK1902-2NC10>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RK1902-2NC10>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RK1902-2NC10&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK1902-2NC10&lang=en)

last modified:

4/2/2025 