



enclosure for command devices, 22 mm, round, enclosure material plastic, enclosure top part gray, 2 control points plastic, B=Pushbutton green, label: start, 1 NO, screw terminal, A=Pushbutton red, label: Stop, 1 NC, screw terminal, floor mounting, 1xM20 each on top and bottom, Labels glued in

product brand name	SIRIUS ACT
product designation	Enclosures
product type designation	3SU1
equipment of commanding and signaling device	A = Pushbutton / B = Pushbutton
manufacturer's article number	<ul style="list-style-type: none"> • of supplied contact module at the command point A 1 • of supplied contact module at the command point B 1 • of the supplied holder at the command point A • of the supplied holder at the command point B • of the supplied actuator at the command point A • of the supplied actuator at the command point B • of supplied empty enclosure • of the supplied accessories at the command point A • of the supplied accessories at the command point B
3SU1400-2AA10-1CA0	
3SU1400-2AA10-1BA0	
3SU1500-0AA10-0AA0	
3SU1500-0AA10-0AA0	
3SU1000-0AB20-0AA0	
3SU1000-0AB40-0AA0	
3SU1802-0AZ00 K0Y	
3SU1900-0AF16-0DS0	
3SU1900-0AF16-0DT0	
Enclosure	
design of the housing	with recess for label
shape of the enclosure front	rectangular
material of the enclosure	plastic
number of command points	2
product component	
• EMERGENCY STOP device	No
• protective collar	No
color of the enclosure top part	grey
delivery state	
• as a kit	No
• pre-wired on strip terminal	No
fastening method of the enclosure	Vertical
Actuator	
design of the actuating element	Pushbutton / pushbutton
suitability for use EMERGENCY OFF switch	No
product feature lockout	No
product extension optional light source	No
color of the actuating element	A = red / B = green
material of the actuating element	plastic
shape of the actuating element	round
number of contact modules	2

type of unlocking device		A = none / B = none
Front ring		
product component front ring	Yes	
design of the front ring	Standard	
material of the front ring	plastic	
color of the front ring	black	
Holder		
material of the holder	Plastic	
Display		
number of LED modules	0	
General technical data		
product function		
• positive opening	Yes	
• EMERGENCY OFF function	No	
• EMERGENCY STOP function	No	
protection class IP	IP66, IP67, IP69(IP69K)	
degree of protection NEMA rating	1, 2, 3, 3R, 4, 4X, 12K, 13	
shock resistance		
• according to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms	
• for railway applications according to EN 61373	Category 1, Class B	
vibration resistance		
• according to IEC 60068-2-6	10 ... 500 Hz: 5g	
• for railway applications according to EN 61373	Category 1, Class B	
reference code according to IEC 81346-2	S	
continuous current of the C characteristic MCB	10 A; for a short-circuit current smaller than 400 A	
continuous current of the quick DIAZED fuse link	10 A	
continuous current of the DIAZED fuse link gG	10 A	
Substance Prohibitance (Date)	10/01/2014	
Net Weight	387 g	
operating voltage		
• at AC		
— at 50 Hz rated value	5 ... 500 V	
— at 60 Hz rated value	5 ... 500 V	
• at DC rated value	5 ... 500 V	
Communication/ Protocol		
design of the interface for communication	without	
Auxiliary circuit		
design of the contact of auxiliary contacts	Silver alloy	
number of NC contacts for auxiliary contacts	1	
number of NO contacts for auxiliary contacts	1	
Connections/ Terminals		
type of electrical connection of modules and accessories	Screw-type terminal	
type of electrical connection on enclosure	Cable routing above and below, both 1 x M20	
tightening torque of the screws in the bracket	1 ... 1.2 N·m	
tightening torque of fixing screws in the enclosure cover	1.5 ... 1.7 N·m	
tightening torque with screw-type terminals	0.8 ... 0.9 N·m	
Ambient conditions		
ambient temperature		
• during operation	-25 ... +70 °C	
• during storage	-40 ... +80 °C	
environmental category during operation according to IEC 60721	3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%, no condensation in operation permitted for all devices behind front panel)	
Environmental footprint		
Environmental Product Declaration(EPD)	Yes	
global warming potential [CO2 eq] total	0.787 kg	
global warming potential [CO2 eq] during manufacturing	0.566 kg	
global warming potential [CO2 eq] during operation	0.235 kg	
global warming potential [CO2 eq] after end of life	-0.015 kg	
Installation/ mounting/ dimensions		

fastening method of modules and accessories	Floor mounting
height	114 mm
width	85 mm
depth	75 mm
shape of the installation opening	round

Accessories

number of labels	2
color of the label	A = black / B = black
number of inscription plates	2
number of backing plates	0

Approvals Certificates

General Product Approval



Test Certificates	Maritime application	other
-------------------	----------------------	-------

[Type Test Certificates/Test Report](#)



other	Environment
-------	-------------

[Confirmation](#)



[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1802-0AL00-2AB1>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1802-0AL00-2AB1>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1802-0AL00-2AB1>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1802-0AL00-2AB1&lang=en



last modified:

7/10/2025